



<b>Technical Data Sheet:</b>	<b>DS508/1013</b>
<b>Product Description</b>	<b>Straight, external thread swivel, nickel plated brass, LTP / LTPHC / LTPUL / LTPE / LTPPU / LTBRDP / LTBRDLFH / LTPSS conduit fitting.</b>
<b>Product Range</b>	<b>LTP - C-S Type fitting (Metric Threads)</b>

Roman Way, Coleshill  
Birmingham  
B46 1HG, United Kingdom  
Tel: 00 44 (0)1675 466900  
Website: www.flexicon.uk.com



**Material:**  
Nickel Plated Brass

**Colour:**  
Self colour

**Fire Performance:**  
Low Fire Hazard  
- Halogen, Sulphur & Phosphorous Free



**IP Rating:**

- IP66, IP67, IP68 (5bar), IP69K

**Applications:**

Suitable for knockouts or threaded entries. Nickel plated brass compression fitting comprising of swivel body, nut, earthing ferrule, nylon compression seal and insulating throat. The external thread swivels about the main body even after tightening. Allows the conduit system to be fully assembled, complete with cables, and still allows the thread to be screwed into threaded entries without rotating the conduit.

**Features:**

- Supplied with insulating throat
- High tensile strength
- Oil resistant
- Corrosion resistant
- Interchangeable with all Liquidtight conduits made to American (UL360) sizes
- Conforms to EN 61386

**Temperature Performance:**

-50°C to +135°C

Conduit Size	Part No.	Metric Thread	Dimension (mm)					
			A	B	C	D	E	F (A/F)
12	LTP12-M16-S	M16 X 1.5	10.0	29.0	22.0	8.6	20.0	20.0
16	LTP16-M16-S	M16 X 1.5	10.0	30.9	26.0	10.7	24.0	24.0
16	LTP16-M20-S	M20 X 1.5	10.0	31.0	26.0	10.7	24.0	24.0
20	LTP20-M20-S	M20 X 1.5	10.0	31.8	29.0	14.5	26.0	26.0
25	LTP25-M25-S	M25 X 1.5	12.0	38.7	35.0	18.0	29.0	33.0
32	LTP32-M32-S	M32 X 1.5	13.0	43.9	42.0	24.6	38.0	40.0
40	LTP40-M40-S	M40 X 1.5	14.0	46.5	52.0	32.7	48.0	50.0
50	LTP50-M50-S	M50 X 1.5	15.0	49.8	58.0	37.7	58.0	58.0

**Compliance, Approvals & Accreditation;**



EN 61386 Classification Available on request

Vibration and Shock resistant to EN 61373 Cat 2

**Typical Applications;**



Errors, omissions and amendments excepted. As part of continuing product development Flexicon Ltd reserve the right to alter product specifications without prior notice. Data given is correct at time of compilation. Product specification and application data is for guidance only and does not constitute a warranty of any kind, either expressed or implied for Flexicon products or their suitability for a specific purpose. Third party approvals maybe limited to certain sizes within a product range.