



- NOTES:**
- ORIENTATION OF  $\varnothing 0.110$  HOLES TO TERMINALS IS NOT CONTROLLED.
  - HARDWARE IS ONLY ASSEMBLED TO FRONT OF JACK. THE REST OF THE HARDWARE IS SHIPPED UNASSEMBLED.
  - MATERIALS:**  
**JACK:**  
 BODY - COPPER ALLOY, NICKEL PLATED  
 INSERT - THERMOPLASTIC  
 GROUND CLIP AND SPRINGS - SPECIAL COPPER ALLOY  
 INSULATING WASHER - PHENOLIC  
 CABLE CLAMP - STEEL, ELECTRO TIN  
**HARDWARE:**  
 STRAP NUT - COPPER ALLOY, GOLD PLATED  
 HEX NUT, WASHER, HANDLE - COPPER ALLOY, NICKEL PLATED  
 LOCK WASHER - SPRING STEEL, NICKEL PLATED
  - SAME AS 6J1206.
  - THIS PRODUCT IS RoHS COMPLIANT.

REV	ECO NUMBER	DATE	BY	APVD
A	28374	03/25/21	PC	TJK
REVISIONS				

UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS IN INCHES [mm]  
 - TWO PLACE DECIMALS  $\pm 0.02$  [0.5]  
 - THREE PLACE DECIMALS  $\pm 0.005$  [0.13]

**DO NOT SCALE DRAWING**

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									
SIZE	WIDTH	MULT	LBS/M	TEMPER					
FINISH					MATERIAL				
SPEC No.					SPEC No.				
FIRST USED ON			SCALE		<b>Switchcraft</b> <sup>®</sup>				
			2:1						
DATE DRAWN	BY	CHKD	APVD						
03/16/21	PC	PC	TJK						
			03/16/21	03/16/21	SHEET 1 OF 1				REV
NAME THICK PANEL JAX WITH GOLD STRAP NUT, RoHS					PART No.		157G		A

**CUSTOMER DRAWING**