



# MASTER TL-D Super 80

MASTER TL-D Super 80 30W/830 1SL

The MASTER TL-D Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

## Product data

### • General Characteristics

Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Cap-Base Information	Green Plate
Bulb	T8 [26 mm]
Life to 10% failures EM	12000 hr
Life to 10% fail Preheat EL,3h	17000 hr
Life to 10% fail Nonpreh EL,3h	10000 hr
Life to 50% failures EM	15000 hr
Life to 50% fail Preheat EL,3h	20000 hr
Life to 50% fail Nonpreh EL,3h	12000 hr
LSF EM 2000h Rated, 3h cycle	99 %
LSF EM 4000h Rated, 3h cycle	99 %
LSF EM 6000h Rated, 3h cycle	99 %
LSF EM 8000h Rated, 3h cycle	99 %
LSF EM 12000h Rated,3h cycle	89 %
LSF EM 16000h Rated,3h cycle	33 %
LSF EM 20000h Rated,3h cycle	2 %

### • Light Technical Characteristics

Color Code	830 [CCT of 3000K]
Color Rendering Index	85 Ra8

Color Designation (text)	Warm White
Color Temperature	3000 K
Luminous Flux EM 25°C, Rated	2400 Lm
Luminous Flux EM 25°C, Nominal	2400 Lm
Lum Efficacy Rated EM 25°C	80 Lm/W
Luminance Average EM	1.10 cd/cm <sup>2</sup>
LLMF EM 2000h Rated	96 %
LLMF EM 4000h Rated	95 %
LLMF EM 6000h Rated	94 %
LLMF EM 8000h Rated	93 %
LLMF EM 12000h Rated	92 %
LLMF EM 16000h Rated	91 %
LLMF EM 20000h Rated	90 %
Design Temperature	25 C
Chromaticity Coordinate X	440 -
Chromaticity Coordinate Y	403 -

### • Electrical Characteristics

Lamp Wattage	30 W
Lamp Wattage EM 25°C, Nominal	30 W

# MASTER TL-D Super 80

Lamp Wattage EM 25°C, Rated	30.0 W
Lamp Voltage EM 25°C	98 V
Lamp Current EM 25°C	0.360 A
Dimmable	Yes

## • Environmental Characteristics

Energy Efficiency Label (EEL)	A
Mercury (Hg) Content	2.0 mg

## • Product Dimensions



Base Face to Base Face A	894.6 (max) mm
Insertion Length B	899.3 (min), 901.7 (max) mm
Overall Length C	908.8 (max) mm

Diameter D 28 (max) mm

## • Product Data

Order code	927920583023
Full product code	927920583023
Full product name	MASTER TL-D Super 80 30W/830 1SL
Order product name	MASTER TL-D Super 80 30W/830 1SL/25
Pieces per pack	1
Packing configuration	25
Packs per outerbox	25
Bar code on pack - EAN1	8711500631831
Bar code on outerbox - EAN3	8711500631848
Logistic code(s) - 12NC	927920583023
ILCOS code	FD-30/30/1B-E-G13
Net weight per piece	103.600 gr

## Dimensional drawing





G13

## MASTER TL-D Super 80 30W/830 1SL

Product	A (Max)	B (Min)	B (Max)	C (Max)	D (Max)
TL-D 30W/830	894.6	899.3	901.7	908.8	28

## Photometric data



© 2013 Koninklijke Philips Electronics N.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2013, January 31  
data subject to change