

## Han-Eco Modular Snap 24-HSE



Image is for illustration purposes only. Please refer to product description.

Part number	09 33 024 0502
Specification	Han-Eco Modular Snap 24-HSE
HARTING eCatalogue	<a href="https://b2b.harting.com/09330240502">https://b2b.harting.com/09330240502</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Snap®
Type of hood/housing	Shell housing
Description of hood/housing	Rear mounting
Type	High construction

### Version

Size	24 B
Version	Side entry
Cable entry	1x
Locking type	Double locking lever
Pack contents	Adapter frame is included within the delivery

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP10

### Material properties

Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)



Pushing Performance  
Since 1945

## Material properties

Material (locking)	Polyamide (PA) Fibre-glass reinforced
Colour (locking)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
Material flammability class acc. to UL 94 (locking levers)	V-0
Length	121 mm
Width	57 mm
Height	111 mm
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Specifications	IEC 61984
Railway classification	F2/I3 acc. to NFF 16-101/102

## Commercial data

Packaging size	1
Net weight	190 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140181977
eCl@ss	27440202 Shell for industrial connectors