

MASTERCcolour CDM-T

MASTERCcolour CDM-T 150W/942 G12 1CT

Range of single-ended, compact, high-efficiency, discharge lamps with a stable colour over lifetime and a crisp, sparkling light



Product data

• General Characteristics

Cap-Base	G12
Bulb	T19 [T 19mm]
Bulb Finish	Clear
Burning Position	any [Any/Universal]
Life to 5% failures EM	9000 hr
Life to 5% failures EL	9000 hr
Life to 10% failures EM	10000 hr
Life to 10% failures EL	10000 hr
Life to 20% failures EM	11000 hr
Life to 20% failures EL	11000 hr
Life to 50% failures EM	12000 hr
Life to 50% failures EL	12000 hr

Lumen Maintenance EM 2000h	85 %
Lumen Maintenance EL 2000h	85 %
Lumen Maintenance EM 5000h	75 %
Lumen Maintenance EL 5000h	80 %
Lumen Maintenance EM 10000h	65 %
Lumen Maintenance EL 10000h	70 %
Design Mean Lumens EL	10800 Lm
Design Mean Lumens EM	9900 Lm
Chromaticity Coordinate X	0.375 -
Chromaticity Coordinate Y	0.363 -

• Light Technical Characteristics

Colour Code	942 [CCT of 4200K]
Colour Rendering Index	96 Ra8
Colour Designation	Cool White
Colour Temperature	4200 K
Colour Temperature Technical	4050 K
Lamp Luminous Flux EM	12000 Lm
Lamp Luminous Flux EL	12700 Lm
Lamp Luminous Efficacy EM	83 Lm/W
Lamp Luminous Efficacy EL	85 Lm/W

• Electrical Characteristics

System Power EM	165 W
System Power EL	167 W
Lamp Wattage	150 W
Lamp Wattage EM 25°C, Nominal	150.0 W
Lamp Wattage EM 25°C, Rated	145.0 W
Lamp Wattage EL 25°C, Rated	150.0 W
Lamp Wattage EL 25°C, Nominal	150.0 W
Lamp Voltage	90 V
Lamp Current EM	1.9 A
Lamp Current EL	1.7 A

PHILIPS

MASTERColour CDM-T

Ignition Time	30 (max) s
Run-up time 90%	3 (max) min
Ignition Peak Voltage	3500 (min) V
Re-ignition Time [min]	15 (max) min
Dimmable	no

• Environmental Characteristics

Energy Efficiency Label (EEL)	A+
Mercury (Hg) Content	10.4 mg
Energy consumption kWh/1000h	165 kWh

• UV-related Characteristics

Damage Factor D/fc PET (NIOSH)	0.4 (max) - 8 (min) h500lx
--------------------------------	----------------------------

• Luminaire Design Requirements

Cap-Base Temperature	280 (max) C
Pinch Temperature	350 (max) C
Bulb Temperature	650 (max) C

• Product Dimensions

Reference Length A	96 (max) mm
--------------------	-------------

Overall Length C	110 (max) mm
Diameter D	20 (max) mm
Light Center Length L	55 (min), 56 (nom), 57 (max) mm
Arc Length O	8 mm
Light Center Length L [inch]	2.21875
Overall Length C [inch]	4.34375 (max)
Diameter D [inch]	0.75 in

• Product Data


Order code	206619 15
Full product code	871150020661915
Full product name	MASTERColour CDM-T 150W/942 G12 1CT
Order product name	MASTERC CDM-T 150W/942 G12 1CT
Pieces per pack	1
Packing configuration	12
Packs per outerbox	12
Bar code on pack - EAN1	8711500206619
Bar code on outerbox - EAN3	8711500206626
Logistic code(s) - 12NC	928084605175
ILCOS code	MT/UB-150/942-H-G12-21/100
Net weight per piece	0.033 kg

- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures


Dimensional drawing



MASTERColour CDM-T 150W/942 G12 1CT


Product	C (Max)	D (Max)	L (Min)	L (Norm)	L (Max)	O (Norm)
CDM-T 150W/942 G12	110	20	55	56	57	8

Dimensional drawing



G12

Photometric data



© 2014 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2014, November 30
data subject to change