
# DUST COVER, SFP, GANGED & STACKED <

TE Part # 1761394-1 TE Internal #: 1761394-1

View on TE.com >



Connectors > Pluggable IO Connectors & Cages > SFP/SFP+/zSFP+/zSQ



Form Factor: SFP

Product Type: Accessory

Data Rate (Max): 4 Gb/s

Port Matrix Configuration: 1 x 1

Pluggable I/O Accessory Type: Dust Cover

### Features


#### Product Type Features

Form Factor

Product Type	Accessory
Pluggable I/O Accessory Type	Dust Cover
Sealable	No
Configuration Features	
Port Matrix Configuration	1 x 1
Number of Ports	1
Electrical Characteristics	
Data Rate (Max)	4 Gb/s
Operation/Application	
For Use With Pluggable I/O Products	SFP Cage
Industry Standards	
UL Flammability Rating	UL 94V-0
Packaging Features	
Packaging Method	Bag

#### DUST COVER, SFP, GANGED & STACKED

TE Part # 1761394-1 TE Internal #: 1761394-1




#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.



## **Compatible Parts**



**Customers Also Bought** 

### DUST COVER, SFP, GANGED & STACKED


TE Part # 1761394-1 TE Internal #: 1761394-1







TE Part #1367147-3 SFP COVER, UNPL, NO LOGO



TE Part #1489948-2 XFP HEAT SINK CLIP, PLATED

#### Documents

Product Drawings DUST COVER, SFP, GANGED & STACKED

English

CAD Files Customer View Model ENG\_CVM\_CVM\_1761394-1\_C.3d\_igs.zip English Customer View Model ENG\_CVM\_CVM\_1761394-1\_C.3d\_stp.zip English Customer View Model ENG\_CVM\_CVM\_1761394-1\_C.2d\_dxf.zip English 3D PDF

#### **Datasheets & Catalog Pages**

1773408-1 Pluggable Input/Output Solutions catalog - SFP section

### DUST COVER, SFP, GANGED & STACKED

TE Part # 1761394-1 TE Internal #: 1761394-1



#### English

1773408-1 Pluggable Input/Output Solutions catalog - SFP+ section

English

4-1773455-4 Quick Reference Guide SFP Solutions

English

4-1773455-3 - Quick Reference Guide SFP+ Solutions

English

SFP+ Product Family: Cages, Connectors, Cable Assemblies 4-1773449-5

English

**Product Specifications** Application Specification

English

**Application Specification** 

English

Product Environmental Compliance

**TE Material Declaration** 

English