




Connectors > Socket Connectors > IC & Component Socket Accessories > IC Socket Hardware



Compatible With IC Socket Type: **LGA 4677**

Card & Socket Accessory Type: **Carrier**

Operating Temperature Range: **-40 – 100 °C**

Features

Product Type Features

Card & Socket Accessory Type	Carrier
------------------------------	---------

Contact Features

Compatible With IC Socket Type	LGA 4677
--------------------------------	----------

Usage Conditions

Operating Temperature Range	-40 – 100 °C
-----------------------------	--------------

Packaging Features

Packaging Method	Box & Tray
------------------	------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2-2347090-1
SOCKET E1 DG1.0 FOR ODM

Customers Also Bought



TE Part #1-2340321-2
ASSY STRADDLE MOUNT 168P 076
SLIVER 2.0



TE Part #2327677-3
RECEPT ASSY, 140 POS, VERT, SLIVER
2.0



TE Part #1-2351052-2
SOCKET E1, E1B CARRIER ASSY



TE Part #1-2351053-2
SOCKET E1 DUST COVER



TE Part #2-2330552-2
ICX POINT PHM CARRIER ASSY, P4



TE Part #2-2347090-1
SOCKET E1 DG1.0 FOR ODM



TE Part #2-2351050-4
SOCKET E1 TFLM ASSY, W/O COVER



TE Part #2-2351050-5
SOCKET E1 TFLM ASSY, W/ COVER



Documents

Product Drawings

SOCKET E1, E1A CARRIER ASSY

English

Product Specifications

Application Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English