



## Basic features

Approval/Conformity	cURus EAC WEEE
---------------------	----------------------

## Electrical connection

Cable diameter D	2.5...5.4 mm
Connection	M8x1-Male, Straight, 3-pin, A-coded
Number of connectable contacts	3
System	Can be fabricated

## Electrical data

Operating voltage $U_b$	32 VDC / 32 VAC
Rated current (40 °C)	4.0 A

## Environmental conditions

Ambient temperature	-40...85 °C
IP rating	IP67

## Material

Conductor insulation material	PVC PP TPE
Housing material	PA Zinc, Die casting
Material contact carrier	PA
Material contacts	Copper alloy
Material cover nut	Brass nickel-plated
Material grip	Plastic

## Mechanical data

Conductor diameter min.	1 mm
Connection cross-section	0.14...0.34 mm <sup>2</sup>
Connection cycles min.	100
Core diameter max.	1.60 mm
Tightening torque pigtail	0.4 Nm
Type of wire mounting	IDC

## Remarks

Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.

## Connector Drawings

