



REV	Change record	Change the date
A/0	Initial issue	2017-05-11



WIRING DIAGRAM:



NOT: COAX

NO.	Cable length (L)	Cable tolerance (T)
1	1000MM	10MM
2	1500MM	15MM
3	1800MM	20MM
4	3000MM	30MM
5		

Test Conditions:


- 100% open & short circuit test;
- Insulation Resistance: 2.0ohm (MAX);
- Conduction Resistance: 10Mohm (MIN) at 300V DC/0.01S .

⑧	JACKET: PVC/TRANSPARENT/ANTI-OXIDATION/50P				
⑦	NYLON WEAVES:BLACK		mm		
⑥	CABLE:30AWG (1P+DW+AL/MY)*5P+4C+ADB OD:7.3, PVC JACKET, BLACK		mm		
⑤	OVER MOLDING:50P PVC RED		g		
④	MIDDLE MOLD:50P PVC STEEL GRAY		g		
③	INNER MOLDING:LD PE		g		
②	ALUMINIUM ALLOY SHELL, RED, RED COIL		PCS		
①	HDMI 19PIN MALE SOLDERING TYPE GOLD PLATED, 3u		PCS		
NO.	THE MATERIAL CONTENT	STOCK NO.	UNIT	QUANTITY	MouId NO.


**VCOM** VCOM INTERNATIONAL LTD.

TITLE	HDMI19PM/HDMI19PM	CUSTOMER		UNIT	mm	PAGE: 1 of 1
PART NO.	VC-F14-0025-B	CUSTOMER NO.		SCALE		
PRODUCT NO.	CG526-R	REV:	A/0	DATE	2017-05-11	
DRAWN BY: XGS		CHECKED BY:		APPROVED BY:CT		

REV	Change record	Change the date
A/0	Initial issue	2017-05-11



WIRING DIAGRAM:



NOT: COAX

NO.	Cable length (L)	Cable tolerance (T)
1	5000MM	50MM
2	10000MM	100MM
3		

Test Conditions:

- 100% open & short circuit test;
- Insulation Resistance: 2Mohm (MIN);
- Conduction Resistance: 10ohm (MAX) at 300V DC/0.01S .

⑧	JACKET: PVC/TRANSPARENT/ANTI-OXIDATION/50P				
⑦	NYLON WEAVES:BLACK		/	/	
⑥	CABLE:30AWG (1P+DW+AL/MY)*5P+4C+ADB OD:7.3, PVC JACKET, BLACK		PCS	1	
⑤	OVER MOLDING:50P PVC BLACK		g	/	
④	MIDDLE MOLD:50P PVC STEEL GRAY		g	/	
③	INNER MOLDING:LD PE		g	/	
②	ALUMINIUM ALLOY SHELL, RED, RED COIL		PCS	2	
①	HDMI 19PIN MALE SOLDERING TYPE GOLD PLATED, 15u		PCS	2	
NO.	THE MATERIAL CONTENT	STOCK NO.	UNIT	QUANTITY	MOULD NO.

**VCOM** VCOM INTERNATIONAL LTD.

TITLE	HDMI19PM/HDMI19PM	CUSTOMER		UNIT	mm	PAGE: 1 of 1
PART NO.	VC-F14-0025-B1	CUSTOMER NO.		SCALE		
PRODUCT NO.	CG526-R	REV:	A/0	DATE	2017-05-11	
DRAWN BY:		CHECKED BY:		APPROVED BY:CT		