## VS-26MT.., VS-36MT.. Series

**Vishay Semiconductors** 

COMPLIANT

# Three Phase Bridge (Power Modules), 25 A to 35 A



www.vishay.com

PRIMARY CHARACTERISTICS			
Ι <sub>Ο</sub>	25 A to 35 A		
V <sub>RRM</sub>	50 V to 1600 V		
Package	D-63		
Circuit configuration	Three phase bridge		

#### **FEATURES**

- Universal, 3 way terminals: push-on, wrap around or solder RoHS
- · High thermal conductivity package, electrically insulated case
- Center hole fixing
- Excellent power/volume ratio
- UL E300359 approved
- Nickel plated terminals solderable using lead (Pb)-free solder; solder alloy Sn/Ag/Cu (SAC305); solder temperature 260 °C to 275 °C
- Designed and qualified for industrial and consumer level
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

#### DESCRIPTION

A range of extremely compact, encapsulated three phase bridge rectifiers offering efficient and reliable operation. They are intended for use in general purpose and instrumentation applications.

MAJOR RATINGS AND CHARACTERISTICS					
SYMBOL	CHARACTERISTICS	VALUES 26MT	VALUES 36MT	UNITS	
		25	35	A	
IO	T <sub>C</sub>	70	60	°C	
	50 Hz	360	475	٨	
IFSM	60 Hz	375	500	A	
l <sup>2</sup> t	50 Hz	635	1130	A <sup>2</sup> s	
1-1	60 Hz	580	1030	A-S	
V <sub>RRM</sub>		50 to 1600		V	
TJ		-55 to	°C		

#### **ELECTRICAL SPECIFICATIONS**

VOLTAGE RATINGS						
TYPE NUMBER	VOLTAGE CODE	V <sub>RRM</sub> , MAXIMUM REPETITIVE PEAK REVERSE VOLTAGE V	V <sub>RSM</sub> , MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE V	I <sub>RRM</sub> MAXIMUM AT T <sub>J</sub> MAXIMUM mA		
	05	50	75			
10		100	150			
	20 40	200	275			
VS-26MT		400	500			
	60	600	725	2		
VS-36MT	80	800	900	2		
120	100	1000	1100			
	120	1200	1300			
	140	1400	1500			
	160	1600	1700			

HAY. www.vishay.com

**Vishay Semiconductors** 

FORWARD CONDUCTION							
PARAMETER	SYMBOL	TEST CONDITIONS		VALUES 26MT	VALUES 36MT	UNITS	
Maximum DC output current at T <sub>C</sub>		m DC output current at T <sub>C</sub> $I_{O}$ 120° rect. conduction angle	100° root conduction angle		25	35	А
Maximum DC output current at T <sub>C</sub>	Ι <sub>Ο</sub>	120 1601.001	iduction angle		70	60	°C
	I <sub>FSM</sub>	t = 10 ms	No voltage		360	475	A
Maximum peak, one-cycle		t = 8.3 ms	reapplied		375	500	
non-repetitive forward current		t = 10 ms	100 % V <sub>RRM</sub>		300	400	
		t = 8.3 ms	reapplied	Initial	314	420	
Maximum I <sup>2</sup> t for fusing	l <sup>2</sup> t	t = 10 ms	No voltage	$T_J = T_J maximum$	635	1130	A <sup>2</sup> s
		t = 8.3 ms	reapplied		580	1030	
		t = 10 ms	100 % V <sub>RRM</sub>		450	800	
		t = 8.3 ms	reapplied		410	730	
Maximum I²√t for fusing	l²√t	$l^2t$ for time $t_x = l^2 \sqrt{t} \; x \; \sqrt{t_x}; \; 0.1 \leq t_x \leq 10 \; \text{ms}, \; V_{\text{RRM}} = 0 \; \text{V}$		6360	11 300	A²√s	
Low level of threshold voltage	V <sub>F(TO)1</sub>	(16.7 % x $\pi$ x $I_{F(AV)} < I < \pi$ x $I_{F(AV)}$ ), T <sub>J</sub> maximum		0.88	0.86	v	
High level of threshold voltage	V <sub>F(TO)2</sub>	$(I > \pi x I_{F(AV)}), T_J$ maximum		1.13	1.03	v	
Low level forward slope resistance	r <sub>t1</sub>	(16.7 % x $\pi$ x $ _{F(AV)}$ < I < $\pi$ x $ _{F(AV)}$ ), T <sub>J</sub> maximum		7.9	6.3	mΩ	
High level forward slope resistance	r <sub>t2</sub>	$(I > \pi \times I_{F(AV)}), T_J$ maximum		5.2	5.0	1115.2	
Maximum forward voltage drop	V <sub>FM</sub>	$T_J = 25 \text{ °C}, I_{FM} = 40 \text{ Apk} - \text{per single junction}$		1.26	1.19	V	
Maximum DC reverse current	I <sub>RRM</sub>	$T_J = 25 \text{ °C}$ , per junction at rated $V_{RRM}$		1(	00	μA	
RMS isolation voltage	V <sub>INS</sub>	$T_J = 25$ °C, all terminal shorted; f = 50 Hz, t = 1 s		27	00	V	

THERMAL - MECHANICAL SPECIFICATIONS						
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES 26MT	VALUES 36MT	UNITS	
Maximum junction and storage temperature range	T <sub>J</sub> , T <sub>Stg</sub>		-55 to	+150	°C	
Maximum thermal resistance, junction to case	R <sub>thJC</sub>	DC operation per bridge (based on total power loss of bridge)	1.42	1.35	- K/W	
Maximum thermal resistance, case to heatsink	R <sub>thCS</sub>	Mounting surface, smooth, flat and greased	0.2	0.2		
Approximate weight			2	0	g	
Mounting torque ± 10 %		Bridge to heatsink with screw M4	2.	.0	Nm	






Fig. 1 - Current Ratings Characteristics





Revision: 05-Sep-17

2

Document Number: 93565

For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>




Fig. 3 - Total Power Loss Characteristics




Fig. 4 - Maximum Non-Repetitive Surge Current






Fig. 5 - Maximum Non-Repetitive Surge Current

150 36MT.. Series 130 Maximum Allowable Case Temperature (°C) 110 90 120° (rect.) 70 50 0 5 10 15 20 25 30 35 40 **Total Output Current (A)** 








Revision: 05-Sep-17


3

Document Number: 93565

For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



**Vishay Semiconductors** 






Fig. 8 - Total Power Loss Characteristics




Fig. 10 - Maximum Non-Repetitive Surge Current Fig. 9 - Maximum Non-Repetitive Surge Current






Fig. 11 - Thermal Impedance Z<sub>thJC</sub> Characteristics

Revision: 05-Sep-17 Document Number: 93565 4 For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000






### **ORDERING INFORMATION TABLE**



### **CIRCUIT CONFIGURATION**



LINKS TO RELATED DOCUMENTS			
Dimensions	www.vishay.com/doc?95251		

Document Number: 93565






D-63

#### **DIMENSIONS** in millimeters (inches)

www.vishay.com

/ISHAY



Not to scale



Vishay

## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.