

SCHOTTKY RECTIFIER

1.1 Amp

Major Ratings and Characteristics



Characteristics	11DQ..	Units
$I_{F(AV)}$ Rectangular waveform	1.1	A
V_{RRM}	90/100	V
I_{FSM} @ $t_p = 5 \mu s$ sine	85	A
V_F @ 1 Apk, $T_J = 25^\circ C$	0.85	V
T_J range	-40 to 150	$^\circ C$

Description/Features

The 11DQ.. axial leaded Schottky rectifier has been optimized for very low forward voltage drop, with moderate leakage. Typical applications are in switching power supplies, converters, free-wheeling diodes, and reverse battery protection.

- Low profile, axial leaded outline
- High purity, high temperature epoxy encapsulation for enhanced mechanical strength and moisture resistance
- Very low forward voltage drop
- High frequency operation
- Guard ring for enhanced ruggedness and long term reliability

CASE STYLE AND DIMENSIONS



Conform to JEDEC Outline DO-204AL (DO-41)

Dimensions in millimeters and inches

Voltage Ratings

Part number	11DQ09	11DQ10
V_R Max. DC Reverse Voltage (V)	90	100
V_{RWM} Max. Working Peak Reverse Voltage (V)		

Absolute Maximum Ratings

Parameters		11DQ..	Units	Conditions	
$I_{F(AV)}$	Max. Average Forward Current * See Fig. 4	1.1	A	50% duty cycle @ $T_C=75^{\circ}\text{C}$, rectangular wave form	
I_{FSM}	Max. Peak One Cycle Non-Repetitive Surge Current * See Fig. 6	85	A	5 μs Sine or 3 μs Rect. pulse	Following any rated load condition and with rated V_{RRM} applied
		14		10ms Sine or 6ms Rect. pulse	

Electrical Specifications

Parameters		11DQ..	Units	Conditions	
V_{FM} Max. Forward Voltage Drop * See Fig. 1 (1)		0.85	V	@ 1A	$T_J = 25\text{ }^{\circ}\text{C}$
		0.96	V	@ 2A	
		0.68	V	@ 1A	$T_J = 125\text{ }^{\circ}\text{C}$
		0.78	V	@ 2A	
I_{RM} Max. Reverse Leakage Current * See Fig. 2 (1)		0.5	mA	$T_J = 25\text{ }^{\circ}\text{C}$	$V_R = \text{rated } V_R$
		1.0	mA	$T_J = 125\text{ }^{\circ}\text{C}$	
C_T Typical Junction Capacitance		35	pF	$V_R = 5V_{DC}$, (test signal range 100Khz to 1Mhz) $25\text{ }^{\circ}\text{C}$	
L_S Typical Series Inductance		8.0	nH	Measured lead to lead 5mm from package body	

(1) Pulse Width < 300 μs , Duty Cycle < 2%

Thermal-Mechanical Specifications

Parameters	11DQ..	Units	Conditions
T_J Max. Junction Temperature Range	-40 to 150	$^\circ\text{C}$	
T_{stg} Max. Storage Temperature Range	-40 to 150	$^\circ\text{C}$	
R_{thJA} Max. Thermal Resistance Junction to Ambient	130	$^\circ\text{C/W}$	DC operation Without cooling fin
R_{thJA} Typical Thermal Resistance Junction to Ambient with PC Board Mounted	81	$^\circ\text{C/W}$	PC board mounted [L=8mm (0.315in.)] Solder land area 100mm ² (0.155in ² .)
wt Approximate Weight	0.33(0.012)	g(oz.)	
Case Style	DO-204AL (DO-41)		




Fig.1 - Max. Forward Voltage Drop Characteristics




Fig.2 - Typical Values Of Reverse Current Vs. Reverse Voltage




Fig.3 - Typical Junction Capacitance Vs. Reverse Voltage




Fig. 4 - Max. Allowable Case Temperature Vs. Average Forward Current




Fig. 5 - Forward Power Loss Characteristics




Fig. 6 - Max. Non-Repetitive Surge Current

(2) Formula used: $T_C = T_J - (Pd + Pd_{REV}) \times R_{thJC}$;

Pd = Forward Power Loss = $I_{F(AV)} \times V_{FM} @ (I_{F(AV)} / D)$ (see Fig. 6);

Pd_{REV} = Inverse Power Loss = $V_{R1} \times I_R (1 - D)$; $I_R @ V_{R1} = 80\%$ rated V_R

WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245 U.S.A Tel: (310) 322-3331 Fax: (310) 322-3332
EUROPEAN HEADQUARTERS: Hurst Green, Oxted, Surrey RH8 9BB, U.K. Tel: ++ 44 1883 732020 Fax: ++ 44 1883 733408
IR CANADA: 7231 Victoria Park Ave., Suite #201, Markham, Ontario L3R 2Z8 Tel: (905) 475 1897. Fax: (905) 475 8801
IR GERMANY: Saalburgstrasse 157, 61350 Bad Homburg Tel: ++ 49 6172 96590 Fax: ++ 49 6172 965933
IR ITALY: Via Liguria 49, 10071 Borgaro, Torino Tel: ++ 39 11 4510111 Fax: ++ 39 11 4510220
IR FAR EAST: K&H Bldg., 2F, 30-4 Nishi-Ikebukuro 3-Chome, Toshima-Ku, Tokyo, Japan 171 Tel: 81 3 3983 0086 Fax: 81 3 3983 0642
IR SOUTHEAST ASIA: 315 Outram Road, # 10-02 Tan Boon Liat Building, SINGAPORE 0316. Tel: 65 221 8371. Fax: 65 221 8372.