
# **Autonics**

# **Photomicro Sensor with Amplifier BS5 SERIES**

# INSTRUCTION MANUAL



Thank you for choosing our Autonics product. Please read the following safety considerations before use.

## Safety Considerations

\*\*Please observe all safety considerations for safe and proper product operation to avoid hazards

※▲ symbol represents caution due to special circumstances in which hazards may occur.

▲ Warning Failure to follow these instructions may result in serious injury or death.

▲ Caution Failure to follow these instructions may result in personal injury or product damage


## **▲** Warning

- 1. Fail-safe device must be installed when using the unit with machinery that may cause serious injury or substantial economic loss. (e.g. nuclear power control, medical equipment, ships, vehicles, railways, aircraft, combustion apparatus, safety equipment crime/disaster prevention devices etc.)
- Failure to follow this instruction may result in fire, personal injury, or economic loss
- 2. Do not disassemble or modify the unit.
- Failure to follow this instruction may result in fire
- 3. Do not connect, repair, or inspect the unit while connected to a power source. Failure to follow this instruction may result in fire.
- 4. Check 'Connections' before wiring.
- Failure to follow this instruction may result in fire


# **▲** Caution


- Use the unit within the rated specifications.
   Failure to follow this instruction may result in fire or product damage
- 2. Use dry cloth to clean the unit, and do not use water or organic solvent
- 3. Do not use the unit in the place where flammable/explosive/corrosive gas, humidity, direct sunlight, radiant heat, vibration, impact, or salinity may be present. Failure to follow this instruction may result in fire or explosion.

# Ordering Information




### Control Output Circuit Diagram







- X1: Operation mode selection: Connect (white)Control cable (terminal) into terminal (brown)+V to operate Light ON mode Dark ON mode is available with disconnection status.
- XIf short-circuit the control output terminal or supply current over the rated specification
- normal control signal is not output due to the output short over current protection circuit
- %The above specifications are subject to change and some models may be discontinued without notice


#### Dimensions








\*When using photoelectric sensors closely over two units, it may result in malfunction due to mutual interference. When installing the product, tighten the screw with a tightening torque of 0.49Nm •BS5-Y1M / BS5-Y1M-P M3 Bolt











# Specifications

2.54

Approval

Weight\*\*

Approx. 50g (approx. 30g)

t=0.2mm

※2: The weight includes packaging. The weight in parentheses is for unit only.
※The temperature or humidity mentioned in Environment indicates a non freezing or condensation environment.

<del>l</del> e	collector output	BS5-K1M	BS5-T1M	BS5-L1M	BS5-Y1M	BS5-V1M	BS5-K2M	BS5-T2M	BS5-L2M	BS5-Y2M	BS5-V2M	
Mo	PNP open collector output	BS5- K1M-P	BS5- T1M-P	BS5- L1M-P	BS5- Y1M-P	BS5- V1M-P	BS5- K2M-P	BS5- T2M-P	BS5- L2M-P	BS5- Y2M-P	BS5- V2M-P	
Sensing type		Through-beam (not modulated)										
Sensing distance		5mm fixed										
Sensing target Hysteresis		0.8×2mm Opaque materials										
		0.05mm										
Res	sponse time	Light ON: max. 20µs, dark ON: max. 100µs										
Res	ponse frequency*1	2kHz										
Pov	ver supply	5-24VDC== ±10% (ripple P-P: max. 10%)										
1	rent sumption	Max. 30mA (at 26.4VDC)										
Ligh	nt source	Infrared LED (940nm)										
Оре	eration mode	Light ON / Dark ON selectable by control wire Light ON / Dark ON selectable by control terminal										
Cor	ntrol output	NPN or PNP open collector output  Load voltage: max. 30VDC::  Load current: max.100mA  Residual voltage: max. 1.2VDC::										
Pro	tection circuit	Reverse power polarity protection circuit, output short overcurrent protection circuit										
Indi	cator	Operation Indicator: red LED										
Connection		Cable type Connector type										
Insulation resistance		Over 20MΩ (at 250VDC megger)										
Noise immunity Dielectric strength Vibration Shock		±240V the square wave noise (pulse width: 1μs) by the noise simulator										
		1,000VAC 50/60Hz for 1 minute										
		1.5mm amplitude at frequency of 10 to 55Hz (for 1 min.) in each X, Y, Z direction for 2 hours										
		500m/s² (approx. 50G) in X, Y, Z directions for 3 times										
ent	Ambient illumination	Fluorescent lamp: max. 1,000lx (receiver illumination)										
Environment	Ambient temperature	e -20 to 55°C, storage: -25 to 85°C										
Envi	Ambient humidity	35 to 85%RH, storage: 35 to 85%RH										
Protection structure Material		IP50 (IEC standard)										
		PBT										
Cable			vire, 1m (AW cores: 19, ins				_					

# Operation Mode

Operation mode	Light ON	Dark ON			
Receiver operation	Received light Interrupted light —	Received light Interrupted light			
Operation indicator (red LED)	ON OFF —	ON OFF			
Transistor output	ON OFF —	ON OFF			

## Caution during Use

- . Follow instructions in 'Cautions during Use'. Otherwise, it may cause unexpected accidents.
- Use the product, 0.5 sec after supplying power.
   When using separate power supply for the sensor and load, supply power to sensor first.
   3.5-24VDC power supply should be insulated and limited voltage/current or Class 2, SELV power supply device.

■ Temperature Controllers

Counters
Timers

■ Panel Meters

■ Display Units ■ Sensor Controllers

Temperature/Humidity Transducers ■ SSRs/Power Controllers


■ Tachometers/Pulse(Rate)Meters

- Wire as short as possible and keep away from high voltage lines or power lines, to prevent inductive noise.
   When using sensor with the equipment which generates noise (switching regulator, inverter, servo motor, etc.), ground F.G. terminal of the
- equipment.

  6. This unit may be used in the following environments.
- ①Indoors (in the environment condition rated in 'Specifications')
  ③Pollution degree 2

@Altitude max. 2.000m

# Connection



## Major Products

- Photoelectric Sensors
- Fiber Optic Sensors
- Door Sensors
- Door Side Sensors
   Area Sensors

- Proximity Sensors
   Pressure Sensors
- Rotary Encoders
   Connectors/Sockets
- Switching Mode Power Supplies
- Control Switches/Lamps/Buzzers
- I/O Terminal Blocks & Cables
- Stepper Motors/Drivers/Motion Controllers
- Graphic/Logic Panels
- Field Network Devices
   Laser Marking System(Fiber, CO₂, Nd:YAG)
   Laser Welding/Cutting System

Autonics Corporation http://www.autonics.com

■ HEADQUARTERS:

18, Bansong-ro 513beon-gil, Haeundae-gu, Busan, South Korea, 48002 TFI : 82-51-519-3232

DRW171441AA