

PRODUCT SPECIFICATION

1.0 SCOPE

This Product Specification covers the 3.96 mm (.156 inch) centerline (pitch) Trifurcon Connectors terminated with 18 to 26 AWG wire using crimp technology when mated with 1.14mm (.045) square pin headers.

2.0 PRODUCT DESCRIPTION

2.1 PRODUCT NAME AND SERIES NUMBERS

Crimp Terminals: 6838, 7258 Crimp Housings: 41695, 6442 Headers: 41771, 41772, 41791, 41792, 42491, 42492, 41661, 41662, 41671, 41672, 41681, 41682 Other products conforming to this specification are noted on the individual drawings.

2.2 DIMENSIONS, MATERIALS, PLATINGS AND MARKINGS

Terminal Material: Brass or Phos. Bronze (for Max performance use phos bronze material.) Housing: Nylon or Polyester Pins: Brass

For more information on dimensions, materials, and plating see the individual drawings.

2.3 SAFETY AGENCY APPROVALS

UL File Number E29179

CSALR19980

CSALIN 19900						
	Agency	Voltage	Agency Current		Agency	
	Rating (A	C RMS or	Rating (Temperature	
SERIES	DC) exce	ot as noted	Circuit) ((Amps)	Rating (°C)	
	UL	CSA	UL	CSA	UL	
6442	600	250	-	7	105°C	
41695	600	250VAC	-	7	105°C	
41661	600	250	-	7	105°C	
41662	600	250	-	7	105°C	
41671	600	250	-	7	105°C	
41672	600	250	-	7	105°C	
41681	600	250	-	7	105°C	
41682	600	250	-	7	105°C	
41771	600	250	-	7	105°C	
41772	600	250	-	7	105°C	
41791	600	250	-	7	105°C	
41792	600	250	-	7	105°C	
42491	600	250	-	7	105°C	
42492	600	250	-	7	105°C	

REVISION:	ECR/ECN INFORMATION:	TITLE: PRODU	JCT SPECIFICATI	ON	SHEET No.
E1	EC No: UCP2016-2207	.156 CENTER KK CONNECTORS		1 of 5	
	<u>DATE:</u> 2015/11/30	TRIFU	1013		
DOCUMENT NUMBER:		CREATED / REVISED BY:	CHECKED BY:	APPROV	ED BY:
PS-40-02		MKIPPER JBELL FSMITH-ROEMER			
TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A](V.1).DOC					



PRODUCT SPECIFICATION

3.0 APPLICABLE DOCUMENTS AND SPECIFICATIONS None

4.0 RATINGS

4.1 VOLTAGE

600 Volts AC (RMS) (or 600 Volts DC)

4.2 CURRENT (Current is dependent on connector size, contact material, plating, ambient temperature, printed circuit board characteristics and related factors. Actual current rating is application dependent and should be evaluated for each application.)

Wire	Amps (Max) With	Amps (Max) With Phos	Wire Insulation Dia
Awg	Brass Terminals	Bronze Terminals	
18	5.00	7.00	See terminal drawings
20	4.75	6.25	See terminal drawings
22	4.50	5.50	See terminal drawings
24	4.25	5.00	See terminal drawings
26	4.00	4.50	See terminal drawings

Note: current ratings are for a single circuit, based on not exceeding 30°C temperature rise.

4.3 TEMPERATURE

	Brass Terminals	Phos Bronze Terminals
Operating Temperature	-40°C to +80°C*	-40°C to +105°C*
Non-Operating Temperature	-40°C to +105°C**	-40°C to +105°C

*including terminal temperature rise.

**parts not mated

REVISION:	ECR/ECN INFORMATION:	TITLE: PRODU	JCT SPECIFICATI	ON	SHEET No.
E1	<u>EC No:</u> UCP2016-2207	.156 CENTER KK CONNECTORS		2 of 5	
	DATE: 2015/11/30	TRIFU	Z 01 J		
DOCUMENT NUMBER:		CREATED / REVISED BY:	CHECKED BY:	APPRO\	/ED BY:
PS-40-02		MKIPPER	JBELL	FSMITH-F	ROEMER
TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A](V.1).DOC					



5.0 PERFORMANCE 5.1 ELECTRICAL REQUIREMENTS

DESCRIPTION	TEST CONDITION	REQUIREMENT
Contact Resistance (Low Level)	Mate connectors: apply a maximum voltage of 20 mV and a current of 100 mA.	6 milliohms MAXIMUM [initial]
Contact Resistance of Wire Termination (Low Level)	Terminate the applicable wire to the terminal and measure wire using a voltage of 20 mV and a current of 100 mA.	2 milliohms MAXIMUM [initial]
Insulation Resistance	Unmate & unmount connectors: apply a voltage of 500 VDC between adjacent terminals and between terminals to ground.	50 K Megohms MINIMUM
Dielectric Withstanding Voltage	Unmate connectors: apply a voltage of {two times the rated voltage plus 1000 volts} VAC for 1 minute between adjacent terminals and between terminals to ground.	No breakdown
Capacitance	Measure between adjacent terminals at 1 MHz.	1.2 picofarads MAXIMUM
Temperature Rise (via Current Cycling)	 Mate connectors: measure the temperature rise at the rated current after: 1) 96 hours (steady state) 2) 240 hours (45 minutes ON and 15 minutes OFF per hour) 3) 96 hours (steady state) 	Temperature rise: +30°C MAXIMUM

					1
REVISION:	ECR/ECN INFORMATION:	TITLE: PRODI	TITLE: PRODUCT SPECIFICATION		SHEET No.
E1	EC No: UCP2016-2207	.156 CENTER KK CONNECTORS		-	3 of 5
	<u>DATE:</u> 2015/11/30	TRIFU	J 01 J		
DOCUMENT NUMBER:		CREATED / REVISED BY:	CHECKED BY:	APPROV	/ED BY:
	PS-40-02	MKIPPER	JBELL	FSMITH-F	ROEMER
TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A](V.1).DOC					



ESCRIPTION	TEST CONDITION	REQUIREMENT
Connector Mate and Unmate Forces	Per circuit when mated to an .045 Sq. pin header without friction lock. Mate and unmate connector (male to female) at a rate of 25 ± 6 mm (1 $\pm \frac{1}{4}$ inch) per minute.	10.0 N (2.25 lbf) MAXIMUM insertion force & 3.7 N (0.84 lbf) MINIMUM withdrawal force
Terminal Insertion Force (into Housing)	Apply an axial insertion force on the terminal at a rate of $25 \pm 6 \text{ mm} (1 \pm \frac{1}{4} \text{ inch})$. (Forces will change with platings and materials.)	17.8 N (4.0 lbf) MAXIMUM insertion force
Terminal Retention Force (in Housing)	Axial pullout force on the terminal in the housing at a rate of $25 \pm 6 \text{ mm} (1 \pm \frac{1}{4} \text{ inch})$ per minute. (Forces will change with platings and materials.)	35.6 N (8.0 lbf) MINIMUM withdrawal force
Durability	Mate connectors up to 25 cycles at a maximum rate of 10 cycles per minute prior to Environmental Tests.	10 milliohms MAXIMUM (change from initial)
Vibration (Random)	Mate connectors and vibrate per EIA 364-28, test condition VII.	10 milliohms MAXIMUM (change from initial) & Discontinuity < 1 microsecon
Shock (Mechanical)	Mate connectors and shock at 50 g's with $\frac{1}{2}$ sine wave (11 milliseconds) shocks in the $\pm X, \pm Y, \pm Z$ axes (18 shocks total).	10 milliohms MAXIMUM (change from initial]) & Discontinuity < 1 microsecon
Wire Pullout Force (Axial)	Apply an axial pullout force on the wire at a rate of 25 ± 6 mm ($1 \pm \frac{1}{4}$ inch). (For maximum performance use molex application tooling with stranded tinned copper wire)	Wire pullout force depends or crimp tooling. See relevant Molex Application Tooling Specification for requirements
Normal Force	Apply a perpendicular force.	7.34 N (748 grams) average

REVISION:	ECR/ECN INFORMATION:		JCT SPECIFICATI	ON	SHEET No.
E1	EC No: UCP2016-2207	.156 CEN	-	4 of 5	
	DATE: 2015/11/30	TRIFL	4 01 J		
DOCUMENT NUMBER:		CREATED / REVISED BY:	CHECKED BY:	<u>APPROV</u>	/ED BY:
PS-40-02		MKIPPER	JBELL	FSMITH-F	ROEMER
TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A](V.1).DOC					



5.3 ENVIRONMEN	TAL REQUIREMENTS	
DESCRIPTION	TEST CONDITION	REQUIREMENT
Shock (Thermal)	Mate connectors; expose to 5 cycles of: Temperature °C Duration (Minutes) -40 +0/-3 30 +25 ±10 5 MAXIMUM +105 +3/-0 30 +25 ±10 5 MAXIMUM	10 milliohms MAXIMUM (change from initial) & Visual: No Damage
Thermal Aging	Mate connectors; expose to: 96 hours at 105 ± 2°C	10 milliohms MAXIMUM (change from initial]) & Visual: No Damage
Humidity (Steady State)	Mate connectors: expose to a temperature of 40 ± 2°C with a relative humidity of 90-95% for 96 hours. Note: Remove surface moisture and air dry for 1 hour prior to measurements.	10 milliohms MAXIMUM (change from initial) & Dielectric Withstanding Voltage: No Breakdown at 500 VAC & Insulation Resistance: 1000 Megohms MINIMUM & Visual: No Damage
Solderability	Per SMES-152	Solder coverage: 95% MINIMUM (per SMES-152)
Solder Resistance	Dip connector terminal tails in solder: Solder Duration: 5 ± 0.5 seconds; Solder Temperature: $230 \pm 5^{\circ}$ C	Visual: No Damage to insulator material

6.0 PACKAGING

Parts shall be packaged to protect against damage during handling, transit and storage.

7.0 GAGES AND FIXTURES

8.0 OTHER INFORMATION

REVISION:	ECR/ECN INFORMATION:	TITLE: PRODL	JCT SPECIFICATI	ON	SHEET No.
E 4	EC No: UCP2016-2207		TER KK CONNEC		E (E
E1	<u>DATE:</u> 2015/11/30	TRIFU	5 of 5		
DOCUMENT NUMBER:		CREATED / REVISED BY:	CHECKED BY:	APPROV	/ED BY:
PS-40-02 МКІРР		MKIPPER	JBELL	FSMITH-F	ROEMER
TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A](V.1).DOC					