

# RSF70 Series

The RSF70 series is designed for external mounting, achieved with a high grade compression seal. This avoids the need for access to the inside of the chamber and is ideally suited to applications where space or fitting time are prime considerations.

They are manufactured in a variety of materials, with a choice of gasket materials, to suit most commonly used liquids.

The switch action may be reversed by rotating the device through 180°C.


TECHNICAL SPECIFICATIONS	RSF73	RSF74	RSF76
Material	Nylon	Polypropylene	Polyphenylene Sulphide (PPS)
Colour	Black	Opaque	Grey
Temp. Range °C	-20 / +75	-20 / +100	-10 / +120*
°F	-4 / +167	-4 / +212	+14 / +248*
Min. Fluid S.G.	0.85	0.85	0.85
Must Close Level (S.G.=1)	7mm	8mm	9mm
Must Open Level (S.G.=1)	20mm	20mm	24mm

\*Maximum temperature requires ETFE cable to be specified.

ELECTRICAL SPECIFICATIONS	Y	V
Contact Form	N/O (N/C)	C/O
VA Rating	25	3
Breakdown Voltage DC	800	150
Switching Voltage AC	240	48
Switching Voltage DC	120	28

All ratings are for resistive load only

\*Maximum Temperature requires ETFE cable to be specified.



\* 49mm RSF76

\*\* Add 10mm to dims. RSF76

Every effort has been made to ensure that the descriptions and specifications quoted are correct, however, no liability can be accepted for any errors or omissions in this data. The detail specifications are subject to change without prior notice.

**CRYDOM**

Control over power



- External mount
- Fast fitting
- Compact size
- Available in Nylon, Polypropylene and PPS
- WRAS approval
- Many variants are UL recognised components
- File Number E171218

Crydom Magnetics Ltd  
 7 Cobham Road  
 Ferndown Industrial Estate  
 Wimborne  
 Dorset BH21 7PE  
 Tel: +44 (0) 1202 897969  
 Fax: +44 (0) 1202 891918  
 magnetics@crydom.com  
 www.crydom.co.uk