

KEMET Part Number: ALS70A202KE400
(A390LH202M400A)

ALS70, Aluminum Electrolytic, 2,000 uF, 20%, 400 VDC, -40/+85°C



General Information

Supplier:	KEMET
Series:	ALS70
Dielectric:	Aluminum Electrolytic
Description:	Screw Terminal, Aluminum Electrolytic
RoHS:	Yes
AEC-Q200:	No
Notes:	Dimensions D And L Include Slewing. MS (MxH) = M12x16. Mounting Clip (Sold Separately): V4/2737

Dimensions

D	51mm +/-1mm
L	82mm +/-2mm
T	5.5mm +/-0.5mm
S	22.2mm +/-0.5mm
DT	13mm +/-0.5mm
LT	86.5mm +/-1mm
TD	10mm MIN
V	13.7mm NOM
Z	10mm NOM

Specifications

Capacitance:	2,000 uF
Capacitance Tolerance:	20%
Voltage DC:	400 VDC, 440 VDC (Surge)
Temperature Range:	-40/+85°C
Rated Temperature:	85°C
Life:	18000 Hrs (Rated Voltage And Ripple Current At 85C), 36000 Hrs (Rated Voltage At 85C)
Resistance:	87 mOhms (100Hz 20C), 52 mOhms (10kHz 20C)
Ripple Current:	7.6 Amps (100Hz 85C), 13.6 Amps (10 kHz 85C)
Leakage Current:	4800 uA

Packaging Specifications

Weight:	220 g
Slewing:	Yes
Packaging:	Tray