



## 6901 - MALE STUD FITTING FDA NICKEL-PLATED BRASS EPDM SEA



<b>maximum working pressure</b>	16 bar 2 MPa 232 psi
<b>working temperature</b>	-10 to 130 °C 14 to 266 °F 263 to 403 °K
<b>vacuum capability</b>	755 mm Hg
<b>body</b>	FDA CHEMICAL NICKEL PLATED BRASS
<b>'O'-rings</b>	EPDM
<b>gripping ring</b>	STAINLESS STEEL




Part Nb	ØD (MM)	C	E (mm)	F (mm)	(mm)	H (mm)	(kg)
	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾
6901 04 10	4	G1/8	5.5	13	3	11.5	.007
6901 04 13	4	G1/4	5.5	16	3	10.5	.011
6901 04 19	4	M5x0,8	3	8	2.5	14	.003
6901 06 10	6	G1/8	4.5	13	4	14	.007
6901 06 13	6	G1/4	5.5	16	4	12.5	.011
6901 06 19	6	M5x0,8	3	11	2.5	16	.005
6901 08 10	8	G1/8	4.5	13	5	20.5	.011
6901 08 13	8	G1/4	5.5	16	6	19.5	.016
6901 08 17	8	G3/8	5.5	20	6	18	.022
6901 10 13	10	G1/4	5.5	16	7	23	.018
6901 10 17	10	G3/8	5.5	20	8	19.5	.021
6901 10 21	10	G1/2	7	24	8	18	.033
6901 12 21	12	G1/2	7	24	10	22.5	.035