


## SMP253MA4390MTR24

Aliases (P101AA392M250V)

SMP253/P101, Film, Metallized Paper, Automotive Safety, 3900 pF, 20%, 250 VAC, 1500 VDC, 100°C, 5045, 6.5mm



Note: '()' correspond to the letters used in the product bulletin

Click here for the 3D model.

Dimensions	
Chip Size	5045
L	12.7mm +/-0.2mm
W	11.5mm +/-0.2mm
Т	6.5mm +/-0.2mm
F	0.5mm NOM

Packaging Specifications	
Packaging	T&R
Packaging Quantity	600

General Information	
Series	SMP253/P101
Dielectric	Metallized Paper
Style	SMD Chip
RoHS	Yes
Termination	Tin
Safety Class	Y2
Qualifications	ENEC, cULus
AEC-Q200	Yes
THB Performance	No
Component Weight	1.6 g

Specifications	
Capacitance	3900 pF
Capacitance Tolerance	20%
Voltage AC	250 VAC
Voltage DC	1500 VDC
Temperature Range	-40/+100°C
Rated Temperature	100°C
Dissipation Factor	1.3% 1kHz
Insulation Resistance	12 GOhms
Max dV/dt	2000 V/us

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.