

EVR 3KW 1-Phase Enclosed Phase Angle Controller c/w Class B Filter

3KW PA CTRL Enclosed X10801

INTRODUCTION

This 3KW 'Mini Stack' is available for single phase, 230V applications. The unit can control loads of up to 13A, with a number of signal control options. The controllers are assembled to suit the final load, operating in phase angle mode. The controller comes complete with BS1362 fuse and an integral heatsink.


APPLICATIONS

Suitable for heaters, ovens, dryers, air curtains, hot plates, heating and ventilation. SCR solid state phase angle power handing gives smooth proportional control of all types of industrial processes, e.g. furnaces, electroplating, controlled rectifiers, transformers etc.

FEATURES

- Wide range of Control Signal Options.
- Enclosed with Status Indication
- Built in Class B Filter
- Phase angle mode of operation with Soft-Start.
- Mains Protection fuse fitted.
- Simple installation.





INSTALLATION

COOLING REQUIREMENTS

Heatsink rating for standard stack assembly is calculated when naturally cooled. If mounted in an enclosure or Cabinet, adequate ventilation and/or forced cooling should be fitted. When thermal trips are fitted we recommend that they are wired in line with the signal, so as to switch off the thyristors in an over temperature situation.

Unusual heating loads such as Molybdenum, Platinum or Tungsten, typically have a 10 to 1 hot to cold resistance ratio and therefore when cold, draw larger currents than normal. Transformers and other inductive loads have surge starting currents and require the correct type of phase angle firing circuit. These and similar types of surge loads, should be indicated, so that appropriate slow start or larger rated units can be correctly supplied for the specific needs.

Note: The unit is factory set for manual control or 0-5Vdc. For4-20mA, a 270R resistor will be required to be fitted across the '+ve' & '0v' terminals and the zero & span adjusters will need recalibrating

Mains voltage	230V ac +10% -6%	Auxiliary Output	5Vdc
Signal Span Minimum	0-5Vdc	Triac Limiting RMS Current	26A
Signal Span Maximum	0-25Vdc	Peak Single Cycle Surge Current	250A
Signal Zero Offset	0-30% of Span	Max. Peak Voltage	600V
Signal Input	0-5VDC/factory default	Current Rating	13A
Manual Potentiometer	5K	Max. Working Temperature	65°C operational
Soft Start Time Constant	1 second fixed	Replacement Fuse	BS1362
Isolation Voltage	2500 Vrms	Storage Temperature	-20°C to +85°C
DIMENSIONS			
DIMENSIONS	W475 × 11405 × D05 × 0	Llaight with Clands	225
Enclosure	W175 x H195 x D65mm	Height with Glands	225mm

FUSING

The unit comes with an integral 13A Mains Protection fuse (BS1362). On initial 'switch' on, some loads may need an increased Factor of Safety (F of S) for Unit and/or Device protection. See SRA Data sheet for further information.

CE MARKING

This product family carries a "CE marking". The 3KW phase angle controller requires a suitable remote filter. For information see recommendation section and contact our sales desk. (See Declaration of Conformity).

RECOMMENDATIONS

Other documents are available on request, which may be appropriate for your application:
CODE IDENTITY DESCRIPTION

X10213 ITA Interaction, uses for phase angle and for burst fire control. X10255 SRA Safety requirements - addressing the Low Voltage Directive (LVD) including: - Thermal data/cooling; "Live" parts warning & Eart requirements; Fusing recommendations.	CODE	IDENTITY	DESCRIPTION
AP02/4 COS UAL Conditions of sale.		SRA	Safety requirements - addressing the Low Voltage Directive (LVD) including: - Thermal data/cooling; "Live" parts warning & Earth requirements; Fusing recommendations.

NOTE It is recommended that installation and maintenance of this equipment should be done with reference to the current edition of the I.E.E. wiring regulations (BS7671) by suitably qualified/trained personnel. The regulations contain important requirements regarding safety of electrical equipment. For International Standards refer to I.E.C/ directive IEC 950.

ORDER CODE State part number: A407802 – 3KW 1.Ph Phase-Angle Controller

Optional extras include: Glands, 270R 1/4 W Resistor, 5k Potentiometer



UNITED AUTOMATION LIMITED

Southport Business Park Wight Moss Way Southport, PR8 4HQ ENGLAND Tel: 0044 (0) 1704 – 516500 Fax: 0044 (0) 1704 – 516501 enquiries@united-automation.com www.united-automation.com

