

PRODUCT-DETAILS

# PAFS16/BL/10M

## PA6 STAND.WEIGHT NC16 10MT BLK



### General Information

Extended Product Type	PAFS16/BL/10M
Product ID	7TCA296000R2169
EAN	5020963004124
Catalog Description	PA6 STAND.WEIGHT NC16 10MT BLK
Long Description	Standard Weight Conduit, Nominal Conduit Size 16mm, NW Conduit Size 13, Fine Conduit Pitch, Outside Diameter 15.8mm, Inside Diameter 11.8mm, Static Bend Radius 35mm, Reel Length 10 Meters, Polyamide (Nylon) 6, Black

### Additional Information

Application	Indoors / Outdoors - Light Industrial, Buildings & Machinery
Product Type	Standard Weight Conduit with Fine Pitch

### Ordering

EAN	5020963004124
UPC	786210258591
Customs Tariff Number	3926909985

### Dimensions

Product Net Depth / Length	10 m
----------------------------	------

---

**Technical**


---

Number of Batteries	0
Color	Black
Material	Polyamide/Nylon 6

---



---

**Environmental**


---

WEEE Category	Product Not in WEEE Scope
---------------	---------------------------

---



---

**Container Information**


---

Package Level 1 Units	1 piece
Package Level 1 Height	0.24 in 6 mm
Package Level 1 Depth / Length	1.65 in 42 mm
Package Level 1 Width	1.65 in 42 mm

---



---

**Certificates and Declarations (Document Number)**


---

Data Sheet, Technical Information	PAFS16/BL/10M
Instructions and Manuals	PAFS16/BL/10M
Declaration of Conformity - CE	9AKK107492A9618
RoHS Information	9AKK107992A8994
RoHS Date	9AKK107992A8994
REACH Declaration	9AKK107992A8994

---



---

**Classifications**


---

ETIM 8	EC001175 - Corrugated plastic hose
UNSPSC	39131706

---



---

**Categories**


---

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

