


PART NO.

CH28-2032LF

REVISIONS								
ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	Α	RELEASED	Asha	26/11/11	Veena	26/11/11		10/12/11



**Specifications:** 

## RoHS Compliant

## Material:

Housing : LCP + 30% GF white colour Contact : Phosphor bronze 0.25 thick

Gold 1 μ plated over Ni 5 μ min.

Current rating : 2 A ac / dc Voltage rating : 500 V ac / dc

 $\begin{array}{ll} \mbox{Contact resistance} & : 30 \ \mbox{m}\Omega \\ \mbox{Insulation resistance} & : 500 \ \mbox{M}\Omega \end{array}$ 

Temperature range : -55°C to +85°C

Humidity : 40°C and 90 - 95% RH for 96 hrs

<b>General Tolerance</b>					
Dimension : 0	±0.3				
0	±0.2				
Angle: ±3° 0	±0.1				

## Part Number Table

Description	Part Number		
Battery Holder, SMT, 20 mm	CH28-2032LF		

www.element14.com www.farnell.com www.newark.com

Important Notice: This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE

PURPOSES ONLY.

TOLERANCES:

DRAWN BY:	DATE:
Asha	26/11/11
CHECKED BY:	DATE:
Veena	26/11/11
APPROVED BY:	DATE:
	10/12/11

DRAWING TITLE:

SIZE DWG NO.

Α

DWG NO. M10002770 ELECT

ELECTRONIC FILE REV
CH28-2032LF\_DWG A

SCALE: NTS U.O.M.: mm

SHEET: 1 OF 1