

Products Low Voltage Products and Systems Connection Devices Terminal Blocks SNK Series

General Information

Extended Product Type:	ZK2.5-D2
Product ID:	1SNK705210R0000
EAN:	3472597052101
Catalog Description:	ZK2.5-D2 PI-Spring clamp Terminal Block - Double deck - Grey
Long Description:	Combine high performance with compact dimensions: - 800 V IEC 600 V UL, - 2 jumper channels and a large input and output marker zone on each deck.

Additional Information

ABB Industrial IT Suite:	Control IT
ATEX Certificate:	1SND162009A1702
Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
Ambient Temperature:	-5 ... +40 °C
BV Certificate:	1SND162013A0203
CB Certificate:	1SND162020A0200
CSA Certificate:	1SND162014A0205
Color:	Grey
Connecting Capacity Main Circuit UL/CSA:	Spring Clamp / Rigid 1x 26 ... 12 AWG Spring Clamp / With Insulated Ferrule 1x 26 ... 14 AWG Spring Clamp / Without Insulated Ferrule 1x 26 ... 14 AWG
Connecting Capacity UL/CSA:	Stranded 12 AWG
Connecting Capacity Main Circuit:	Spring Clamp / Flexible 1x 0.22 ... 2.5 mm ² Spring Clamp / Rigid 1x 0.2 ... 4 mm ² Spring Clamp / With Insulated Ferrule 1x 0.22 ... 2.5 mm ² Spring Clamp / Without Insulated Ferrule 1x 0.22 ... 2.5 mm ² Spring Clamp / With Twin Ferrule 2x 0.22 ... 0.5 mm ²
Connection Type:	PI Spring
Country of Origin:	France (FR)
Customs Tariff Number:	85369010
DNV Certificate:	1SND162023A0200
Data Sheet, Technical Information:	1SNK162037D0201
Declaration of Conformity - CE:	1SND225112U1001
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
EAC Certificate:	1SND161010A1100
EAN:	3472597052101
ETIM 4:	EC000897 - Feed-through terminal block
ETIM 5:	EC000897 - Feed-through terminal block
ETIM 6:	EC000897 - Feed-through terminal block
Environmental Information:	1SND220072E1002
Flammability According to UL94:	V0
Function:	Feed-through
Gauge Type:	A2 / 2.3 mm Dia.
IIT Publishing Status:	Level 0 - Information enabled
Industrial IT Certification Level:	0
Instructions and Manuals:	1SNK160027C0201
Insulation Material:	Polyamide
Invoice Description:	ZK2.5-D2 PI-Spring clamp Terminal Block - Double deck - Grey

Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Minimum Order Quantity:	50 piece
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Number of Connections:	4
Number of Levels:	2
Object Classification Code:	X
Order Multiple:	50 piece
Package Level 1 EAN:	3472597052101
Package Level 1 Gross Weight:	0.61 kg
Package Level 1 Height:	65 mm
Package Level 1 Length:	265 mm
Package Level 1 Units:	50 piece
Package Level 1 Width:	82 mm
Package Level 2 Gross Weight:	4.880 kg
Package Level 2 Height:	200 mm
Package Level 2 Length:	400 mm
Package Level 2 Units:	400 piece
Package Level 2 Width:	300 mm
Package Level 3 Units:	19200 piece
Pollution Degree:	3
Power Loss:	1.6 W
Product Main Type:	ZK2.5-D2
Product Name:	Terminal Block
Product Net Depth:	60.2 mm
Product Net Height:	78.5 mm
Product Net Length:	60.2 mm
Product Net Weight:	11.2 g
Product Net Width:	5.2 mm
Product Packing Type:	Box
Rated Cross-Section:	2.5 mm ²
Rated Current (I _n):	Main Circuit 24 A
Rated Impulse Withstand Voltage (U _{imp}):	8000 V
Rated Short-time Withstand Current (I _{cw}):	for 1 s 300 A
Rated Voltage (U _r):	800 V
Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
RoHS Date:	20110608
RoHS Information:	1SND230535F0201
RoHS Status:	Following EU Directive 2011/65/EC
Selling Unit of Measure:	piece
Short-Circuit Current Rating (SCCR):	100 kA
Spacing:	5.2 mm
Sub-Function:	2 feed-through circuits
Sub-Function 3:	2 feed-through circuits
Sub-Function 4:	2 feed-through
Wire Stripping Length:	11.0 mm
cUL Certificate:	1SND162012A0203
Number of Potentials:	2

