, solder terminal, Plug, 5.5 mm, 2-pole, DC Plug/Socket



See below: Approvals and Compliances

Stock-Check, Detailed request for product

Weblinks

## Description

**Technical Data** 

Insulation Resistance

- Solder :

Diameter Number of Poles

Ratings DC Dielectric Strength

- for cable mounting
- Low Voltage DC Plug and Socket

5.5 mm / 2.1 mm

 $> 100 M\Omega$  @ 500 VDC

<u>2-pole</u> 0.5 A / 12 VDC

500 VDC

- DC Plug: 2-pole , straight

Allowable Operation Tempe-	-20 °C to 70 °C	
rature		
Terminal	solder terminal nickel-plated	
	lockable	
Style	straight	
Lifetime	5000 Insertions	

pdf data sheet, html datasheet, General Product Information, Distributor-

4840.1201


### Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals


SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

#### Compliances

The product complies with following Guide Lines







Cable diameter max. 4.0 mm

# 4840.1201

4840.2202

# All Variants

Product group	Diameter [mm]	Number of Poles	Terminal	Order Number	
DC Plug/Socket	5.5	2-pole	solder terminal	4840.1201	
DC Plug/Socket	5.5	2-pole	solder terminal	4840.1201	

### Most Popular.

Availability for all products can be searched real-time:https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER

 Packaging unit
 100 Pcs

## Mating Outlets/Connectors

Category / Description



DC Plugs / Sockets Overview complete

, PCB terminals, Socket, 5.7 mm, 2-pole, DC Plug/Socket