


**KEMET Part Number: PEH200PJ5100MU2**  
(A351MK103M100A)

PEH200, Aluminum Electrolytic, 10,000 uF, 20%, 100 VDC, -40/+85°C



**General Information**

<b>Supplier:</b>	KEMET
<b>Series:</b>	PEH200
<b>Dielectric:</b>	Aluminum Electrolytic
<b>Description:</b>	Screw Terminal, Aluminum Electrolytic
<b>RoHS:</b>	Yes
<b>AEC-Q200:</b>	No
<b>Notes:</b>	Dimensions D And L Include Slewing. MS (MxS) = M12x16
<b>Shelf Life:</b>	156 Weeks

**Dimensions**

<b>D</b>	51.6mm +/-1mm
<b>L</b>	95.5mm +/-1mm
<b>T</b>	4.9mm NOM
<b>S</b>	22mm
<b>F</b>	15mm +/-0.5mm
<b>DT</b>	15mm NOM
<b>G</b>	13mm NOM
<b>LT</b>	103.4mm +/-1mm
<b>Z</b>	13mm NOM

**Specifications**

<b>Capacitance:</b>	10,000 uF
<b>Capacitance Tolerance:</b>	20%
<b>Voltage DC:</b>	100 VDC
<b>Temperature Range:</b>	-40/+85°C
<b>Rated Temperature:</b>	85°C
<b>Life:</b>	12000 Hrs (Rated Voltage And Ripple Current At 85C)
<b>Resistance:</b>	23 mOhms (100Hz 20C), 19 mOhms (100kHz 20C)
<b>Ripple Current:</b>	15.3 Amps (100Hz 85C), 34.7 Amps (10kHz 50C), 25.6 Amps (10kHz 40C)
<b>Leakage Current:</b>	7000 uA (5min 20°C)
<b>Inductance:</b>	16 nH (ESL)

**Packaging Specifications**

<b>Weight:</b>	240 g
<b>Slewing:</b>	Yes
<b>Packaging:</b>	Bulk, Bag
<b>Packaging Quantity:</b>	20