

HOLDER MATERIAL: NYLON 46, 30% GLASS REINFORCED

FLAMMABILITY RATING:UL94-HB, FILE #E47960

CONTACTS: 301 SPRING TEMPER STAINLESS STEEL,

GOLD FLASH 1u -3u

TEMPERATURE RANGE: -40°C TO +270°C

* VIBRATION TEST: 10-50-10 HZ SWEEPED IN 60 SECONDS X,Y,Z DIRECTION: 1 HOUR EACH DIRECTION

* RESULT: NO DISLODGEMENT OF THE CELL OR DAMAGE

NO DISCONTINUITY OVER 10 MICRO-SECONDS

* SHOCK TEST: HALF SINE WAVE ACCELERATION 150G. 6 MICRO-SECONDS 3 SHOCK PULSES EACH DIRECTION PER AXIS, TOTAL OF 18 PULSES

* RESULT: NO EVIDENCE OF PHYSICAL DAMAGE

* DROP TEST: DROPED FROM 1M HIGH TO CONCRETE FLOOR

* RESULT: NO EVIDENCE OF PHYSICAL DAMAGE

ROHS 2 COMPLIANT

Tolerance (Except as noted)	MPD Memory Protection Devices, Inc 200 Broad Hollow Road, Farmingdale, New York 11735			
decimal			Scale	Drawn By B.S.
±.5 (.020)				Approved By T.B.
Fractional	Title 1/2AA BATTERY HOLDER, PCB MOUNTING			
± .8 (.030)				
Angular	Date	Drawing Number		
± 3°	07/17/17		BH1/2AA-SM	