



Revision level		Revision Record	Changed	Date	Approved	Date
part	drawing					
—	03					



**PRODUCT CODE DESCRIPTION**

T120R\_STNL

COLOR  
(CONSULT FACTORY FOR AVAILABLE COLORS)



Product Code	Cable Range (mm)	Material	Aerospace Spec. Tie SAE A33671	A	B	D	E	G	H
T120R_STNL	5 to 105	PA46	no	1.9 ±0.2	7.6 ±0.2	7.35 ±1.0	12.65 ±1.0	387.0 ±10.0	10.5 ±1.5
T120R_VO	15 to 105	PA66VO	no						
T120R_	5 to 105	PA66	yes						
T120R_UV	5 to 105	PA66UV	yes						
T120R_HS	5 to 105	PA66HS	no						
T120R_HIR	5 to 105	PA66HIR	no						

- BENT TAIL
- TAPERED TIP TAIL
- RADIUSED, SMOOTH EDGES ALONG STRAP
- MAX INSERTION FORCE PER HT TEST METHODS: 27N

**FEATURES**

535N

Minimum Loop Tensile Strength

SEE CHART

Material


Dimension tolerances unless otherwise specified

- .XXXX =
- .XXX =
- .XX = NOTED
- .X = NOTED
- ∠ =

Dimension Units mm

PERFORMANCE SPECIFICATION

ACAD MECH  
2008



Drawn

G.G.G.

11/8/91

Scale

1:1

Computer File Number  
CT\CST\2120003\_03

Approved

K.A.C.

1/16/09

Title

**T120R  
HEAVY DUTY LASHING  
CABLE TIE**

ALL PROPRIETARY RIGHTS IN THE SUBJECT MATTER SHOWN ON THIS DRAWING ARE EXCLUSIVE PROPERTY OF HELLERMANN TYTON

**HellermannTyton**

7930 N. Faulkner Rd.  
Milwaukee, WI 53224  
Ph: (414) 355-1130  
Fx: (414) 362-8338

Drawing-No

**CT2120003CST**

Format  
AH

Sheet 1 of 1