

PIN 8

PANEL CUTOUT



ISS.	AMEND	DATE
1 2 3 4	1st DRAWN ADD M3 VARIANT ADD MIN MAX TEMP UPDATE MATERIALS	04/09/15 16/07/18 30/06/20 25/03/22

VARIANTS

HOLE DETAILS

HOLE Ø3.50 x CSK 82° x Ø5.85


M3 HOLES

Material:

- RJ45 In-Line Coupler: ABS UL94-V0
- RJ45 In-Line Coupler Contact: Phosphor Bronze, 3-50 micro inches gold plating over nickel plate.
- PCB: FR4
- Frame: Nickel plated zinc diecast

Performance:

- T568A & T568B wiring.
- Meet ISO/IEC 11801 and EN50173
- Meet ANSI/TIA/EIA 568B.2
- Rating: 125VAC RMS 1.5A
- Operating Temperatures: Min -10°C Max +70°C



RoHS CO	MPLIANT

TOLERANCE

NO DEC. PLACE ±

1 DEC. PLACE ±

2 DEC. PLACE ±

HOLE ر

ANGLES ±

UNLESS

OTHERWISE STATED DO NOT SCALE

CLIFF

CLIFF

PIN 1

Cliff Electronic Components Ltd.
76 Holmethorpe Avenue, Holmethorpe Industrial Estate,
Redhill, Surrey, RH1 2PF, England, UK
Tel: 01737-771375 Fax: 01737-766012 Website: www.cliffuk.co.uk

26

THE CONTENTS OF THIS DOCUMENT MUST NOT BE COPIED OR DISCLOSED TO A 3rd PARTY WITHOUT WRITTEN PERMISSION OF CLIFF UK. \bigcirc 2015

DIMENSIONS IN MILLIMETERS UNLESS OTHERWISE STATED. WORK TO DIMENSIONS. REMOVE ALL BURRS. IF IN DOUBT ASK.

MATERIAL: See Notes

See Notes FINISH: D.P.J. DRAWN: APPROVED: D.P.J.

-2.8

--2.3

Ø24

2 HOLES: Ø3.5mm CSK 82° x Ø5.85

M3 VERSION HAS M3 THREAD HOLES.

TITLE: FT METAL FTP CAT5e RJ45 SHIELDED

3rd ANGLE PROJECTION:

PART No.

CP30220SM

CP30220SM3

CP30220SM

DRWG. No.

FORM: A4DRWGH