



PRODUCT NUMBER  
SEE TABLE



SECTION A-A



mat'l code	NOTE 3 & 4	surface	tolerance	projection	product family
lit	EDN NO	DATE	ISO 902	ISO 406	HEADERS
E	V13304	JWB 12/19/91	ISO 101	ISO 101	
F	V50975	MDP 8/7/95	ISO 101	ISO 101	
G	V71450	HTB 10/7/97	ISO 101	ISO 101	
H	M05-0089	ERE 4/20/05	ISO 101	ISO 101	
J	M07-0118	AGS 2/19/07	ISO 101	ISO 101	
K	M08-0279	MHT 9/20/08	ISO 101	ISO 101	
sheet	revision	K	K	K	
index	sheet	1	2	3	4

product family: HEADERS

title: VERTICAL STACKING 2-ROW HEADER

sheet no: 68210

sheet 1 of 4 size: A3

type: Product Customer Drawing



PRODUCT NO NOTE 7	TERMINAL PLATING (NOTE 10)
68210-XXX	15u"/0.38u MIN Au OVER 50u"/1.27u MIN Ni.
68210-033	15u"/0.38u MIN Au OVER 50u"/1.27u MIN Ni.
68210-034	15u"/0.38u MIN Au OVER 50u"/1.27u MIN Ni.
68533-XXX	120u"/3.05u MIN 93/7 SnPb OVER 50u"/1.27u MIN Ni.
68563-XXX	30u"/0.76u MIN GXT OVER 50u"/1.27u MIN Ni.
69205-XXX	15u"/0.38u MIN GXT OVER 50u"/1.27u MIN Ni.
69667-XXX	30u"/0.76u MIN Au OVER 50u"/1.27u MIN Ni.
69963-XXX	DUPLEX { CONTACT: 15u"/0.38u Au OVER 50u"/1.27u Ni. TAIL: 100u"/2.54u MIN Sn OVER 50u"/1.27u Ni.
69967-XXX	DUPLEX { CONTACT: 30u"/0.76u Au OVER 50u"/1.27u Ni. TAIL: 100u"/2.54u MIN Sn OVER 50u"/1.27u Ni.
89445-022	15u"/0.38u MIN Au OVER 50u"/1.27u MIN Ni.
90045-XXX	DUPLEX { CONTACT: 15u"/0.38u Au OVER 50u"/1.27u Ni. TAIL: 100u"/2.54u MIN Sn OVER 50u"/1.27u Ni.

mat'l code	NOTE 3 & 4	surface	tolerance	projection	product family
lit	ecm no	dr	date	ISO 9002	ISO 9001
K				linear	linear
				angular	angular
				form	form
				position	position
				feature	feature
				dimension	dimension
				tolerance	tolerance
				material	material
				finish	finish
				texture	texture
				color	color
				weight	weight
				volume	volume
				area	area
				perimeter	perimeter
				radius	radius
				diameter	diameter
				height	height
				width	width
				depth	depth
				thickness	thickness
				length	length
				width	width
				height	height
				radius	radius
				diameter	diameter
				height	height
				width	width
				depth	depth
				thickness	thickness
				length	length
				width	width
				height	height
				radius	radius
				diameter	diameter
				height	height
				width	width
				depth	depth
				thickness	thickness
				length	length
				width	width
				height	height
				radius	radius
				diameter	diameter
				height	height
				width	width
				depth	depth
				thickness	thickness
				length	length
				width	width
				height	height
				radius	radius
				diameter	diameter
				height	height
				width	width
				depth	depth
				thickness	thickness
				length	length
				width	width
				height	height
				radius	radius
				diameter	diameter
				height	height
				width	width
				depth	depth
				thickness	thickness
				length	length
				width	width
				height	height
				radius	radius
				diameter	diameter
				height	height
				width	width
				depth	depth
				thickness	thickness
				length	length
				width	width
				height	height
				radius	radius
				diameter	diameter
				height	height
				width	width
				depth	depth
				thickness	thickness
				length	length
				width	width
				height	height
				radius	radius
				diameter	diameter
				height	height
				width	width
				depth	depth
				thickness	thickness
				length	length
				width	width
				height	height
				radius	radius
				diameter	diameter
				height	height
				width	width
				depth	depth
				thickness	thickness
				length	length
				width	width
				height	height
				radius	radius
				diameter	diameter
				height	height
				width	width
				depth	depth
				thickness	thickness
				length	length
				width	width
				height	height
				radius	radius
				diameter	diameter
				height	height
				width	width
				depth	depth
				thickness	thickness
				length	length
				width	width
				height	height
				radius	radius
				diameter	diameter
				height	height
				width	width
				depth	depth
				thickness	thickness
				length	length
				width	width
				height	height
				radius	radius
				diameter	diameter
				height	height
				width	width
				depth	depth
				thickness	thickness
				length	length
				width	width
				height	height
				radius	radius
				diameter	diameter
				height	height
				width	width
				depth	depth
				thickness	thickness
				length	length
				width	width
				height	height
				radius	radius
				diameter	diameter
				height	height
				width	width
				depth	depth
				thickness	thickness
				length	length
				width	width
				height	height
				radius	radius
				diameter	diameter
				height	height
				width	width
				depth	depth
				thickness	thickness
				length	length
				width	width
				height	height
				radius	radius
				diameter	diameter
				height	height
				width	width
				depth	depth
				thickness	thickness
				length	length
				width	width
				height	height
				radius	radius
				diameter	diameter
				height	height
				width	width
				depth	depth
				thickness	thickness
				length	length
				width	width
				height	height
				radius	radius
				diameter	diameter
				height	height
				width	width
				depth	depth
				thickness	thickness
				length	length
				width	width
				height	height
				radius	radius
				diameter	diameter
				height	height
				width	width
				depth	depth
				thickness	thickness
				length	length
				width	width
				height	height
				radius	radius
				diameter	diameter
				height	height
				width	width
				depth	depth
				thickness	thickness
				length	length
				width	width
				height	height
				radius	radius
				diameter	diameter
				height	height
				width	width
				depth	depth
				thickness	thickness
				length	length
				width	width
				height	height
				radius	radius
				diameter	diameter
				height	height
				width	width
				depth	depth
				thickness	thickness
				length	length
				width	width
				height	height
				radius	radius
				diameter	diameter
				height	height
				width	width
				depth	depth
				thickness	thickness
				length	length
				width	width
				height	height
				radius	radius
				diameter	diameter
				height	height
				width	width
				depth	depth
				thickness	thickness
				length	length
				width	width
				height	height
				radius	radius
				diameter	diameter
				height	height
				width	width
				depth	depth
				thickness	thickness
				length	length
				width	width
				height	height
				radius	radius
				diameter	diameter
				height	height
				width	width
				depth	depth
				thickness	thickness
				length	length
				width	width
				height	height
				radius	radius
				diameter	diameter
				height	height
				width	width
				depth	depth
				thickness	thickness
				length	length
				width	width
				height	height
				radius	radius
				diameter	diameter
				height	height

PRODUCT NO	SIZE	DIM "B"	DIM "C"	DIM "L"	TAIL LENGTH DIM "T"	MATING LENGTH DIM "M"	TOTAL PIN LENGTH DIM "P"
66210-XXX	NOTE 1	NOTE 2	DIM "B" + .130/3.30	DIM "B" + 210/5.33	.103/2.62 MIN .130/3.30 MAX	.275±.010 6.98±0.25	.810/20.57
68210-033	2 x 15	1,400/35.56	1.53/38.9	1.61/40.9	.148±.008 3.76±0.20	.275±.010 6.98±0.25	.840/21.34
68210-034	2 x 25	2,400/60.96	2.53/64.3	2.61/66.3	.148±.008 3.76±0.20	.275±.010 6.98±0.25	.840/21.34
68533-XXX	NOTE 1	NOTE 2	DIM "B" + .130/3.30	DIM "B" + 210/5.33	.103/2.62 MIN .130/3.30 MAX	.275±.010 6.98±0.25	.810/20.57
68583-XXX						.275±.010 6.98±0.25	.810/20.57
69205-XXX						.275±.010 6.98±0.25	.810/20.57
69667-XXX						.275±.010 6.98±0.25	.810/20.57
69963-XXX						.275±.010 6.98±0.25	.810/20.57
69967-XXX	NOTE 1	NOTE 2	DIM "B" + .130/3.30	DIM "B" + 210/5.33		.275±.010 6.98±0.25	.810/20.57
89445-022	2 x 26	2,500/63.50	2.63/66.8	2.71/68.8	.400±.010 10.16±0.25	.275±.010 6.98±0.25	.935/23.75
90045-XXX	NOTE 1	NOTE 2	DIM "B" + .130/3.30	DIM "B" + 210/5.33		.275±.010 6.98±0.25	.810/20.57
69967-XXX	NOTE 1	NOTE 2	DIM "B" + .130/3.30	DIM "B" + 210/5.33		.275±.010 6.98±0.25	.810/20.57
90045-XXX	NOTE 1	NOTE 2	DIM "B" + .130/3.30	DIM "B" + 210/5.33	.103/2.62 MIN .130/3.30 MAX	.275±.010 6.98±0.25	.810/20.57

mat'l code	NOTE 3 & 4	surface	tolerance	projection	product family
lit	ecm no	ISO 902	ISO 901		HEADERS
	dr	distance	linear	INCH/MM	file
	date	between webs	angular	scale 2:1	VERTICAL STACKING 2-ROW HEADER
					.755/19.18 w/o MOUNTING HOLES
					sheet 4 of 4 size
					68210
					Product Customer Drawing
					A3
sheet	revision				
index	sheet				

