



**TEMPERATURE COMPENSATING AND  
TEMPERATURE STABLE TYPES (CLASS I)**





**FEATURES**

- PROVIDES AN ACCURATE, PREDICTABLE LINEAR CAPACITANCE CHANGE WITH VARIATIONS IN OPERATING TEMPERATURE
- NPO TYPES PROVIDE DRIFT FREE PERFORMANCE
- TIGHT TOLERANCES AVAILABLE
- AVAILABLE WITH FORMED LEADS AND ON TAPE

**SPECIFICATIONS**

| Temperature Characteristics                    |                 | NPO  | N750        | SL          | N1500                           |
|--|-----------------|--|-------------|-------------|---------------------------------|
| Operating Temperature Range                    |                 | -30°C ~ +85°C  |             |             |                                 |
| Capacitance Range                              |                 | 0.5 ~ 22pF   | 22 ~ 470pF  | 10 ~ 1000pF | 22 ~ 1000pF                     |
| Standard Tolerance                             |                 | ±5% (J)  |             |             |                                 |
| Capacitance Change Over Temperature Range      |                 | ±1%  | -5% ~ +7.5% | -5% ~ +9%   | -10% ~ +20%                     |
| Q Factor (Min. 1MHz)                           |                 | 1000 (C≥30pF)<br>400+20C (<30pF)                                 |             |             | 500 (C≥30pF)<br>200+10C (<30pF) |
| Insulation Resistance                          |                 | Minimum 10,000 Megohms   |             |             |                                 |
| Temperature Coefficient                        |                 | 0±60ppm  | N750±120ppm | N330±500ppm | N1500±250ppm                    |
| Working Voltage Range                          |                 | 50Vdc ~ 1KVdc  |             |             |                                 |
| Dielectric Withstanding Voltage (Test Voltage) |                 | 2.5 Times Rated Voltage For Not Less Than 1 Second, 50mA Maximum |             |             |                                 |
| Load Life Test @ 85°C<br>1,000 Hours           | Cap. Change     | ±3%  | ±15%        | ±30%        | ±50%                            |
|  | Q Factor (min.) | Shall Conform To Initial Measurements Above                      |             |             |                                 |
| I.R. (min.)                                    |                 | 10,000 Megohms   |             |             |                                 |
| Test Conditions                                |                 | <1,000pF; 1MHz, 1.2Vrms Max., ≥1,000pF; 1KHz, 1.2Vrms Max.       |             |             |                                 |







| Lead Spacing (mm) - S |               |              |                           |                          |
|-----------------------|---------------|--------------|---------------------------|--------------------------|
| Body Diameter         | Standard Bulk | Standard T&R | Optional Bulk mm (inches) | Optional T&R mm (inches) |
| 5 ~ 11                | 6.35 ± 0.8    | 5.0 ± 0.8    | 5.0 ± 0.8 (0.200LS)       | 2.5 ± 0.8 (0.100LS)      |
| ≥12                   | 6.35 ± 0.8    | 5.0 ± 0.8    | 7.5 ± 0.8 (0.295LS)       | 7.5 ± 0.8 (0.295LS)*     |
|                       |               |              | 10.0 ± 0.8 (0.395LS)      | 10.0 ± 0.8 (0.395LS)*    |

\*T&R 7.5mm & 10mm LS not available on 270pF, 330pF & 470pF N750 parts

**Standard**  
500Vdc & Up



**Low Voltage**  
100Vdc & Below




**LEAD DIAMETER**

0.6MM IS STANDARD

**BODY THICKNESS**


2 ~ 4MM DEPENDENT ON CV

**J Style**




(BULK AND TAPED STYLES)

**K Style**




**D Style**



(BULK ONLY)

**E Style**




**STANDARD PRODUCTS AND MAXIMUM DIAMETER (mm) BY T.C. AND VOLTAGE**

| Cap. (pF) | NPO                   |     |     | N750 |    |     | SL  |    |    | N1500 |     |    |
|-----------|-----------------------|-----|-----|------|----|-----|-----|----|----|-------|-----|----|
|           | Working Voltage (Vdc) |     |     |      |    |     |     |    |    |       |     |    |
|           | 50                    | 100 | 500 | 1K   | 50 | 100 | 500 | 1K | 50 | 100   | 500 | 1K |
| 0.5 ~ 9.1 | 6                     | 6   | 6   | -    | -  | -   | -   | -  | -  | -     | -   | -  |
| 10        | 6                     | 6   | 6   | -    | -  | -   | 6   | 6  | 6  | -     | -   | -  |
| 12        | 6                     | 6   | 6   | -    | -  | -   | 6   | 6  | 6  | -     | -   | -  |
| 15        | 6                     | 6   | 6   | -    | -  | -   | 6   | 6  | 6  | -     | -   | -  |
| 18        | 6                     | 6   | -   | -    | -  | -   | 6   | 6  | 6  | -     | -   | -  |
| 22        | 6                     | 6   | 6   | 6    | 6  | 6   | 6   | 6  | 6  | 6     | 6   | 6  |
| 27        | -                     | -   | -   | 6    | 6  | 6   | 6   | 6  | 6  | 6     | 6   | 6  |
| 33        | -                     | -   | -   | 6    | 6  | 7   | 6   | 6  | 6  | 6     | 6   | 6  |
| 39        | -                     | -   | -   | 6    | 6  | 7   | 6   | 6  | 6  | 6     | 6   | 6  |
| 47        | -                     | -   | -   | 6    | 7  | 8   | 6   | 6  | 6  | 6     | 6   | 6  |
| 56        | -                     | -   | -   | 7    | 7  | 8   | 6   | 6  | 6  | 6     | 6   | 6  |
| 68        | -                     | -   | -   | 7    | 7  | 9   | 6   | 6  | 6  | 6     | 6   | 6  |
| 82        | -                     | -   | -   | 7    | 7  | 9   | 6   | 6  | 7  | 6     | 6   | 7  |
| 100       | -                     | -   | -   | 8    | 8  | 10  | 6   | 7  | 7  | 6     | 7   | 7  |
| 120       | -                     | -   | -   | 8    | 8  | 10  | 6   | 7  | 7  | 6     | 7   | 7  |
| 150       | -                     | -   | -   | 9    | 9  | 12  | 6   | 8  | 8  | 6     | 7   | 8  |
| 180       | -                     | -   | -   | 9    | 9  | 14  | 6   | 8  | 8  | 6     | 8   | 8  |
| 220       | -                     | -   | -   | 10   | 10 | 16  | 7   | 9  | 9  | 7     | 9   | 9  |
| 270       | -                     | -   | -   | 12   | 12 | -   | 8   | 9  | 10 | 8     | 9   | 10 |
| 330       | -                     | -   | -   | 14   | 14 | -   | 8   | 12 | 12 | 8     | 12  | 12 |
| 470       | -                     | -   | -   | 16   | 16 | -   | 9   | 14 | 14 | 9     | 14  | 14 |
| 560       | -                     | -   | -   | -    | -  | -   | 10  | 14 | 14 | 10    | 14  | 14 |
| 680       | -                     | -   | -   | -    | -  | -   | 11  | 16 | 16 | 10    | 16  | 16 |
| 750       | -                     | -   | -   | -    | -  | -   | 12  | 16 | 16 | 12    | 16  | 16 |
| 820       | -                     | -   | -   | -    | -  | -   | 14  | 16 | 16 | 12    | 16  | 16 |
| 1000      | -                     | -   | -   | -    | -  | -   | 14  | 16 | 16 | 14    | 16  | 16 |

**NIC RESERVES THE RIGHT TO REQUEST MINIMUM QUANTITIES ON CERTAIN VALUES**


**DIMENSIONS (mm)**



| Symbol    | D max.   | d              | P    | P <sub>0</sub> | P <sub>1</sub> | P <sub>2</sub> | S            | H            | H <sub>0</sub>                              | H <sub>1</sub>  | Dφ   | W    | L         | t    | Δh   |
|-----------|----------|----------------|------|----------------|----------------|----------------|--------------|--------------|---|-----------------|------|------|-----------|------|------|
| Value     | ≤ 12     | 0.6            | 12.7 | 12.7           | 5.1            | 6.35           | 2.5          | 20.0         | Applies to Parts with Crimped Leads<br>16.0 | 32.25 max.      | 4.0  | 18.0 | 11.0 max. | 0.6  | 0.0  |
|           |          |                |      |                | 3.85           |                | 5.0          |              |   | H max. + D max. |      |      |           |      |      |
|           |          |                |      |                | 3.18           |                | 6.35         |              |   |                 |      |      |           |      |      |
|           | >12 ~ 23 | 0.6 or 0.8*    | 25.4 | 8.95           | 12.7           | 7.5            | 9.5          |              |   |                 |      |      |           |      |      |
| Tolerance | ≤ 12     | +0.06<br>-0.05 | ±1.0 | ±0.2           | ±0.7           | ±1.0           | +0.8<br>-0.2 | +1.5<br>-1.0 | ±0.5  | ---             | ±0.2 | ±0.5 | ---       | ±0.3 | ±2.0 |
|           | >12 ~ 23 |                |      |                | ±1.5           | ±1.3           |              |              |   |                 |      |      |           |      |      |

\*Lead diameter dependent on capacitor diameter. Contact NIC for details


**AMMO PACK**



$H \leq 372$  (14.64")  
 $L \leq 377$  (14.84")  
 $W \leq 55$  (2.16")

Acceptable to standard radial type cartridge.

**REEL**



$D \leq 354$  (13.93")  
 $B \geq 21$  (.83") but  
 $\leq 30$  (1.18")  
 $W \leq 55$  (2.16")

Acceptable to standard radial type cartridge with a few extra accessories.

**PART NUMBER SUFFIX FOR OPTIONAL TAPE & REEL OR TAPE & BOX PACKAGING**

**Tape & Reel Straight Lead Options**

- TRF = Tape & Reel with 5mm lead-space
- TR.100LSF = Tape & Reel with 2.0mm lead-space
- TR.250LSF = Tape & Reel with 6.35mm lead-space
- TR.300LSF = Tape & Reel with 7.5mm lead-space
- TR.375LSF = Tape & Reel with 9.5mm lead-space

**Tape & Reel Crimped Lead Options (J = Inward Crimp, K = Outward Crimp)**

- JTRF or KTRF = Tape & Reel with 5mm lead-space
- JTR.250LSF or KTR.250LSF = Tape & Reel with 6.35mm lead-space
- JTR.300LSF or KTR.300LSF = Tape & Reel with 7.5mm lead-space
- JTR.375LSF or KTR.375LSF = Tape & Reel with 9.5mm lead-space

**Tape & Box Straight Lead Options**

- TBF = Tape & Reel with 5mm lead-space
- TB.100LSF = Tape & Reel with 2.0mm lead-space
- TB.250LSF = Tape & Reel with 6.35mm lead-space
- TB.300LSF = Tape & Reel with 7.5mm lead-space
- TB.375LSF = Tape & Reel with 9.5mm lead-space

**Tape & Box Crimped Lead Options (J = Inward Crimp, K = Outward Crimp)**

- JTBF or KTBF = Tape & Reel with 5mm lead-space
- JTB.250LSF or KTB.250LSF = Tape & Reel with 6.35mm lead-space
- JTB.300LSF or KTB.300LSF = Tape & Reel with 7.5mm lead-space
- JTB.375LSF or KTB.375LSF = Tape & Reel with 9.5mm lead-space

Notes:

1. The above lead-space options may not be available in all part diameters. Contact NIC for details.
2. Inward "J style" and outward "K style" may not be available in all part diameters and voltages. Contact NIC for details.