

used for:

Notes




**SPECIFICATIONS**

**Materials**


Insulator: High Temperature Thermoplastic UL94V-0.  
 Contact: Phosphor Bronze  
 30u" Gold Plated over Nickel on mating area  
 Tin Plated over Nickel on Solder tail  
 Metal Board Lock: Zinc Alloy, 150u" Tin Plated  
 Shell: Zinc Alloy, 150u" Nickel Plated

**Electrical**

Insulation Resistance: 2000 Megohms Min.  
 Contact Resistance: 20mΩ MAX. (Initial)  
 Current Rating: 1.5 AMP.  
 Voltage Rating: 250 VAC R.M.S.  
 Dielectric Withstanding Voltage: 500 VAC (R.M.S.)  
 Temperature Range: -55°C ~ 85°C



TYPE:1



THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION DO NOT ALTER CAD DRAWING BY HAND	tolerance unless otherwise specified tolerance shall be as follow Decimal: .xx .xxx      Angles:			finish Dim. in mm		scale: material: SEE NOTES
	2006	date	name	title: DVI 29p female R/A connector with 4-40 UNC thread (RoHS)		
	draw.	April 06	Vincent Ke	drawing no.: AutoCAD 2005		
	appd.	April 06	Kathy Skelhorn	39K1A234		
	norm			drawing no.: AutoCAD 2005		
	d-old			39K1A234		
	a	origin	CONEC®		DIN A3 sheet 1/1	
	rev.	description	date	name	part no.: 33DVIR-29S12R	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[33DVIR-29S12R](#)