



NOTES:

1. METALSHELLS: STEEL; min. 315µm TIN over 40-80µm NICKEL
2. INSULATORS: PBT GF UL 94 V-0, BLACK
3. FRAME: STEEL; NICKEL PLATED
4. FLOAT MOUNTS: COPPER ALLOY; NICKEL PLATED
5. RIVETED INSERTS: COPPER ALLOY; min. 200µm TIN over 80µm NICKEL
6. COLLARS: COPPER ALLOY; min. 200µm TIN over 80µm NICKEL
7. CONNECTOR WILL BE SUPPLIED WITHOUT CONTACTS
8. CONNECTOR IS PART MARKED: DSS4XPXB01X CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND				tolerance		dim. in mm	scale: 2:1 (5:1)		
				date			material: SEE NOTES		
				drawn	16.02.04	Lehmenkühler		title: D-SUB MALE 37pos. CRIMP STYLE with frame and float mount	
				appd.	16.02.04	Mickenbecker			
norm									
4 x b	Ä5047	17.01.2014	Lehm.	dwg no:		DIN-A3			
a	Original			16K1A1100		sh: 1			
rev.	description	date	name			part no: DSS4XPXB01X			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[DSS4XPXXB01X](#)