


Metal Film Resistors, Axial, Industrial Power, Precision, Flameproof



FEATURES

- · High power rating, small size
- Flameproof, high temperature silicone coating
- Special filming and coating processes
- · Excellent high frequency characteristics
- Low noise









Note


^{*} This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

STANDARD ELECTRICAL SPECIFICATIONS						
GLOBAL MODEL	HISTORICAL MODEL	MAXIMUM WORKING VOLTAGE (1) V	POWER RATING P _{70 °C} W	RESISTANCE RANGE Ω	TOLERANCE ± %	TEMPERATURE COEFFICIENT ± ppm/°C
				5 to 150K	0.1, 0.25, 0.5, 1	25
		250	1	5 to 150K	0.1, 0.25, 0.5, 1, 2, 5	50
				1 to 150K	0.5, 1, 2, 5	100
CPF1	CPF-1			0.5 to 150K	1, 2, 5	150
				0.5 to 150K	1	200
				0.2 to 150K	2, 5	200
				0.1 to 150K	2, 5	300
	CPF-2	350	2	5 to 150K	0.1, 0.25, 0.5, 1	25
				5 to 150K	0.1, 0.25, 0.5, 1, 2, 5	50
				1 to 150K	0.5, 1, 2, 5	100
CPF2				0.5 to 150K	1, 2, 5	150
				0.5 to 150K	1	200
				0.2 to 150K	2, 5	200
				0.1 to 150K	2, 5	300
	CPF-3	500	3	8 to 150K	0.1, 0.25, 0.5, 1	25
				8 to 150K	0.1, 0.25, 0.5, 1, 2, 5	50
				1 to 150K	0.5, 1, 2, 5	100
CPF3				1 to 150K	1, 2, 5	150
				1 to 150K	1	200
				0.2 to 150K	2, 5	200
				0.1 to 150K	2, 5	300

Note

⁽¹⁾ Continuous working voltage shall be $\sqrt{P \times R}$ or maximum working voltage, whichever is less





Note

• For additional information on packaging, refer to the Through-Hole Resistor Packaging document (www.vishay.com/doc?31544)


TEMPERATURE COEFFICIENT CODES				
GLOBAL TC CODE	HISTORICAL TC CODE	TEMPERATURE COEFFICIENT		
E	T-9	25 ppm/°C		
Н	T-2	50 ppm/°C		
К	T-1	100 ppm/°C		
L	T-0	150 ppm/°C		
N	T-00	200 ppm/°C		
M	M	300 ppm/°C		

TECHNICAL SPECIFICATIONS				
PARAMETER	UNIT	CPF1	CPF2	CPF3
Rated Dissipation at 70 °C	W	1	2	3
Limiting Element Voltage (1)	V≅	250	350	500
Insulation Voltage	V _{eff}	900	900	900
Thermal Resistance	K/W	85	60	50
Insulation Resistance	Ω		10 ¹⁰	
Category Temperature Range	°C		-65 °C / +230 °C	

Note

(1) Rated voltage $\sqrt{P \times R}$

DIMENSIONS




Note

(1) Lead length for product in bulk pack. For product supplied in tape and reel, the actual lead length would be based on the body size, tape spacing and lead trim


GLOBAL	DIMENSIONS in inches (millimeters)				
MODEL	L	D	L _{1 max.}	d	
CPF1	0.240 ± 0.020 (6.10 ± 0.51)	0.090 ± 0.008 (2.29 ± 0.20)	0.310 (7.87)	0.025 ± 0.002 (0.64 ± 0.05)	
CPF2	0.344 ± 0.031 (8.74 ± 0.79)	0.145 ± 0.015 (3.68 ± 0.38)	0.425 (10.80)	0.032 ± 0.002 (0.81 ± 0.05)	
CPF3		0.180 ± 0.015 (4.57 ± 0.381)		0.032 ± 0.002 (0.81 ± 0.05)	



THERMAL RESISTANCE







Note

 Surface temperatures were taken with an infrared pyrometer in +25 °C still air. Resistors were supported by their leads in test clips at a point 0.500" (12.70 mm) out from the resistor body ends

MATERIAL SPECIFICATIONS			
Element	Proprietary nickel-chrome alloy		
Core	Cleaned high purity ceramic		
Coating	Special high temperature conformal coat		
Termination	Standard lead material is solder-coated Solderable and weldable per MIL-STD-1276, type C		

MECHANICAL SPECIFICATIONS			
Terminal Strength	2 pound pull test		
Solderability	Continuous satisfactory coverage when tested in accordance with MIL-STD-202, method 208		

MARKING

Temperature Coefficient: T00 = 200 ppm, T0 = 150 ppm, T1 = 100 ppm, T2 = 50 ppm, T9 = 25 ppm, M = 300 ppm

CPF1, CPF2, CPF3: (5 lines)

DALE Manufacturer's name CPF-1 Style and size

49.9 kΩ Value

1 % T2 Tolerance and TC 1208 4-digit date code

PERFORMANCE		
TEST	MAX. △R (TYPICAL TEST LOTS)	
Thermal Shock	± 1.0 %	
Short Time Overload	± 0.5 %	
Low Temperature Operation	± 0.5 %	
Moisture Resistance	± 1.5 %	
Resistance to Soldering Heat	± 0.5 %	
Shock	± 0.5 %	
Vibration	± 0.5 %	
Terminal Strength	± 0.5 %	
Dielectric Withstanding Voltage	± 0.5 %	
Life	± 2.0 %	



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

```
CPF151K000JKB14 CPF12R0000FKB14 CPF21K6200FKB14 CPF190K900FEB14 CPF15R0000FHB14
CPF3680R00GKB14 CPF3422R00BHB14 CPF230K000JKR36 CPF2898R00BEB14 CPF210R000JKR36
CPF3150K00FHB14 CPF2150K00FKB14 CPF1150K00FEB14 CPF3270R00GKB14 CPF3626R00DKB14
CPF3200R00BHB14 CPF3470R00GKB14 CPF1470R00GKB14 CPF1249R00BEB14 CPF31K0000BHB14
CPF12R2100FKB14 CPF230R000JKR36 CPF3150R00CHB14 CPF3100R00FKB14 CPF315R000FKB14
CPF111K000FEB14 CPF110K700FKB14 CPF251R100FKB14 CPF151R100FKB14 CPF212R000GKB14
CPF251R000GKB14 CPF310K000BHB14 CPF351K100FKB14 CPF37R5000DKB14 CPF2360R00BEB14
CPF310R000FKR36 CPF210R000FKR36 CPF13R0100FKB14 CPF22K7000FKB14 CPF33R6500FKB14
CPF322R100FKB14 CPF310K000FKR36 CPF222R100FKB14 CPF110R000FEB14 CPF32R2100DKB14
CPF2562R00FKB14 CPF11K2000BEB14 CPF12K0000BHB14 CPF25R0000FKB14 CPF21R0000FKB14
CPF22R0000FKB14 CPF23R0000JKB14 CPF362K000FKB14 CPF38R0600FKB14 CPF110R000BHR36
CPF150R000BHR36 CPF256K000FKR36 CPF1R56000JNB14 CPF13K2400FHB14 CPF211K000FKB14
CPF111K000FKB14 CPF11R0000FKRE5 CPF3100K00BHB14 CPF2100K00BEB14 CPF33R9200DKB14
CPF315K000FKB14 CPF115K000FEB14 CPF124K900FEB14 CPF3620R00FKB14 CPF320R000DKB14
CPF324R000JKB14 CPF1200R00FKR36 CPF12K2100FKB14 CPF1866R00FEB14 CPF310R000DKB14
CPF38R2000FHB14 CPF360K400FKB14 CPF33R0000JKB14 CPF312K600DKB14 CPF25K1100FKB14
CPF315R000JKB14 CPF318R000JKB14 CPF312R000JKB14 CPF382R000JKB14 CPF347R000JKB14
CPF11K2000JKB14 CPF218R200JHB14 CPF3271R00DKB14 CPF3R50000GNB14 CPF3R10000GNB14
CPF3R30000GNB14 CPF1R30000GNB14 CPF31K0000GKB14 CPF142K200FKB14 CPF215R000BEB14
CPF2200R00FKB14 CPF1200R00FKB14 CPF32K4900FKB14 CPF261R900FEB14 CPF22R0000FKRE5
```