



Part Number : [2166201031](#)

Product Description : Squba 3.6 Female-to-Squba 3.6 Female Off-the-Shelf (OTS) Cable Assembly, 3.60mm Pitch, Single Row, 150.00mm Length, Tin (Sn) Plating, 3 Circuits, Black

Series Number : 216620

Status : Active

Product Category : Power and Signal Cable Assemblies



Documents & Resources

Drawings

[Drawing 2166201031_sd.pdf](#)

3D Models and Design Files

[3D Model 2166201031_stp.zip](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	216620
Description	Squba 3.6 Female-to-Squba 3.6 Female Off-the-Shelf (OTS) Cable Assembly, 3.60mm Pitch, Single Row, 150.00mm Length, Tin (Sn) Plating, 3 Circuits, Black
Application	Power, Signal, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Squba-to-Squba
Product Family	Squba Sealed Wire-to-Wire Connectors
Product Name	Squba
Type	Discrete Wire Assembly, Sealed Assembly
UPC	193264746354

Electrical

Current - Maximum per Contact	14.0A
Voltage - Maximum	600V

Physical

Cable Length	150.00mm
Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Matte Tin

Material - Plating Termination	Matte Tin
Material - Resin	Nylon
Net Weight	17.430/g
Number of Rows	1
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	3.60mm
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 11028
Wire Insulation Diameter	1.90mm-2.40mm
Wire Size (AWG)	16

Mates With / Use With

Mates with Part(s)

Description	Part Number
Squba 3.6 Sealed Plug Assembly, 3.60mm Pitch, 2 Circuits, Single Row, Glow-Wire Capable, Black, UL1007/UL1061 Compatible	<u>2077780002</u>

This document was generated on Dec 12, 2023