



CM7V-T1A

Tuning Fork Crystal 32.768 kHz



DIMENSIONS



APPLICATIONS

IoT
 Metering
 Industrial
 Automotive
 Health Care
 Wearables, Portables

DESCRIPTION

The CM7V-T1A is a low frequency SMT Quartz Crystal Unit that incorporates a tuning fork Quartz Crystal Resonator. It operates under vacuum in a hermetically sealed ceramic package with metal lid.

FEATURES

Outstanding hermetic sealing with gold-tin preform.
 High stability and low aging guaranteed by hermetic sealing.
 Available for extended operating temperature range.
 Small size, low profile, lightweight (10.3 mg).
 High shock and vibration resistant.
 100% Pb-free, RoHS-compliant.
 Automotive qualification according to AEC-Q200 available.

ELECTRICAL CHARACTERISTICS AT 25°C

Standard Frequencies 32.768 kHz / 100.000 kHz ¹⁾	F _L	32.768	kHz
Load capacitance ²⁾	C _L	6.0 / 7.0 / 9.0 / 12.5	pF
Frequency tolerance ³⁾	ΔF/F	±20	ppm
	ΔF/F	±100	ppm
Series resistance typ./max.	R _S	50 / 70	kΩ
Motional capacitance typ.	C ₁	3.7	fF
Static capacitance typ.	C ₀	1.2	pF
Drive level max.	P	1.0	μW
Insulation resistance min.	R _i	500	MΩ
Aging first year max.	ΔF/F	±3	ppm
Turnover temperature	T ₀	25 ±5	°C
Frequency vs. temperature	ΔF/F ₀	-0.035 ppm/°C ² (T - T ₀) ² ±10%	

1) Other frequencies on request.
 2) Other load capacitances on request.
 3) Tighter frequency tolerances on request.

STANDARD FREQUENCIES

Frequencies
32.768 kHz / 100.000 kHz
Other frequencies on request

ENVIRONMENTAL CHARACTERISTICS

		Conditions	Max. Dev.
Storage temp. range		-55 to +125°C	
TA Operating temperature range		-40 to +85°C	
TB Extended oper. temp. range		-40 to +125°C	
TC Extended oper. temp. range		-55 to +125°C	
Shock resistance	ΔF/F	5000 g, 0.3 ms, ½ sine	±5 ppm
Vibration resistance	ΔF/F	20 g / 10–2000 Hz	±5 ppm

TERMINATIONS AND PROCESSING

Type	Termination	Processing
CM7V-T1A	For SMT mounting Au flashed pads	IPC/JEDEC J-STD-020C 260°C / 20 - 40 s

ORDERING INFORMATION

	C M 7 V - T 1 A 32.768 kHz 12.5 pF ±20 ppm TA QC
Ceramic package _____	Frequency F_L _____
Metal lid _____	Load capacitance C_L _____
Package size _____	6.0 pF
7 = 3.2 x 1.5 x 0.65 mm	7.0 pF
Tuning fork _____	9.0 pF
SMT Package _____	12.5 pF
Au flashed pads _____	Other C_L on request
Pads on both ends _____	Frequency tolerance _____
	±20 ppm
	±100 ppm
	Tighter freq. tolerances on request
	Temperature range _____
	TA = -40 to +85°C (Standard)
	TB = -40 to +125°C
	TC = -55 to +125°C
	Qualification _____
	QC = Commercial Grade (Standard)
	QA = Automotive Grade AEC-Q200

A unique part number will be generated for each product specification, i.e:	
20xxxx-MG01	1'000 pcs (in 12 mm tape on 7" reel)
20xxxx-MG03	3'000 pcs (in 12 mm tape on 7" reel)
20xxxx-PG14	14'000 pcs (in 12 mm tape on 13" reel)

All specifications subject to change without notice.



Micro Crystal AG
 Muehlestrasse 14
 CH-2540 Grenchen
 Switzerland

Phone +41 32 655 82 82
 Fax +41 32 655 82 83
 sales@microcrystal.com
 www.microcrystal.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Micro Crystal:

[CM7V-T1A-32.768kHz-7pF-20PPM-TA-QC](#) [CM7V-T1A-32.768kHz-7pF-10PPM-TA-QC](#) [CM7V-T1A-32.768k-12.5pF-20PPM-TB-QA](#) [CM7V-T1A-32.768k-9pF-20PPM-TA-QA](#) [CM7V-T1A-32.768k-7pF-100PPM-TB-QA](#) [CM7V-T1A-32.768kHz-12.5pF-20PPM-TA-QC](#) [CM7V-T1A-32.768kHz-6pF-20PPM-TA-QC](#) [CM7V-T1A-32.768kHz-9pF-20PPM-TC-QC](#) [CM7V-T1A-32.768k-9pF-100PPM-TC-QA](#) [CM7V-T1A-32.768kHz-12.5pF-10PPM-TB-QC](#) [CM7V-T1A-32.768kHz-7pF-20PPM-TB-QC](#) [CM7V-T1A-100.000KHZ-9PF-100PPM-TA-QC](#) [CM7V-T1A-32.768k-7pF-20PPM-TB-QA](#) [CM7V-T1A-0.3-32.768kHz-7pF-20PPM-TA-QC](#) [CM7V-T1A-32.768kHz-9pF-20PPM-TA-QC](#) [CM7V-T1A-0.3-32.768kHz-9pF-20PPM-TA-QC](#) [CM7V-T1A-32.768kHz-6pF-10PPM-TA-QC](#) [CM7V-T1A-32.768kHz-12.5pF-20PPM-TC-QC](#) [CM7V-T1A-32.768kHz-9pF-100PPM-TA-QC](#) [CM7V-T1A-32.768kHz-12.5pF-100PPM-TC-QC](#) [CM7V-T1A-32.768k-12.5pF-10PPM-TA-QA](#) [CM7V-T1A-32.768k-12.5pF-20PPM-TC-QA](#) [CM7V-T1A-32.768kHz-12.5pF-100PPM-TA-QC](#) [CM7V-T1A-32.768kHz-12.5pF-10PPM-TA-QA](#) [CM7V-T1A-32.768k-12.5pF-20PPM-TC-QA](#) [CM7V-T1A-32.768kHz-12.5pF-100PPM-TA-QC](#) [CM7V-T1A-32.768k-6pF-20PPM-TB-QA](#) [CM7V-T1A-32.768kHz-12.5pF-20PPM-TB-QC](#) [CM7V-T1A-32.768k-9pF-20PPM-TB-QA](#) [CM7V-T1A-32.768kHz-9pF-20PPM-TB-QC](#) [CM7VT1A-0.3-32.768kHz-12.5pF-20PPM-TA-QC](#) [CM7V-T1A-32.768kHz-12.5pF-100PPM-TB-QC](#) [CM7V-T1A-32.768k-9pF-20PPM-TC-QA](#) [CM7V-T1A-32.768kHz-7pF-100PPM-TA-QC](#) [CM7V-T1A-32.768kHz-12.5pF-10PPM-TA-QC](#) [CM7V-T1A-32.768k-7pF-20PPM-TC-QA](#) [CM7V-T1A-32.768kHz-9pF-10PPM-TB-QC](#) [CM7V-T1A-32.768k-12.5pF-20PPM-TA-QA](#) [CM7V-T1A-32.768kHz-9pF-10PPM-TA-QC](#) [CM7V-T1A-32.768k-7pF-20PPM-TA-QA](#) [CM7V-T1A-32.768k-9pF-20PPM-TA-QA T3](#) [CM7V-T1A-32.768kHz-7pF-20PPM-TB-QA](#) [201563-MG03](#) [CM7V-T1A-32.768kHz-7pF-10PPM-TA-QC T3](#)