

ACCLIMATE"





IP68 SEALED USB & ETHERNET

Mates with:

SPECIFICATIONS

For complete specifications and recommended panel hole layout see www.samtec.com?SCRUS

Insulator Material: PBT

Contact Material:


Phosphor Bronze Wire:

20 AWG (Power) 25 AWG (Signal) 28 AWG (Drain)

O-Ring: Silicone

Operating Temp Range: -20 °C to +75 °C RoHS Compliant:

Note: Some lengths, styles and options are non-standard, non-returnable.



Mates with:

SPECIFICATIONS

For complete specifications and recommended panel hole layout see www.samtec.com?SCRES

Insulator Material: PRT

Contact Material:

Phosphor Bronze Shield Material:

Phosphor Bronze

Wire: 24 AWG

O-Ring:

Silicone

Overmold:


PA66 Current Rating:

3.8 A per pin

(1 pin powered)
Operating Temp Range:
-40 °C to +70 °C

RoHS Compliant:

Some lengths, styles and options are non-standard, non-returnable.



Due to technical progress, all designs, specifications and components are subject to change without notice