

## Sealing cap - PROT-M12 FS - 1560251

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




M12 sealing cap for unoccupied M12 plugs of the sensor/actuator cable, flush-type plugs and I/O devices in the field

### Your advantages

- ✓ Reliable protection of unoccupied slots during transport and use in the field
- ✓ Protected against splash water and dust by the internal seal
- ✓ Good haptics due to ribbing on the cap
- ✓ Easy assembly without tools



### Key Commercial Data

|                        |   |
|------------------------|---|
| Packing unit           | 5 pc  |
| Minimum order quantity | 5 pc  |
| GTIN                   | <br>4 046356 183659 |
| GTIN                   | 4046356183659   |

### Technical data

#### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Ambient temperature (operation) | -40 °C ... 90 °C |
|                                 | -40 °C ... 90 °C |
| Degree of protection            | IP67             |

#### Material

|  |     |
|--|-----|
| Flammability rating according to UL 94 | HB  |
| Material of grip body                  | PE  |
| Sealing material                       | NBR |

#### Environmental Product Compliance

|            |   |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|------------|---|

# Sealing cap - PROT-M12 FS - 1560251


## Technical data

### Environmental Product Compliance

|  |  |
|--|--|
|  | No hazardous substances above threshold values |
|--|--|

## Drawings

Dimensional drawing



## Classifications

### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 23111190 |
| eCl@ss 11.0   | 23111190 |
| eCl@ss 4.0    | 27141200 |
| eCl@ss 4.1    | 27141200 |
| eCl@ss 5.0    | 27149100 |
| eCl@ss 5.1    | 27149100 |
| eCl@ss 6.0    | 27261200 |
| eCl@ss 7.0    | 27440208 |
| eCl@ss 9.0    | 23111190 |

### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC002040 |
| ETIM 4.0 | EC002040 |
| ETIM 6.0 | EC000032 |
| ETIM 7.0 | EC000032 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30212113 |
| UNSPSC 7.0901 | 39121712 |
| UNSPSC 11     | 39121712 |
| UNSPSC 12.01  | 39121712 |
| UNSPSC 13.2   | 39121421 |
| UNSPSC 18.0   | 31261502 |
| UNSPSC 19.0   | 31261502 |
| UNSPSC 20.0   | 31261502 |
| UNSPSC 21.0   | 31261502 |

Phoenix Contact 2022 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>