



# **TO-2106BY-SWG**


# **Surface Mount Device LED**

Part Number	Chip		Lens Color
	Material	Source Color	Lens Color
TO-2106BY-SWG	AlGaInP	Ultra White	Water clear

# **Features**

- IC compatible. Top view type. RoHS compliant.
- Compatible with automatic placement equipment.
- Compatible with infrared and vapor phase reflow soldering process.
- Pack in 8 mm tape on 7" diameter reel.
- Moisture sensitivity Level: level 3.

# **Dimensions**



# 1.00 [D.04"] 1.50 [D.06"] 88 3.50 [D.14"]

Doc No: GS1803025

#### Notes:

- 1. All dimensions are in millimeter.
- 2. Tolerance is ±0.1mm unless individual mark noted.

Taiwan Oasis Technology Co., Ltd.

www.oasistek.com.tw





# Absolute Maximum Rating @ Ta=25°C

Parameter	Maximum Rating	Unit	
Peak Forward Current (1/8 duty f=1kHz)	125	mA	
Power Dissipation	108	mW	
Continuous Forward Current	30	mA	
Reverse Voltage	5	V	
Operating Temperature Range	-40°C to +80°C		
Storage Temperature Range	-40°C to +85°C		
IR Reflow Soldering Profile For Lead Free Soldering	260°C / 10sec		

# Electrical / Optical Characteristic @ Ta=25°C

P.						
Parameter	Symbol	Min.	Тур.	Max.	Unit	Test Condition
Luminous Intensity	lv	630	570	-	mcd	I <sub>F</sub> =20mA
Viewing Angle	2θ <sub>1/2</sub>	-	120	-	deg	I <sub>F</sub> =20mA
Forward Voltage	VF	2.8	-	3.6	V	I <sub>F</sub> =20mA
Reverse Current	I <sub>R</sub>	-	-	10	μΑ	V <sub>R</sub> =5V
Color Temperature	Тс	4945	-	7100	K	I <sub>F</sub> =20mA
Chromaticity Coordinates	Х	0.2927	-	0.3513	-	I <sub>F</sub> =20mA
	Y	0.3100	-	0.4036	-	

<sup>\*</sup> Please refer to CIE 1931 chromaticity diagram.





# **Bin Code List for Reference**

Luminous Intensity	Unit: mcd@20mA		
Bin Code	Min	Max	
Р	400	500	
Q	500	630	
R	630	800	
S	800	1000	
Т	1000		

Tolerance of Luminous Intensity on each bin is  $\pm 15\%$ .

Forward Voltage	Unit: VF@20mA		
Bin Code	Min	Max	
Н	2.8	2.9	
I	2.9	3.0	
J	3.0	3.1	
К	3.1	3.2	
L	3.2	3.3	
M	3.3	3.4	
N	3.4	3.5	
0	3.5	3.6	

Tolerance of Forward Voltage on each bin is ±0.1V.






# **Color Bins**

C5 -	Х	0.3060	0.3028	0.3156	0.3172
CS	Υ	0.3100	0.3239	0.3418	0.3257
C6 -	Х	0.3028	0.2997	0.3139	0.3156
	Υ	0.3239	0.3379	0.3578	0.3418
C8	Х	0.3172	0.3155	0.3272	0.3276
C8	Υ	0.3257	0.3418	0.3581	0.3402
60	Х	0.3156	0.3139	0.3269	0.3272
C9	Υ	0.3418	0.3578	0.3760	0.3581
D2 -	Х	0.3276	0.3272	0.3365	0.3360
	Υ	0.3402	0.3581	0.3711	0.3519
D3	Х	0.3272	0.3269	0.3371	0.3365
D3	Υ	0.3581	0.3760	0.3903	0.3711
D6	Х	0.3360	0.3365	0.3490	0.3468
	Υ	0.3519	0.3711	0.3839	0.3641
D7	Х	0.3365	0.3371	0.3513	0.3490
	Υ	0.3711	0.3903	0.4036	0.3839













# **Optical characteristic curves**

Relative Intensity vs. Wavelength










## **Reflow Profile**

#### ■ Reflow Temp/Time



#### Notes:


- 1.We recommend the reflow temperature 245°C ( $\pm 5$ °C).the maximum soldering temperature should be limited to 260°C.
- 2.Don't cause stress to the epoxy resin while it is exposed to high temperature.
- 3. Number of reflow process shall be 2 times or less.

#### ■ Soldering iron

Basic spec is  $\leq$  5sec when 260  $^{\circ}$ C. If temperature is higher, time should be shorter (+10  $^{\circ}$ C  $\rightarrow$  -1sec ). Power dissipation of iron should be smaller than 20W, and temperatures should be controllable . Surface temperature of the device should be under 230  $^{\circ}$ C .

## ■ Rework

- 1.Customer must finish rework within 5 sec under 260°C.
- 2. The head of iron can not touch copper foil
- 3.Twin-head type is preferred.




■ Avoid rubbing or scraping the resin by any object, during high temperature, for example reflow solder etc.





# 2106 SMD Chip LED Lamps Packaging Specifications




Taiwan Oasis Technology Co., Ltd.

www.oasistek.com.tw







Taiwan Oasis Technology Co., Ltd.

www.oasistek.com.tw





# **Reliability Test Items and Condition**

Item	Condition	Time
Thermal Shock	-30°C * 30mins ~ 80°C * 30mins	100 cycles
Temperature Humidity Storage	Ta= 65°C, RH= 90%	500h
High Temperature Storage	Ta= 80°C	500h
Low Temperature Storage	Ta= -30°C	500h
DC Operating Life	Ta= 25°C, 20mA	1000h
Resistance to Soldering Heat IR-Reflow Normal Process	Refer to recommended profile	1 time
Resistance to Soldering Heat IR-Reflow Pb Free Process	Refer to recommended profile	1 time

## **Cautions**

The LED's are devices which are materialized by combining blue LED's and special phosphors. Consequently the color of the LED's is changed a little by an operating current. Care should be taken after due consideration when using LED's.

#### (1) Moisture Proof Package:

When moisture is absorbed into the SMT package it may vaporize and expand during soldering. There is a possibility that this can cause exfoliation of the contacts and damage to the optical characteristics of the LED's. For this reason, the moisture proof package is used to keep moisture to a minimum in the package.

#### (2) Storage Conditions

Before opening the package:

The LED's should be kept at 30°C or less and 60%RH or less. The LED's should be used with in a year. When storing the LED's. Moisture proof packaging with absorbent material (silica gel) is recommended. After opening the package:

The LED's should be kept at 30°C or less and 50%RH or less. The LED's should be soldered within 168 hours (7days) after opening the package. If unused LED's remain, they should be stored in moisture proof packages, such as sealed containers with packages of moisture absorbent material (silica gel). It is also recommended to return the LED's to the original moisture proof bag and to reseal the moisture proof bag again. If the moisture absorbent material (silica gel) has faded away or the LED's have exceeded the storage time, baking treatment should be performed using the following conditions. Baking treatment: more than 48 hours at 65±5°C Oasistek LED electrode and lead free are comprised of a silver plated copper alloy .The silver surface may be affected by environments which contain corrosive gases and so on. Please Avoid conditions which may cause the LED to corrode, tarnish or discolor. This corrosion or discoloration might lower solderability or might affect on optical characteristics. Please avoid rapid transitions in ambient temperature, especially in high humidity environments where condensation can occur.

Taiwan Oasis Technology Co., Ltd.

www.oasistek.com.tw

Doc No: GS1803025

REV.: A-1 Prepared by XY Xia(10053) Released Date: 2018/03/27 Notes: Above specification may be changed without notice.





#### (3) Heat Generation

Thermal design of the end product is of paramount importance. Please consider the heat generation of the LED when making the system design. The coefficient of temperature increase per input electric power is affected by the thermal resistance of the circuit board and density of LED placement on the board, as well as other components. It is necessary to avoid intense heat generation and operate within the maximum ratings given in this specification. The operating current should be decided after considering the ambient maximum temperature of LED's.

### (4) Cleaning

It is recommended that isopropyl alcohol be used as a solvent for cleaning the LED 's. when using other solvents, it should be confirmed beforehand whether the solvents will dissolve the package and the resin or not. Freon solvents should not be used to clean the LED's because of worldwide regulations. Do not clean the LED's by the ultrasonic. When it is absolutely necessary, the influence of ultrasonic cleaning on the LED's depends on factors such as ultrasonic power and the assembled condition. Before cleaning, a pre-test should be done to confirm whether any damage to the LED's will occur °C.

#### (5) Static Electricity

Static electricity or surge voltage damages the LED's. It is recommended that a wrist band or an anti-electrostatic glove be used when handling the LED's. All devices, equipment and machinery must be properly grounded. It is recommended that measures be taken against surge voltage to the equipment that mounts the LED's. When inspecting the final products in which LED's were assembled, it is recommended to check. Whether the assembled LED's are damaged by static electricity or not, it is easy to find static-damaged LED's by a light –on test or a VF test at a lower current (below 1mA is recommended). Damaged LED's will show some unusual characteristics such as the leak current remarkably increases, the forward voltage becomes lower, or the LED's do not light at the low current. Criteria (Vf>2.0V at If=0.5mA)

## (6) Others

Care must be taken to ensure that the reverse voltage will not exceed the absolute maximum rating when using the LED's with matrix drive. The LED light output is strong enough to injure human eyes. Precautions must be taken to prevent looking directly at the LED's with unaided eyes for more than a few seconds. Flashing lights have been known to cause discomfort in people, you can prevent this by taking precautions during use. Also, people should be cautions when using equipment that has had LED's incorporated into it. The LED's described in this brochure are intended to be used for ordinary electronic equipment (such as office equipment, communications equipment, measurement instruments and household appliances) Consult Oasistek's sales staff in advance for information on the applications in which exceptional quality and reliability are required, particularly when the failure or malfunction of the LED's may directly jeopardize life or health (such as for airplanes, aerospace, submersible repeaters, nuclear reactor control systems, automobile, traffic control equipment, life support systems and safety devices). User shall not reverse engineer by disassembling or analysis of the LED's without having prior written consent from Oasistek when defective LED's are found, the User shall inform Oasistek directly before disassembling or analysis. The formal specifications must be exchanged and signed by both parties before large volume purchase begins. The appearance and specifications of the product may be modified for improvement without notice.

Taiwan Oasis Technology Co., Ltd.

www.oasistek.com.tw