


Coaxial Cable Connector 16_MCX-50-2-11/111_N_-1

Description

Right angle cable plug

Interface standards

IEC 60169-36_CECC 22220



Technical Data

Electrical Data

| | |
|--------------------------|-------------|
| Impedance | 50 Ω |
| Interface frequency max. | 6 GHz |

Mechanical Data

| | |
|----------------|-----------|
| Centre contact | soldered |
| Outer contact | crimped |
| Weight | 0.0011 kg |

Environmental Data

| | |
|--|------------------|
| Operating temperature | -65 °C to 165 °C |
| 2011/65/EU (RoHS - including 2015/863 and 2017/2102) | compliant |

Material Data

| Piece Parts | Material | Surface Plating |
|----------------|------------------------|--|
| Centre contact | Brass | Gold Plating (Nickel underplated) |
| Outer contact | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Body | Brass | SUCOPRO Plating |
| Insulator | PFA / PTFE | |
| Crimp ferrule | Copper | Gold Plating (without Nickel underplating) |

Related Documents

| | |
|----------------------|----------------|
| Outline drawing | DOU-00006014 |
| Catalogue drawing | DOU-00006016 |
| Assembly instruction | DOC-0000179229 |

Ordering Information

| | |
|----------------------|-------------------------|
| Bulk 100 pcs package | 16_MCX-50-2-11/111_NH-1 |
|----------------------|-------------------------|

Additional Information

| | |
|-----------------|--|
| Suitable cables | K_02252_D, ENVIROFLEX_316_D, G_02232_D |
|-----------------|--|

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[16_MCX-50-2-11/111_NH-1](#)