

Non-contact voltage tester

testo 745

Filter for high-frequency interference signals

Adjustable sensitivity

Visual and acoustic signal

Waterproof and dustproof according to IP 67

Measuring point illumination





The testo 745 non-contact voltage tester with a voltage range of up to 1,000 V AC is particularly well-suited to fast initial checking of any suspected fault sources. When the presence of alternating current is determined, the testo 745 gives a warning via a clear visual and acoustic signal.

In order to increase reliability, the voltage tester has a filter for high-frequency interference signals and is also waterproof and dustproof according to IP 67.



Technical data/accessories

testo 745 testo 745, non-contact voltage tester including batteries Order no. 0590 7450

Technical data

| Voltage testing | 12 to 1,000 V AC |
|------------------------------|---------------------------------|
| Measuring point illumination | ✓ |
| Measurement category | CAT IV 600 V CAT III 1,000 V |
| Protection class | IP 67 |
| Operating temperature | -10 to +50 °C |
| Storage temperature | -15 to +60 °C |
| Dimensions | 155 x 25 x 23 mm (L x W x H) |
| Weight | 63 g |
| Warranty | 2 years |
| Authorizations | CSA, CE |
| Standards | EN 61326-1, EN 61010-1 |

| Accessories | Order no. |
|--|-----------|
| ISO calibration certificate voltage tester | 0520 0750 |
| DAkkS calibration certificate voltage tester | 0520 0751 |