


# angle gripper DHWS-32-A

Part number: 1310182

FESTO



## Data sheet

Feature	Value
Size	32
Max. replacement accuracy	$\leq 0.2$ mm
Max. opening angle	40 deg
Rotationally symmetrical	$\leq 0.2$ mm
Repetition accuracy, gripper	$\leq 0.04$ mm
Number of gripper fingers	2
Assembly position	Any
Mode of operation	double-acting
Gripper function	Angle
Design structure	Lever
Position detection	For proximity sensor
Operating pressure	2 ... 8 bar
Max. operating frequency of gripper	$\leq 3$ Hz
Min. opening time at 6 bar	46 ms
Min. closing time at 6 bar	77 ms
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1 - Low corrosion stress
Ambient temperature	5 ... 60 °C
Total gripping torque at 6 bar, opening	810 Ncm
Total gripping torque at 6 bar, closing	746 Ncm
Mass moment of inertia	1.6 kgcm <sup>2</sup>
Max. force on gripper jaw Fz static	120 N
Max. torque at gripper Mx static	6 Nm
Max. torque at gripper My static	6 Nm
Max. torque at gripper Mz static	6 Nm
Product weight	452 g
Mounting type	Optional Internal thread and centring sleeve With through-hole and centring sleeve
Pneumatic connection	G1/8
Materials note	Conforms to RoHS
Material cover cap	PA
Material housing	Wrought Aluminium alloy Hard anodised
Material gripper jaws	High alloy steel