

1218124-2 ✓ ACTIVE

AMPLIMITE

TE Internal #: 1218124-2

Box Mount D-Sub Connectors, Plug, Round Termination Post & Tail  
Diameter .76 mm [.03 in], Cable-to-Board, 15 Position, 2 Connector  
Shell Size, Pin

[View on TE.com >](#)



Connectors > D-Shaped Connectors > D-Sub Connectors > Box Mount D-Sub Connectors



Connector & Housing Type: **Plug**

Round Termination Post & Tail Diameter: **.76 mm [.03 in]**

Connector System: **Cable-to-Board**

Number of Positions: **15**

Power/Signal/Coax Combination: **No**

**Features**

**Product Type Features**

Connector & Housing Type	Plug
Connector System	Cable-to-Board
Connector Shell Size	2
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

**Configuration Features**

PCB Mount Orientation	Vertical
Number of Positions	15
Power/Signal/Coax Combination	No

**Body Features**

Rear Shell Material	Steel
Rear Shell Plating Material	Cadmium
Front Shell Plating Material	Cadmium
Front Shell Material	Steel
D-Sub Connector Insert Arrangement	MS18274-1

**Contact Features**

Contact Mating Area Plating Material	Gold
Contact Base Material	Brass



Contact Type	Pin
Contact Size	Size 20
Contact Current Rating (Max)	5 A

#### Termination Features

Termination Post & Tail Length	3.95 mm[.156 in]
Round Termination Post & Tail Diameter	.76 mm[.03 in]

#### Mechanical Attachment

Mounting Hole Diameter	3.05 mm[.12 in]
Mating Alignment	Without

#### Housing Features

Centerline (Pitch)	2.77 mm[.109 in]
--------------------	------------------

#### Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

#### Operation/Application

Circuit Application	Signal
---------------------	--------

#### Packaging Features

Packaging Method	Package
------------------	---------

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Cd (2%) Pb (3.7%) <b>Article Safe Usage Statements:</b> Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Wave solder capable to 265°C

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


## Customers Also Bought



TE Part #1-5747150-4  
09 RCPT SP/FMS SCRLK



TE Part #1473150-4  
SEMI-HARD TRAY ASSY DDR2  
SODIMM 5.2H RV



TE Part #215297-8  
8P HV100 REC CON. TE, 7.0MM



TE Part #443975-4  
AMPLIMITE,RCPT ASY,POSTD,109,4



TE Part #1218124-4  
37 POS,ASSY,PLUG,LOW PROF,109



TE Part #1218124-1  
9 POS,ASSY,PLUG,LOW PROF,109



TE Part #443975-2  
AMPLIMITE,RCPT ASY,POSTD,109,2



TE Part #443975-5  
AMPLIMITE,RCPT ASY,POSTD,109,5



TE Part #1218440-4  
AMPLIMITE,ASY,PLUG,RT ANG,109,4

## Documents

### Product Drawings

15 POS,ASSY,PLUG,LOW PROF,109

English

### CAD Files

Customer View Model



[ENG\\_CVM\\_1218124-2\\_E.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_1218124-2\\_E.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_1218124-2\\_E.2d\\_dxf.zip](#)

English

[3D PDF](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

[Agency Approvals](#)

[UL Report](#)

English