



- NOTES:**
1. IP67 RATED WHEN PROPERLY ASSEMBLED.
 2. PANEL THICKNESS MAX OF 0.169 [4.30].
 3. ALL PARTS SHIPPED ASSEMBLED.
 4. MATERIALS:
HOUSING AND HEX NUT - NICKEL PLATED, ZINC ALLOY
SPRING WASHER - STAINLESS STEEL
GASKET - SILICONE, BLACK
 5. THIS PRODUCT IS RoHS COMPLIANT.

REV	ECO NUMBER	DATE	BY	APVD
A	28311	08/24/20	PC	TJK
REVISIONS				

UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS IN INCHES [mm]
 - TWO PLACE DECIMALS ±0.02 [0.5]
 - THREE PLACE DECIMALS ±0.005 [0.13]

DO NOT SCALE DRAWING

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.											
SIZE	WIDTH	MULT	LBS/M	TEMPER							
FINISH					MATERIAL						
SPEC No.					SPEC No.						
FIRST USED ON				SCALE 2:1							
DATE DRAWN	BY	CHKD	APVD	Switchcraft®							
7/7/20	FM	FM	TJK	SHEET 1 OF 1							
				7/7/20				7/30/20			
NAME RJ45 CAT6 PANEL MOUNT, SHIELDED JACK, PC TERMINALS								PART No.		REV	
								ENDP6SPC		A	

CUSTOMER DRAWING