


- Rugged, compact metal case
- Screw terminal adaptor available for easy connection
- EN 50155 approval for railway applications
- Ultra wide 4:1 input voltage range
- Full load operation up to +60°C with convection cooling
- Undervoltage lockout
- Reverse input voltage protection
- Input protection filter
- 3-year product warranty



The TEP-75WI Series is a family of isolated high performance DC/DC converter modules with ultra-wide 4:1 input voltage ranges which come in a rugged, sealed metal case. These converters are suitable for a wide range of applications. For easy connection there is also an unique adaptor available with screw terminals. A very high efficiency allows an operating temperature up to +60°C with natural convection cooling without power derating. Further features include output voltage trimming, Remote On/Off and under voltage lockout. The very wide input voltage range and reverse input voltage protection make these converters also an interesting solution for battery operated systems.

Models				
Order Code	Input Voltage Range	Output Voltage nom.	Output Current max.	Efficiency typ.
TEP 75-2411WI	9 - 36 VDC (24 VDC nom.)	5 VDC	15'000 mA	88 %
TEP 75-2412WI		12 VDC	6'300 mA	88 %
TEP 75-2413WI		15 VDC	5'000 mA	88 %
TEP 75-2415WI		24 VDC	3'200 mA	87 %
TEP 75-2416WI		28 VDC	2'700 mA	87 %
TEP 75-2418WI		48 VDC	1'600 mA	87 %
TEP 75-4811WI	18 - 75 VDC (48 VDC nom.)	5 VDC	15'000 mA	90 %
TEP 75-4812WI		12 VDC	6'300 mA	90 %
TEP 75-4813WI		15 VDC	5'000 mA	89 %
TEP 75-4815WI		24 VDC	3'200 mA	88 %
TEP 75-4816WI		28 VDC	2'700 mA	88 %
TEP 75-4818WI		48 VDC	1'600 mA	87 %
TEP 75-7211WI	43 - 160 VDC (110 VDC nom.)	5 VDC	15'000 mA	91 %
TEP 75-7212WI		12 VDC	6'300 mA	91 %
TEP 75-7213WI		15 VDC	5'000 mA	91 %
TEP 75-7215WI		24 VDC	3'200 mA	90 %
TEP 75-7216WI		28 VDC	2'700 mA	90 %
TEP 75-7218WI		48 VDC	1'600 mA	90 %

Options

Suffix -CM	- Chassis mount models without filter: www.tracopower.com/products/tep75wicm.pdf
Suffix -CMF	- Chassis mount models with filter to meet EN 55032 class A: www.tracopower.com/products/tep75wicmf.pdf
TEP-HS1	- Optional Heat Sink: www.tracopower.com/products/tep-hs1.pdf
on demand (backorder with MOQ non stocking item)	<ul style="list-style-type: none"> - Optional model with 3.3 VDC / 20'000 mA Output and 9 - 36 VDC Input - Optional model with 3.3 VDC / 20'000 mA Output and 18 - 75 VDC Input - Optional model with 3.3 VDC / 20'000 mA Output and 43 - 160 VDC Input - Inverse Remote On/Off function (passive = off)

Input Specifications

Input Current	- At no load	110 Vin models: 10 mA typ. 24 Vin models: 85 mA typ. (3.3 Vout model) 120 mA typ. (5 Vout model) 185 mA typ. (12 Vout model) 185 mA typ. (15 Vout model) 85 mA typ. (24 Vout model) 85 mA typ. (28 Vout model) 85 mA typ. (48 Vout model)
	- At full load	48 Vin models: 60 mA typ. (3.3 Vout model) 60 mA typ. (5 Vout model) 90 mA typ. (12 Vout model) 50 mA typ. (15 Vout model) 50 mA typ. (24 Vout model) 50 mA typ. (28 Vout model) 50 mA typ. (48 Vout model)
Surge Voltage		24 Vin models: 50 VDC max. (1 s max.)
		48 Vin models: 100 VDC max. (1 s max.)
		110 Vin models: 185 VDC max. (1 s max.)
Under Voltage Lockout		24 Vin models: 7.3 VDC min. / 7.7 VDC typ. / 8.1 VDC max.
		48 Vin models: 15.5 VDC min. / 16 VDC typ. / 16.3 VDC max.
		110 Vin models: 33 VDC min. / 34.5 VDC typ. / 36 VDC max.
Recommended Input Fuse		24 Vin models: 15'000 mA (fast acting)
		48 Vin models: 8'000 mA (fast acting)
		110 Vin models: 3'150 mA (slow blow) (The need of an external fuse has to be assessed in the final application.)
Reverse Voltage Protection		Parallel diode (24 Vin and 48 Vin models only) (external input fuse required)
Input Filter		Internal Pi-Type (For 24 Vin models an input capacitor 4.7 μ F X7R or 68 μ F Nippon chemi-con KY is recommended for a reliable supply.)

Output Specifications

Output Voltage Adjustment		-20% to +10% (By external trim resistor)
	See application note:	www.tracopower.com/overview/tep75wi Output power must not exceed rated power!
Voltage Set Accuracy		$\pm 1\%$ max.
Regulation	- Input Variation (Vmin - Vmax)	0.1% max.
	- Load Variation (0 - 100%)	0.1% max.

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Ripple and Noise (20 MHz Bandwidth)	3.3 Vout models:	100 mVp-p max. (w/ 4.7 μ F)
	5 Vout models:	100 mVp-p max. (w/ 4.7 μ F)
	12 Vout models:	125 mVp-p max. (w/ 4.7 μ F)
	15 Vout models:	125 mVp-p max. (w/ 4.7 μ F)
	24 Vout models:	250 mVp-p max. (w/ 4.7 μ F)
	28 Vout models:	250 mVp-p max. (w/ 4.7 μ F)
	48 Vout models:	350 mVp-p max. (w/ 2.2 μ F)
Capacitive Load	3.3 Vout models:	60'600 μ F max.
	5 Vout models:	30'000 μ F max.
	12 Vout models:	5'250 μ F max.
	15 Vout models:	3'330 μ F max.
	24 Vout models:	1'330 μ F max.
	28 Vout models:	960 μ F max.
	48 Vout models:	330 μ F max.
Minimum Load	Not required	
Temperature Coefficient	± 0.02 %/K max.	
Start-up Time	60 ms typ. (110 Vin models) 25 ms typ. (other models)	
Short Circuit Protection	Continuous, Automatic recovery	
Output Current Limitation	150% typ. of Iout max. (110 Vin models) 110 - 140% (other models)	
Overvoltage Protection	115 - 130% of Vout nom.	
Transient Response	- Response Time	200 μ s typ. / 250 μ s max. (25% Load Step)

Safety Specifications

Safety Standards	- IT / Multimedia Equipment	EN 60950-1 EN 62368-1 IEC 60950-1 IEC 62368-1 UL 60950-1 UL 62368-1
	- Railway Applications - Certification Documents	EN 50155 www.tracopower.com/overview/tep75wi

EMC Specifications

EMI Emissions	- Conducted Emissions	EN 55011 class B (with external filter) EN 55032 class B (with external filter)
	- Radiated Emissions	EN 55011 class B (with external filter) EN 55032 class B (with external filter)
External filter proposal:		www.tracopower.com/overview/tep75wi
EMS Immunity	- Electrostatic Discharge	EN 50155 (Railway Applications) EN 55024 (IT Equipment) Air: EN 61000-4-2, ± 8 kV, perf. criteria A Contact: EN 61000-4-2, ± 6 kV, perf. criteria A EN 61000-4-3, 20 V/m, perf. criteria A EN 61000-4-4, ± 2 kV, perf. criteria A EN 61000-4-5, ± 2 kV, perf. criteria A
	- RF Electromagnetic Field	Ext. input component: 24 & 48 Vin models: 2 x KY 220 μ F 110 Vin models: 2 x KY 150 μ F
	- EFT (Burst) / Surge	EN 61000-4-6, 10 Vrms, perf. criteria A
	- Conducted RF Disturbances	Continuous: EN 61000-4-8, 100 A/m, perf. criteria A
	- PF Magnetic Field	1 s: EN 61000-4-8, 1000 A/m, perf. criteria A

General Specifications

Relative Humidity	95% max. (non condensing)
-------------------	---------------------------

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Temperature Ranges	- Operating Temperature - Case Temperature - Storage Temperature	-40°C to +75°C +105°C max. -55°C to +125°C
Power Derating	- High Temperature	See application note: www.tracopower.com/overview/tep75wi
Over Temperature Protection Switch Off	- Protection Mode - Measurement Point	115°C typ. (Automatic recovery at 105°C typ.) Base-Plate
Cooling System		Natural convection (20 LFM)
Sense Function		10% max. of Vout nom.
Remote Control	- Voltage Controlled Remote - Off Idle Input Current	On: 3.0 to 12 VDC or open circuit Off: 0 to 1.2 VDC or short circuit Refers to 'Remote' and '-Vin' Pin 3 mA typ. (Optional models with inverse logic available)
Altitude During Operation		2'000 m max.
Switching Frequency		270 - 330 kHz (PWM) 300 kHz typ. (PWM)
Insulation System		Reinforced Insulation (110 Vin models) Basic Insulation (other models)
Working Voltage (rated)		157 VAC (110 Vin models) 125 VAC (other input models)
Isolation Test Voltage	- Input to Output, 60 s - Input to Case, 60 s - Output to Case, 60 s	3'000 VAC (110 Vin models) 3'000 VDC (other models) 1'500 VAC (110 Vin models) 1'600 VDC (other models) 1'500 VAC (110 Vin models) 1'600 VDC (other models)
Isolation Resistance	- Input to Output, 500 VDC	1'000 MΩ min.
Isolation Capacitance	- Input to Output, 100 kHz, 1 V	2'500 pF max.
Reliability	- Calculated MTBF	336'000 h (MIL-HDBK-217F, ground benign)
Washing Process		Allowed (hermetical product) See Cleaning Guideline: www.tracopower.com/info/cleaning.pdf
Environment	- Vibration - Mechanical Shock - Thermal Shock	MIL-STD-810F EN 61373 MIL-STD-810F EN 61373 MIL-STD-810F EN 50155
Housing Material		Alu base-plate w. metal case (24 and 48 Vin models) Alu base-plate w. plastic case (110 Vin models)
Base Material		Non-conductive FR4 (UL 94 V-0 rated) (24 and 48 Vin models only)
Potting Material		Silicone (UL 94 V-0 rated)
Pin Material		Copper
Pin Foundation Plating		Nickel (2 - 3 μm)
Pin Surface Plating		Tin (3 - 5 μm), matte
Housing Type		Metal Case (24 and 48 Vin models) Plastic Case (110 Vin models)
Mounting Type		PCB Mount
Connection Type		THD (Through-Hole Device)
Footprint Type		Half-Brick
Weight		97 g
Thermal Impedance		6.7 K/W 4.7 K/W (with Heat Sink)

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Environmental Compliance - REACH Declaration

www.tracopower.com/info/reach-declaration.pdf

REACH SVHC list compliant

REACH Annex XVII compliant

www.tracopower.com/info/rohs-declaration.pdf

- RoHS Declaration

Exemptions: 7a, 7c-I

(RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule).
The SCIP number is provided on request.)

- Flammability (EN 45545-2)


www.tracopower.com/info/en45545-declaration.pdf

Supporting Documents

Overview Link (for additional Documents)

www.tracopower.com/overview/tep75wi

Outline Dimensions



Dimensions in mm (inch)
Tolerances x.xx±0.5 (x.xx±0.02)
Tolerances x.xx±0.25 (x.xxx±0.01)
Pin pitch tolerances ±0.25 (±0.01)
Pin dimension tolerances ±0.1 (±0.004)

Pin diameter pin 5 & 9: 2.0 (0.08)
Pin diameter other pins: 1.0 (0.04)

Pinout	
Pin	Function
1	-Vin (GND)
2	Case
3	Remote
4	+Vin (Vcc)
5	-Vout
6	-Sense*
7	Trim
8	+Sense*
9	+Vout

*Sense line to be connected to the output either at the module or at the load under regard of polarity.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TRACO Power:

[TEP 75-2415WI](#) [TEP 75-2412WI](#) [TEP 75-2416WI](#) [TEP 75-4815WI](#) [TEP 75-4818WI](#) [TEP 75-7211WI](#) [TEP 75-2418WI](#) [TEP 75-2410WI](#) [TEP 75-7216WI](#) [TEP 75-7213WI](#) [TEP 75-2411WI](#) [TEP 75-4812WI](#) [TEP 75-4813WI](#) [TEP 75-7210WI](#) [TEP 75-7218WI](#) [TEP 75-7212WI](#) [TEP 75-2413WI](#) [TEP 75-4810WI](#) [TEP 75-4816WI](#) [TEP 75-7215WI](#) [TEP 75-4811WI](#)