



PRODUCT NUMBER
SEE SHEET 2

NOTES :

1. MINI PUSH-OUT FORCE TERMINAL IN BOTH DIRECTIONS 22N.
2. TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS PER ROW
EXAMPLE: 8 POS: $(N \times 2.54) - 1 = 19.32$ mm



mat'l. code				surface	tolerance	projection	product family		
SEE NOTES				ISO 1302	ISO 406	ISO 1101	DUBOX		
ltr	ecn no	dr	date	tolerances unless	otherwise specified	mm	title SHR. HEADER STR DR TMT		
G	F10103	GCO	01.01.12	angles	.X ±0.3				
H	F10116	GCO	01.01.23	linear	.XX ±0.15				
J	F04-0317	LMU	06.07.13		.XXX ±0.05	scale 5:1	dwg no		
K	F05-0159	LMU	05.03.31	dr	G CORBOZ	01.01.12	sheet 1 of 2		
L	F06-0106	LMU	06.01.12	enr	P NIZZI	01.01.12	size		
M	F06-0228	LMU	06.07.11	chr	D LEGRAND	01.01.12	A3		
N	F07-0147	LMU	07.03.01	appd	P N	01.01.12	type		
sheet index		revision	N D						
		sheet	1 2						

STANDARD PRODUCT NUMBER
76385-YXX

NUMBER OF POSITIONS PER ROW: 02 TO 18

PLATING CODE

- 3= 0.76µm GOLD ON CONTACT AREA.
3.81µm TIN-LEAD ON TAIL.
- 4= 5µm TIN-LEAD ON CONTACT AREA.
3.81µm TIN-LEAD ON TAIL.

NOTES:

- 1 - HOUSING MAT'L: THERMOPLASTIC GLASS FILLED
FLAME RETARDANT PER UL 94 V-O COLOR: BLUE.
- 2 - TERMINAL MATERIAL: PHOSPHOR BRONZE.
- 3 - 2 UP TO 6 POSITIONS PER ROW, PRODUCT PACKED IN PLASTIC BAG.
7 UP TO 18 POSITIONS PER ROW, PRODUCT PACKED IN TUBE.
- 4 - ONLY DASH NUMBER -X02 AND -X03
ALWAYS TEN (10) PRODUCTS MOLDED ASSEMBLY
& DELIVERED ON STRIP ACCORDING PHANTOM LINES.

RoHs COMPLIANT PRODUCT NUMBER
76385-YXXLF

SUFFIX LETTER "LF" INDICATES THE PRODUCT
IS RoHs COMPLIANT, SEE NOTE 5

PLATING CODE

- 3= 0.76µm GOLD ON CONTACT AREA.
2µm MIN MATTE TIN ON TAILS.
OVER 1.27µm Ni MIN
- 4= 2µm MIN MATTE TIN
OVER 1.27µm Ni MIN

NUMBER OF POSITIONS PER ROW: 02 TO 18

NOTES:

- 1 - HOUSING MAT'L: THERMOPLASTIC GLASS FILLED
FLAME RETARDANT PER UL 94 V-O COLOR: BLACK.
- 2 - TERMINAL MATERIAL: PHOSPHOR BRONZE.
- 3 - 2 UP TO 6 POSITIONS PER ROW, PRODUCT PACKED IN PLASTIC BAG.
7 UP TO 18 POSITIONS PER ROW, PRODUCT PACKED IN TUBE.
- 4 - ONLY DASH NUMBER -X02 AND -X03
ALWAYS TEN (10) PRODUCTS MOLDED ASSEMBLY
& DELIVERED TON STRIP ACCORDING PHANTOM LINES.
- 5 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS
 - a - PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE,
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATE.
 - b - MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO
260°C ±5°C SOLDER BATH TEMPERATURE FOR
5 SECONDS IN A WAVE SOLDER APPLICATION
WITH A 1.6mm MIN THICK CIRCUIT BOARD.
 - c - LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - d - LEGAL STATEMENT: SEE GS-22-008

mat'l. code SEE NOTES				surface ISO 1302	tolerance ISO 406 ISO 1101	projection	product family DUBOX
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title SHR. HEADER STR DR TMT
A	F05-0159	LMU	05.03.31	angles	.X ±0.3		
B	F06-0106	LMU	06.01.12	linear	.XX ±0.15		
C	F06-0228	LMU	06.07.11		.XXX ±0.05	scale 5:1	
D	F07-0147	LMU	07.03.01	dr	L.MULIN 05.03.31		dwg no 76385
				enr	J.COMPAGNON 05.03.31		sheet 2 of A3
				chr			type CUSTOMER Drawing
				appd	JM.C 05.03.31		
sheet index	revision sheet						



Copyright FCI