

Product Datasheet uvex i-3 add 2.0
Material No. 6108.211**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189, D-90766 Fürth**

Productcharacteristic	<ul style="list-style-type: none">* Innovative spectacle with invisible integrated dioptrre correction for near vision, +2,0 dpt.* Patented lens technology* Free-form lens design, manufactured in accordance with standard parameters and designed for a distance of approx. 64mm between the eyes* Extremely good coverage and fit all the way to the side area* Individually adjustable side arms with variable inclination* Integrated Softflex zone ensures outstanding wearer comfort for all head sizes* Softflex adjustable nose piece ensures comfortable, pressure-free fit and remain firmly in place
Technical details Frame Material Features Colour	TPU/TPE Variable inclination, individually adjustable grey/lime

Manufacturer	Marking W
EN Standard	166
Low-energy impact	F (45 m/sec) EN 166
Resistance to high speed particles at extremes of temperat.	T
Conformity symbol	CE
Lens	
Material	PC
Coating	supravision HC-AF
Colour	clear
Feature	integrated dioptrre correction; +2,0 dpt.
Filter	Marking 2C-1,2 (DIN EN 170)
Manufacturer	W
Optical class	1
Low-energy impact	F (45 m/sec)
Resistance to high speed particles at extremes of temperature	T
Surface resistance to fine particles	K
Antifog	N
Conformity symbol	CE
Corr./PD	i-3 add 2.0, PD 64 / Add. 2,0 dpt.
Miscellaneous	
Weight	38g
Packing	1 piece in soft spectacles case with microfiber cloth
Standards	DIN EN 166 + DIN EN 170