

VIP-3/SC/HD26SUB/F - Interface module



2322414

<https://www.phoenixcontact.com/us/products/2322414>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, with screw connection and high density D-SUB miniature socket strip, for mounting on NS 35 rails, no. of pos.: 26, width: 79 mm

Your advantages

- Screw connection
- 1:1 connection

Commercial data

Item number	2322414
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C423
Product key	CK2112
Catalog page	Page 558 (C-5-2019)
GTIN	4046356451710
Weight per piece (including packing)	142.133 g
Weight per piece (excluding packing)	140 g
Customs tariff number	85366990
Country of origin	US

VIP-3/SC/HD26SUB/F - Interface module



2322414

<https://www.phoenixcontact.com/us/products/2322414>

Technical data

Product properties

Product type	Interface module
Product family	VARIOFACE Professional
Number of positions	26

Electrical properties

Nominal voltage U_N	25 V AC
	60 V DC
Max. current carrying capacity per branch	1 A

Connection data

Connection 1 (control level)

Connection method	High-density D-SUB socket strip
Screw thread	UNC 4-40
Number of connections	1
Number of positions	26

Connection 2 (field level)

Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Number of positions	27
Conductor cross section rigid	0.2 mm ² ... 4 mm ²
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross section AWG	24 ... 12
Tightening torque	0.5 Nm ... 0.6 Nm

Signaling

Status display	No
Status display present	No

Dimensions

Item dimensions

Width	52.3 mm
Height	69 mm
Depth	62 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0

VIP-3/SC/HD26SUB/F - Interface module



2322414

<https://www.phoenixcontact.com/us/products/2322414>

Housing insulation material	Polyamide PA non-reinforced
-----------------------------	-----------------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations

Standards/regulations	EN 50178
-----------------------	----------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

VIP-3/SC/HD26SUB/F - Interface module




2322414

<https://www.phoenixcontact.com/us/products/2322414>

Drawings

Circuit diagram




VIP-3/SC/HD26SUB/F - Interface module



2322414

<https://www.phoenixcontact.com/us/products/2322414>

Dimensional drawing



VIP-3/SC/HD26SUB/F - Interface module





2322414

<https://www.phoenixcontact.com/us/products/2322414>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2322414>

 cUL Recognized Approval ID: FILE E 238705				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	1 A	30 - 12	-

 UL Recognized Approval ID: FILE E 238705				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	1 A	30 - 12	-

cULus Recognized				
-------------------------	--	--	--	--

VIP-3/SC/HD26SUB/F - Interface module



2322414

<https://www.phoenixcontact.com/us/products/2322414>

Classifications

ECLASS

ECLASS-11.0	27141152
ECLASS-12.0	27141152
ECLASS-13.0	27141152

ETIM

ETIM 9.0	EC002780
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VIP-3/SC/HD26SUB/F - Interface module



2322414

<https://www.phoenixcontact.com/us/products/2322414>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	1127e2e3-01d5-46ab-b951-de2d2a37e13e

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com