

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

OCT. 2005

© COPYRIGHT 2005 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
A1		Released as per ECR-08-022292	4-Sep-08	SP	JC
AH		ECR-16-003725	12MAR2016	KR	TN
AH1		ECR-18-019547	14DEC2018	SR	AP
AH2		ECR-19-004212	15MAR2019	SR	CB

LASER MARKING: TE LOGO PN VALUE  
TOLERANCE & DATE CODE4 HOLES OF  $\phi 4.4$ 





1 FOR FURTHER INFORMATION SEE DATA SHEET FOR  
HS SERIES-ALUMINIUM HOUSED RESISTORS2 FOR A SPECIFIC PN FOR A RESISTANCE VALUE  
AND TOLERANCE, PLEASE REFER TO DMF3 TECHNICAL SPECIFICATION

DISSIPATION AT 25°C : 100 WATTS MOUNTED  
ON STD HEATSINK

OHMIC RANGE : R10 TO 75K

STABILITY :  $\Delta R \leq 2\%$  PER 1000Hrs

ISOLATION VOLTAGE : 3500VAC rms

MAX WORKING VOLTAGE : 1900V DC/AC rms

TEMP COEFFICIENT : > 1R0 50ppm  
> 100R 25ppm

CLIMATIC CATEGORY : 55/200/56

RoHS Compliant

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 27.SEP.05  
DAVE KENNEDYCHK 28.SEP.05  
J CATCHPOLEAPVD 28.SEP.05  
J CATCHPOLE

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT -

TE Connectivity

NAME  
HSC100 METAL HOUSED  
POWER RESISTOR

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 00779 C-1625999

CUSTOMER DRAWING

SCALE 1:1 SHEET 1 OF 1 REX AH2

DIMENSIONS:

mm

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

0 PLC	$\pm 0.5$
1 PLC	$\pm 0.2$
2 PLC	$\pm 0.1$
3 PLC	$\pm$
4 PLC	$\pm$
ANGLES	$5^\circ$

MATERIAL

-

FINISH

-

1470-19 (3/13)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[HSC100180RJ](#)