

**VDE SCREWDRIVER**

**VDE 42**

**VDE HEXAGON ALLEN KEY for in-hex screws**

- Acc. to DIN ISO 2936
- Particularly suitable for cable branch clamping rings
- Oil-hardened
- GEDORE vanadium special steel
- VDE insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004



1000 V

Code	No.	mm	L <sub>1</sub>	L <sub>2</sub>	mm	mm	£
2324849	<b>VDE 42 3</b>	3	130	23.5	20	1	
2324857	<b>VDE 42 4</b>	4	120	40.0	25	1	
2324865	<b>VDE 42 5</b>	5	140	48.0	45	1	
2324873	<b>VDE 42 6</b>	6	140	48.0	60	1	
2324881	<b>VDE 42 8</b>	8	150	51.0	110	1	
2324903	<b>VDE 42 10</b>	10	220	51.0	230	1	
2324911	<b>VDE 42 12</b>	12	260	61.5	350	1	

**VDE 42 T**

**VDE HEXAGON ALLEN KEY WITH T-HANDLE for in-hex screws**

- Insulated acc. to IEC 60900:2004
- With Check-Tool insulation
- GEDORE chrome-vanadium steel 59CrV4



1000 V

Code	No.	mm	mm	mm	mm	£
2661225	<b>VDE 42 T 4</b>	4	160	145	1	
2661233	<b>VDE 42 T 5</b>	5	160	250	1	
2661241	<b>VDE 42 T 6</b>	6	160	250	1	
2661268	<b>VDE 42 T 8</b>	8	160	260	1	
2661276	<b>VDE 42 T 10</b>	10	200	390	1	
2661284	<b>VDE 42 T 11</b>	11	200	400	1	
2661292	<b>VDE 42 T 12</b>	12	200	420	1	

**VDE 2170**

**VDE SCREWDRIVER for slotted head screws**

- VDE insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, fully insulated blade
- Blade tip to DIN ISO 2380-1 form A
- With impact resistant handle
- Blade in chrome-vanadium steel, with black tip



1000 V

Code	No.	mm	mm	mm	mm	mm	£
1612220	<b>VDE 2170 2,5</b>	0.4	2.5	75	155	29	10
1612239	<b>VDE 2170 3</b>	0.5	3.0	100	180	33	10
1612247	<b>VDE 2170 3,5</b>	0.6	3.5	100	190	46	10
1612255	<b>VDE 2170 4</b>	0.8	4.0	100	190	49	10
1612271	<b>VDE 2170 5,5</b>	1.0	5.5	125	225	81	10
1612298	<b>VDE 2170 6,5</b>	1.2	6.5	150	260	116	10
1612301	<b>VDE 2170 8</b>	1.2	8.0	175	195	158	10
1612336	<b>VDE 2170 10</b>	1.6	10.0	200	320	188	10

**VDE 2160 PH**

**VDE SCREWDRIVER for cross-slotted head screws PH**

- VDE insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, fully insulated blade
- Blade tip to DIN ISO 8764-1 PH
- With impact-resistant handle
- Blade in chrome-vanadium steel, with black tip



1000 V

Code	No.	PH	mm	mm	mm	mm	£
1612107	<b>VDE 2160 PH 0</b>	0	M1,6 - M2	60	140	30	10
1612115	<b>VDE 2160 PH 1</b>	1	M2 - M3	80	180	68	10
1612123	<b>VDE 2160 PH 2</b>	2	M3,5 - M5	100	210	101	10
1612131	<b>VDE 2160 PH 3</b>	3	M5,5 - M7	150	270	168	10
1612158	<b>VDE 2160 PH 4</b>	4	M8 - M10	200	320	249	10

**VDE 2160 PZ**

**VDE SCREWDRIVER for cross-slotted head screws PZ**

- VDE insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, fully insulated blade
- Blade tip to DIN ISO 8764-1 PZ
- With impact-resistant handle
- Blade in chrome-vanadium steel, with black tip



1000 V

Code	No.	PZ	mm	mm	mm	mm	£
1612166	<b>VDE 2160 PZ 0</b>	0	M1,6 - M2	60	140	29	10
1612182	<b>VDE 2160 PZ 1</b>	1	M2 - M3	80	180	68	10
1612190	<b>VDE 2160 PZ 2</b>	2	M3,5 - M5	100	210	102	10
1612204	<b>VDE 2160 PZ 3</b>	3	M5,5 - M7	150	270	168	10
1612212	<b>VDE 2160 PZ 4</b>	4	M8 - M10	200	320	250	10

**VDE 2170-2160 PH-077**

**VDE SCREWDRIVER SET 7 pieces**

- Packed in environmentally-friendly cardboard box
- For slotted and cross-slotted head screws PH
- VDE insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, fully insulated blade
- With impact-resistant handle




1000 V

Code	No.	Contents	mm	mm	£
1616048	<b>VDE 2170-2160 PH-077</b>	⊖ VDE 2170 2,5 4 5,5 6,5 ⊕ VDE 2160 PH 0 1 2	575	1	

**VDE 8098**

**VDE STRIPPING PLIERS with VDE dipped insulation**

- Opening stop, spring and brass adjusting screw for wires 0.8 - 6.0 mm<sup>2</sup>
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE dipped insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, two-ply Check-Tool insulation




1000 V

Code	No.	L	L <sub>3</sub>	W <sub>3</sub>	T <sub>1</sub>	mm <sup>2</sup>			£
6708980	<b>VDE 8098-160</b>	160	43.5	18.5	8.5	0,8-6	217	1	

**VDE 8098 H**

**VDE STRIPPING PLIERS with VDE insulating sleeves**

- Opening stop, spring and brass adjusting screw for wires 0.8 - 6.0 mm<sup>2</sup>
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE insulating sleeves up to 1000 V, acc. to EN 60900/IEC 60900:2004



1000 V

Code	No.	L	L <sub>3</sub>	W <sub>3</sub>	T <sub>1</sub>	mm <sup>2</sup>			£
1552074	<b>VDE 8098-160 H</b>	160	43.5	18.5	8.5	0,8-6	204	1	

**VDE 8099**

**VDE STRIPPING PLIERS STRIP-FIX with VDE dipped insulation**

- Self-adjusting, for wires 0.5 - 5.0 mm<sup>2</sup>
- GEDORE special hardened and tempered steel, oil-hardened, chrome-plated
- Handles with VDE dipped insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, two-ply Check-Tool insulation
- E-8099 = Pair of spare knives



1000 V

Code	No.	mm	inch	mm <sup>2</sup>			£
6709600	<b>VDE 8099-160</b>	160	6.1/2	0,5-5	226	1	
5709580	<b>E-8099</b>			12	1		

**VDE 8099 H**

**VDE STRIPPING PLIERS STRIP-FIX with VDE insulating sleeves**

- Self-adjusting, for wires 0.5 - 5.0 mm<sup>2</sup>
- V-shaped cutting jaws for stripping the plastic insulation of single and multi-strand conductors
- GEDORE special hardened and tempered steel, oil-hardened, chrome-plated
- Handles with VDE insulating sleeves up to 1000 V, acc. to EN 60900/IEC 60900:2004



1000 V

Code	No.	mm	inch	mm <sup>2</sup>			£
1552082	<b>VDE 8099-160 H</b>	160	6.1/2	0,5-5	211	1	

**VDE 146**

**VDE UNIVERSAL PLIERS 7 settings**

- Gripping pliers with safety box joint and finger protection
- GEDORE special chrome-vanadium steel
- Handles with VDE dipped insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, two-ply Check-Tool insulation




1000 V

Code	No.	mm	mm			£
6120140	<b>VDE 146 10</b>	250	31	485	1	

**VDE 8250**

**VDE HEAVY DUTY COMBINATION PLIERS with VDE dipped insulation**

- For heavy continuous use
- Good lever action for easy cutting
- Induction-hardened precision cutting edges, hardness 62 - 64 HRC
- For flat and round material
- To cut all wire types including piano wire, 1.6 mm
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE dipped insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, two-ply Check-Tool insulation



1000 V

Code	No.	L	L <sub>3</sub>	W <sub>3</sub>	W <sub>4</sub>	T <sub>1</sub>			£
1429582	<b>VDE 8250-160</b>	160	35.0	22.8	5.8	10.4	236	1	
6720090	<b>VDE 8250-180</b>	180	38.5	25.6	6.5	11.0	312	1	
6720250	<b>VDE 8250-200</b>	200	39.5	27.0	6.5	12.4	365	1	
6720330	<b>VDE 8250-225</b>	225	42.2	27.7	6.5	13.0	485	1	





### VDE 8250 H

#### VDE HEAVY DUTY COMBINATION PLIERS

##### with VDE insulating sleeves

- For heavy continuous use
- Good lever action for easy cutting
- Induction-hardened precision cutting edges, hardness 62 - 64 HRC
- For flat and round material
- To cut all wire types including piano wire, 1.6 mm
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE insulating sleeves up to 1000 V, acc. to EN 60900/ IEC 60900:2004




Code	No.	L	L <sub>3</sub>	W <sub>3</sub>	W <sub>4</sub>	T <sub>1</sub>	mm <sup>2</sup>	Ø	£
1550942	<b>VDE 8250-160 H</b>	160	35.0	22.8	5.8	10.4	228	1	
1550950	<b>VDE 8250-180 H</b>	180	38.5	25.6	6.5	11.0	288	1	
1550969	<b>VDE 8250-200 H</b>	200	39.5	27.0	6.5	12.4	369	1	

### VDE 8314

#### VDE SIDE CUTTER with VDE dipped insulation

- With slender head - ideal for confined spaces
- Induction-hardened precision cutting edges, hardness 63 - 65 HRC
- For medium-hard wire, 1.6 mm
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE dipped insulation up to 1000 V, acc. to EN 60900/ IEC 60900:2004, two-ply Check-Tool insulation




Code	No.	L	L <sub>3</sub>	W <sub>3</sub>	T <sub>1</sub>	Ø	mm <sup>2</sup>	£
6743540	<b>VDE 8314-140</b>	140	18.5	18.5	9.5	1.6	199	1
6743620	<b>VDE 8314-160</b>	160	19.0	22.0	10.0	1.6	253	1

### VDE 8314 H

#### VDE SIDE CUTTER with VDE insulating sleeves

- With slender head - ideal for confined spaces
- Induction-hardened precision cutting edges, hardness 63 - 65 HRC
- For medium-hard wire, 1.6 mm
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE insulating sleeves up to 1000 V, acc. to EN 60900/ IEC 60900:2004




Code	No.	L	L <sub>3</sub>	W <sub>3</sub>	T <sub>1</sub>	Ø	mm <sup>2</sup>	£
1552155	<b>VDE 8314-140 H</b>	140	18.5	18.5	9.5	1.6	177	1
1552163	<b>VDE 8314-160 H</b>	160	19.0	22.0	10.0	1.6	231	1

### VDE 8315 H

#### VDE ELECTRICIANS' SIDE CUTTER

##### with VDE insulating sleeves

- Double-function electricians' side cutters for cutting and wire stripping
- Stripping holes for single or multi-strand conductors 1.5 and 2.5 mm<sup>2</sup>
- Induction-hardened precision cutting edges
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE insulating sleeves up to 1000 V, acc. to EN 60900/ IEC 60900:2004




Code	No.	L	L <sub>3</sub>	W <sub>3</sub>	T <sub>1</sub>	mm <sup>2</sup>	Ø	£
1742582	<b>VDE 8315-160 H</b>	160	19	22	10	1,5 / 2,5	1,6	231


### VDE 8316

#### VDE POWER SIDE CUTTER with VDE dipped insulation

- Good lever action for easy cutting
- Induction-hardened precision cutting edges, hardness 63 - 65 HRC
- For hard wire/piano wire - values see table
- Max. cutting capacity Ø 1.8 - 2.0 mm
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE dipped insulation up to 1000 V, acc. to EN 60900/ IEC 60900:2004, two-ply Check-Tool insulation



Code	No.	L	L <sub>3</sub>	W <sub>3</sub>	T <sub>1</sub>	Ø	mm <sup>2</sup>	£
1429590	<b>VDE 8316-180</b>	180	22.6	26	11	1,8	285	1
6742570	<b>VDE 8316-200</b>	200	22.0	28	11	2,0	341	1







**VDE 8316 H**

**VDE POWER SIDE CUTTER with VDE insulating sleeves**

- Good lever action for easy cutting
- Induction-hardened precision cutting edges, hardness 63 - 65 HRC
- For hard wire/piano wire - values see table
- Max. cutting capacity Ø 1.8 - 2.0 mm
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE insulating sleeves up to 1000 V, acc. to EN 60900/IEC 60900:2004





Code	No.	L	L <sub>3</sub>	W <sub>3</sub>	T <sub>1</sub>	Ø	↔	☒	£
1550993	<b>VDE 8316-180 H</b>	180	22.6	26	11	1,8	267	1	
1551000	<b>VDE 8316-200 H</b>	200	22.0	28	11	2,0	344	1	

**VDE 8120 H**

**VDE FLAT NOSE PLIERS with VDE insulating sleeves**

- Long, flat jaws and serrated gripping surfaces
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE insulating sleeves up to 1000 V, acc. to EN 60900/IEC 60900:2004




Code	No.	L	L <sub>3</sub>	W <sub>3</sub>	W <sub>4</sub>	T <sub>1</sub>	↔	☒	£
1552090	<b>VDE 8120-160 H</b>	160	51	16.5	3.4	9	175	1	

**VDE 8367**

**VDE HEAVY DUTY END CUTTING NIPPERS**

- Good lever action for easy cutting
- Induction-hardened precision cutting edges, hardness 63 - 65 HRC
- For hard wire/piano wire 1.6 mm
- GEDORE special hardened and tempered steel, drop-forged, oil-hardened and annealed
- Handles with VDE dipped insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, two-ply Check-Tool insulation




Code	No.	L	L <sub>3</sub>	W <sub>3</sub>	T <sub>1</sub>	Ø	↔	☒	£
2324830	<b>VDE 8367-160</b>	160	6.9	27	23.5	1,6	220	1	

**VDE 8122**

**VDE ROUND NOSE PLIERS with VDE dipped insulation**

- Long, round jaws and serrated gripping surfaces
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE dipped insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, two-ply Check-Tool insulation





Code	No.	L	L <sub>3</sub>	W <sub>3</sub>	D <sub>1</sub>	T <sub>1</sub>	↔	☒	£
6717110	<b>VDE 8122-160</b>	160	48	16.5	2.5	8.7	170	1	

**VDE 8120**

**VDE FLAT NOSE PLIERS with VDE dipped insulation**

- Long, flat jaws and serrated gripping surfaces
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE dipped insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, two-ply Check-Tool insulation




Code	No.	L	L <sub>3</sub>	W <sub>3</sub>	W <sub>4</sub>	T <sub>1</sub>	↔	☒	£
6715330	<b>VDE 8120-160</b>	160	51	16.5	3.4	9	185	1	

**VDE 8122 H**

**VDE ROUND NOSE PLIERS with VDE insulating sleeves**

- Long, round jaws and serrated gripping surfaces
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE insulating sleeves up to 1000 V, acc. to EN 60900/IEC 60900:2004




Code	No.	L	L <sub>3</sub>	W <sub>3</sub>	D <sub>1</sub>	T <sub>1</sub>	↔	☒	£
1552104	<b>VDE 8122-160 H</b>	160	48	16.5	2.5	8.7	154	1	

### VDE 8132

#### VDE TELEPHONE PLIERS with VDE dipped insulation, straight pattern

- Long, flat-round jaws, straight gripping faces, serrated
- Induction-hardened precision cutting edges, hardness 61 - 63 HRC
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE dipped insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, two-ply Check-Tool insulation




Code	No.	L	L <sub>3</sub>	W <sub>3</sub>	W <sub>4</sub>	T <sub>1</sub>	T <sub>2</sub>	↔	☑	£
6721570	<b>VDE 8132-160</b>	160	50.0	16.5	3.2	9.0	2.5	193	1	
6721650	<b>VDE 8132-200</b>	200	75.7	18.5	3.7	9.5	2.8	248	1	



### VDE 8132 AB

#### VDE BENT NOSE TELEPHONE PLIERS with VDE dipped insulation, angled pattern

- Long, flat-round jaws, angled gripping surfaces, serrated
- Induction-hardened precision cutting edges, hardness 61 - 63 HRC
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE dipped insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, two-ply Check-Tool insulation




Code	No.	L	L <sub>3</sub>	W <sub>3</sub>	W <sub>4</sub>	T <sub>1</sub>	T <sub>2</sub>	↔	☑	£
6721730	<b>VDE 8132 AB-160</b>	160	46.0	16.5	3.2	9.0	2.5	177	1	
6721810	<b>VDE 8132 AB-200</b>	200	70.5	18.5	3.7	9.5	2.8	252	1	



### VDE 8132 H

#### VDE TELEPHONE PLIERS with VDE insulating sleeves, straight pattern

- Long, flat-round jaws, straight gripping faces, serrated
- Induction-hardened precision cutting edges, hardness 61 - 63 HRC
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE insulating sleeves up to 1000 V, acc. to EN 60900/IEC 60900:2004




Code	No.	L	L <sub>3</sub>	W <sub>3</sub>	W <sub>4</sub>	T <sub>1</sub>	T <sub>2</sub>	↔	☑	£
1552112	<b>VDE 8132-160 H</b>	160	50.0	16.5	3.2	9.0	2.5	164	1	
1552120	<b>VDE 8132-200 H</b>	200	75.7	18.5	3.7	9.5	2.8	235	1	

### VDE 8132 AB H

#### VDE BENT NOSE TELEPHONE PLIERS with VDE insulating sleeves, angled pattern

- Long, flat-round jaws, angled gripping surfaces, serrated
- Induction-hardened precision cutting edges, hardness 61 - 63 HRC
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE insulating sleeves up to 1000 V, acc. to EN 60900/IEC 60900:2004



Code	No.	L	L <sub>3</sub>	W <sub>3</sub>	W <sub>4</sub>	T <sub>1</sub>	T <sub>2</sub>	↔	☑	£
1552139	<b>VDE 8132 AB-160 H</b>	160	46.0	16.5	3.2	9.0	2.5	173	1	
1552147	<b>VDE 8132 AB-200 H</b>	200	70.5	18.5	3.7	9.5	2.8	235	1	

**VDE S 8003**

**VDE PLIERS SET WITH VDE DIPPED INSULATION 3 pieces**

- ✔ Packed in environmentally-friendly cardboard box
- ✔ Handles with VDE dipped insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, two-ply Check-Tool insulation



Code	No.	Contents	Weight	Units	£
6708120	<b>VDE S 8003</b>	<b>VDE 8132-160</b> <b>VDE 8250-180</b> <b>VDE 8314-160</b>	760	1	

**VDE S 8003 H**

**VDE PLIERS SET WITH VDE INSULATING SLEEVES 3 pieces**

- ✔ Packed in environmentally-friendly cardboard box
- ✔ Handles with VDE insulating sleeves up to 1000 V, acc. to EN 60900/IEC 60900:2004



Code	No.	Contents	Weight	Units	£
1550594	<b>VDE S 8003 H</b>	<b>VDE 8132-160 H</b> <b>VDE 8250-180 H</b> <b>VDE 8314-160 H</b>	747	1	

**RZB2-11**

**VDE PLIERS SET 3 pieces**

- ✔ In rugged plastic case
- ✔ Handles with VDE insulating sleeves up to 1000 V, acc. to EN 60900/IEC 60900:2004



Code	No.	Contents	Weight	Units	£
1692291	<b>RZB2-11</b>	<b>VDE 8132-160 H</b> <b>VDE 8250-180 H</b> <b>VDE 8314-160 H</b>	865	1	

**RZB2-5**

**VDE PLIERS SET 3 pieces**

- ✔ In rugged plastic case
- ✔ Handles with VDE insulating sleeves up to 1000 V, acc. to EN 60900/IEC 60900:2004



Code	No.	Contents	Weight	Units	£
1708244	<b>RZB2-5</b>	<b>VDE 8098-160 H</b> <b>VDE 8250-180 H</b> <b>VDE 8314-160 H</b>	835	1	

**RZB1-17**

**VDE TOOL SET 8 pieces**

- ✔ In rugged plastic case



Code	No.	Contents	Weight	Units	£
1828045	<b>RZB1-17</b>	<b>VDE 8132-200 H</b> <b>VDE 8250-180 H</b> <b>VDE 8314-160 H</b> <b>VDE 2170 4 5,5</b> <b>VDE 2160 PH 1 2</b> <b>4615 3</b>	1700	1	

Contents

	<b>VDE 8132 -200 H</b>
	<b>VDE 8250 -180 H</b>
	<b>VDE 8314 -160 H</b>
	<b>VDE 2170 4 5,5</b>
	<b>VDE 2160 PH 1 2</b>
	<b>4615 3</b>



## VDE ASSORTMENTS

### S 1023

#### TOOL ASSORTMENT FOR MECHANICAL ENGINEERS 120 pieces

- Practical entry-level toolset
- The range includes mechanical and electrical engineering tools
- Recommended hook assortment 1500 HS-1023 (53 pieces)
- Also available in tool trolley or on tool boards

Code	No.	Contents	€	£
1999060	<b>S 1023</b>	118 tools in metric sizes	13.0	<b>876.17</b>
2657619	<b>1023-1450-2</b>	Tool set S 1023 + 2x tool panel 1450 L + hook assortment 1500 HS-1023	27.3	<b>1,114.05</b>
2657627	<b>1023-1578</b>	Tool set S 1023 + tool trolley 1578	56.5	<b>1,272.64</b>



Contents	€
<b>1 B</b> 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 21 22	
<b>D 20</b> 4 5 6 7 8 9 10 11 12 13	
<b>680</b> 4 5,5 6,5	
<b>685</b> 3 4 5 6	
<b>685 X</b> 5 6 8	
<b>687 TX</b> T10 T15 T20 T25 T27 T30 T40	
<b>690</b> 1 2	
<b>690 PZD</b> 1 2 3	
<b>620</b>	
<b>676</b>	
<b>699</b>	
<b>2090</b> -4	
<b>2093 U</b> -20	
<b>1993 U</b> -10 T	
<b>19</b> 8 9 10 11 12 13 14 15 16 17 19 22 24 27 30 32	
<b>1987</b>	

Contents	€
<b>1990</b> -5 -10	
<b>1995</b>	
<b>VDE 8132</b> -200 H	
<b>VDE 8250</b> -180 H	
<b>VDE 8314</b> -160 H	
<b>VDE 2170</b> 4 5,5	
<b>VDE 2160 PH</b> 1 2	
<b>V 4614 PLUS</b>	
<b>4615</b> 3	
<b>171 IS</b> 1,2 1,5 2	
<b>165 PH</b> 00 0	
<b>8305</b> -2	
<b>8306</b> -5	
<b>42</b> 1,3 1,5 2 (5/64AF) 2,5 3 4 5 6 8 10	
<b>97</b> -150	

Contents	€
<b>100</b> -10	
<b>119</b> -3 -5	
<b>600 H</b> -500	
<b>248 ST</b> -30	
<b>8701</b> 2-8	
<b>8719</b> 2-8	
<b>8722</b> 2-8	
<b>403</b>	
<b>4528</b>	
<b>710</b>	
<b>745</b>	
<b>4534</b> -3	
<b>298</b> -04	
<b>8354</b> -1	
<b>8139</b> -220 TL	

### S 1093

#### VDE TOOL ASSORTMENT 26 pieces

- Particularly suited as the initial outfit for electrical specialists
- The GEDORE tool case or tool trolley are suited for mobile assignments
- Recommended hook assortment 1500 HS-1093 (26 pieces)
- Also available with case or on tool board

Code	No.	Contents	€	£
2319942	<b>S 1093</b>	26 tools in metric sizes	4.8	<b>289.39</b>
2657317	<b>1093</b>	Tool set S 1093 + tool case WK 1091 L	9.0	<b>389.41</b>
2657309	<b>1093-1450</b>	Tool set S 1093 + tool panel 1450 L + hook assortment 1500 HS-1093	11.1	<b>375.67</b>



Contents	€
<b>142</b> 10 C	
<b>VDE 8250</b> -180 H	
<b>VDE 8132</b> -160 H	
<b>VDE 8314</b> -160 H	
<b>VDE 2170</b> 4 5,5 6,5 8	
<b>VDE 2160 PZ</b> 1 2	

Contents	€
<b>V 4614 PLUS</b>	
<b>42</b> 2 (5/64AF) 2,5 3 4 5 6 8 10	
<b>4533</b> -2	
<b>4528</b>	

Contents	€
<b>8097</b>	
<b>600 H</b> -500	
<b>112 A</b> -250	
<b>110 HS</b> -318	
<b>0175</b> -06	

**1090**

**TOOL CASE ELECTRICIAN 90 pieces**

- ✔ The perfect tool set for the electrician or property manager
- ✔ A thoughtful assortment for the work to be done
- ✔ Packed in a strong plastic case with aluminium frame
- ✔ Three steel hinges, screwed handle, fitted with built in locks
- ✔ May be used wherever the right tools have to be always at hand
- ✔ GEDORE vanadium tools, chrome-plated
- ✔ Dimensions: W 460 x D 380 x H 200 mm



Code	No.	Contents	kg	£
6601590	<b>1090</b>	Tool set S 1090 + tool case WK 1090 L	13.2	<b>708.94</b>

Contents	
<b>401</b>	
<b>401 A</b> [10x]	
<b>6</b> 14x17 18x19 21x23 22x24	
<b>8</b> 4,5 5,5 5,5 6 7 8 9 10 11 12 13	
<b>20</b> 4,5 5,5 5,5 6 7 8 9 10 11 13	
<b>2087</b>	
<b>2095</b>	
<b>2098</b>	
<b>2090</b> -4	
<b>2093 U</b> -3	
<b>42</b> 2 (5/64AF) 2,5 3 4 5 6 7 8 10	
<b>60 CP</b> 10	
<b>156 S</b>	

Contents	
<b>2153</b> 5,5	
<b>2161 PH</b> 1	
<b>2160 PZ</b> 1 2	
<b>VDE 2160 PH</b> 1 2	
<b>VDE 2170</b> 3,5 4,5 5,5 6,5	
<b>4615</b> 3,5	
<b>173</b> 5,5 8	
<b>174</b> 1	
<b>745</b>	
<b>4522</b>	
<b>4534</b> -3	
<b>145</b> 10 JC	
<b>8096</b> -140	

Contents	
<b>VDE 8098</b> -160	
<b>VDE 8120</b> -160	
<b>VDE 8250</b> -180	
<b>VDE 8132 AB</b> -160	
<b>VDE 8316</b> -200	
<b>95</b> -175	
<b>99</b> 10-2 10-4	
<b>101</b>	
<b>112 A</b> -250	
<b>112 S</b>	
<b>600 H</b> -300	
<b>72 H</b> -100	
<b>E-1090</b> LK LZ LF LS	

**1091**

**ELECTRICIANS TOOL CASE 18 pieces**

- ✔ Robust tool case with 18-piece basic assortment
- ✔ **Particularly suitable for beginners in electronic professions**
- ✔ From eco-friendly tanned cowhide
- ✔ Carefully processed with strong industrial seams
- ✔ Base insert from zinc-plated sheet steel
- ✔ Edges reinforced with aluminium angle brackets, metal parts durable riveted
- ✔ With feet to protect sensitive surfaces
- ✔ Front part can be lowered for quick access to the tools, with two key locks to prevent inadvertent opening
- ✔ Removable carrying strap with shoulder protector and sturdy carrying handle
- ✔ Anti-theft protection due to two lockable notches, delivery includes two keys
- ✔ Document partition
- ✔ Interior measurements 430 x 200 x 290 mm



Code	No.	Contents	kg	£
1953710	<b>1091</b>	Tool set S 1091 + tool case WK 1091 L	8.3	<b>364.05</b>

Contents	
<b>VDE 2133</b> 7 8 10	
<b>VDE 2160 PH</b> 1 2 3	
<b>VDE 2170</b> 3 4 5,5	
<b>4528</b>	
<b>4533</b> -2	

Contents	
<b>V 4614 PLUS</b>	
<b>4629</b>	
<b>8097</b>	

Contents	
<b>VDE 8132</b> -160 H	
<b>VDE 8250</b> -180 H	
<b>VDE 8316</b> -180 H	
<b>E-1091 ST</b>	





### VDE 1001

#### VDE TOOL SET 14 pieces

- With practical foam insert in sturdy PVC case
- Dimensions: 380 x 285 x 70 mm
- Cranked allen socket screwdriver no. 42 is for locking the adjusting screw of extension VDE 1990, not VDE insulated



Code	No.	Contents	Weight	Quantity	Price (£)
6602560	<b>VDE 1001</b>	<b>VDE 19</b> 10 12 13 14 17 19 22 24 <b>VDE 1993 U</b> <b>VDE 1990-5 -10</b> <b>VDE 1989 T</b> <b>VDE 2170 5,5</b> <b>42 2,5</b>	3.5	1	<b>700.39</b>

Contents	
	<b>VDE 19</b> 10 12 13 14 17 19 22 24
	<b>VDE 1993 U</b>
	<b>VDE 1990 -5 -10</b>

Contents	
	<b>VDE 1989 T</b>
	<b>VDE 2170 5,5</b>
	<b>42 2,5</b>

### VDE 1030

#### VDE TOOL CABINET 108 pieces

- Complete with a selection of VDE tools
- Dimensions: 190 x 500 x 750 mm



Code	No.	Contents	Weight	Quantity	Price (£)
6602130	<b>VDE 1030</b>	108 tools in cabinet	46.0	1	<b>2,698.85</b>
5600730	<b>VDE 1030 L</b>	Cabinet, empty	20.0	1	<b>836.93</b>

Contents	
	<b>VDE 2133</b> 5 6 7 8 9 10 11 12 13
	<b>VDE 19</b> 10 11 12 13 14 15 17 19 22 24 27 30 32
	<b>VDE IN 19</b> 5 6 8
	<b>VDE 1990 -5 -10</b>
	<b>VDE 1993 U</b>
	<b>VDE 2170</b> 2,5 4 5,5 6,5
	<b>VDE 2160 PH</b> 0 1 2
	<b>VDE 894</b> 10 11 12 13 14 15 16 17 19
	<b>VDE 8098 -160 H</b>
	<b>VDE 8132 -160 H</b>

Contents	
	<b>VDE 8250 -160 H</b>
	<b>VDE 8314 -160 H</b>
	<b>VDE 4507 -4</b>
	<b>647</b>
	<b>171 IS</b> 1,2 1,5 2
	<b>165 PH</b> 0 0 0
	<b>8305 -2</b>
	<b>8306 -5</b>
	<b>4 K -500</b>
	<b>1500 H</b> 1-50 [6x] 2-13 [17x] 3 [27x]

**VDE ACCESSORIES**

**VDE 910**

**VDE RUBBER COVER SHEET**

- ▶ VDE protective equipment acc. to VDE 0680, Part 1
- ▶ Thickness: 1.6 mm



Code	No.	L	W	±mm	📦	£
1826816	<b>VDE 910 13</b>	130	130	40	1	<b>9.17</b>
1826832	<b>VDE 910 25</b>	250	350	210	1	<b>33.04</b>
1827030	<b>VDE 910 50</b>	500	500	430	1	<b>91.22</b>
1828193	<b>VDE 910 60</b>	600	600	700	1	<b>123.23</b>
1828207	<b>VDE 910 100</b>	1000	1000	1800	1	<b>282.06</b>
1828215	<b>VDE 910 120</b>	1200	1200	2950	1	<b>410.42</b>

**VDE 911**

**VDE INSULATION MAT**

- ▶ VDE protective equipment acc. to VDE 0303
- ▶ Thickness: 4.5 mm



Code	No.	L	W	±mm	📦	£
1828258	<b>VDE 911 100</b>	1000	1000	6.0	1	<b>158.67</b>
1828266	<b>VDE 911 1000</b>	10000	1000	60.0	1	<b>1,386.22</b>

**VDE 912**

**VDE ELECTRICIANS' SAFETY GLOVES**

- ▶ Acc. to DIN EN 60903
- ▶ Made of natural latex

⚠ 1000 V



Code	No.	±mm	📦	£
1828274	<b>VDE 912 9</b>	215	1	<b>110.02</b>
1828282	<b>VDE 912 10</b>	215	1	<b>110.02</b>

**VDE 912**

**UNDER-GLOVES for VDE 912**



Code	No.	±mm	📦	£
1828290	<b>VDE 912 50</b>	50	1	<b>9.75</b>

**V 915**

**NH-FUSE INSERTION GLOVE WITH SLEEVE**

- ▶ To work on NH fuse inserts sizes 00 to 3
- ▶ To insert and remove low-tension high-performance fuses (NH fuse inserts)
- ▶ Can also be used for other devices applied instead of the fuse inserts, e.g. earthing and short-circuiting devices, inserting or removing blind fuse elements
- ▶ With contact blades to DIN 43620 Part 1, sizes 00 - 3 for nominal voltage to 600 V alternating voltage



⚠ 1000 V

Code	No.	±mm	📦	£
2661314	<b>V 915</b>	460	1	<b>122.35</b>

**V 916**

**PROTECTIVE BOOTS (PU)**

- ▶ From polyurethane (PU) with steel cap
- ▶ To CE-EN 345-1



⚠ 1000 V

Code	No.	Size	±mm	📦	£
2661322	<b>V 916 39-40</b>	39-40 / 6-6.1/2	3000	1	<b>213.50</b>
2661330	<b>V 916 41</b>	41 / 7.1/2	3000	1	<b>213.50</b>
2661349	<b>V 916 42</b>	42 / 8	3000	1	<b>213.50</b>
2661357	<b>V 916 43</b>	43 / 9	3000	1	<b>213.50</b>
2661365	<b>V 916 44-45</b>	44-45 / 9.1/2-10.1/2	3000	1	<b>213.50</b>
2661373	<b>V 916 46</b>	46 / 11	3000	1	<b>213.50</b>
2661381	<b>V 916 47</b>	47 / 12	3000	1	<b>213.50</b>

**VDE 913**

**VDE PLASTIC CLAMP**

- ▶ VDE protective equipment acc. to VDE 0680, Part 1



VDE 913 80

VDE 913 160

Code	No.	±mm	±mm	📦	£
1828304	<b>VDE 913 80</b>	80	30	1	<b>17.49</b>
1828312	<b>VDE 913 160</b>	160	70	1	<b>17.86</b>



- ▶ More VDE tools on request!
- ▶ Haven't you found the right tool?
- ▶ Ask us about custom-orders.
- ▶ Your problems are our assignments.