



Easy to use, self-explanatory counting scale with laboratory accuracy, counting resolution up to 360,000 points

**Features**

- **Self-explanatory graphic control panel**, the workings steps can be understood immediately, even without operating instructions
  - no learning time = reduces costs
  - ideal for untrained users
  - visualised process avoids operating errors
- The 4 steps are carried out from left to right:
  - 1 Place the empty container onto the weighing plate and tare by pressing the TARE key
  - 2 Place the reference quantity for the goods to be counted into the container (5, 10 or 20 pieces)
  - 3 Confirm the selected reference quantity by pressing the key (5, 10 or 20)
  - 4 Pour in the goods to be counted. The number of pieces will immediately be shown in the display
- **Precise counting:** The automatic reference weight optimisation of reference weight gradually improves the average piece weight value

- **Two balances in one:** Changes from counting mode to weighing mode at the touch of a key
- **Protective working cover** included with delivery

**Technical data**

- Large backlit LCD display
  - A, B digit height 9 mm
  - C digit height 18 mm
- Dimensions weighing surface
  - A  $\varnothing$  81 mm, plastic
  - B WxD 150x170 mm, stainless steel
  - C WxD 340x240 mm, stainless steel
- Overall dimensions WxDxH
  - A, B 167x250x85 mm
  - C 350x390x120 mm
- Optional battery operation, 6x1.5 V Size C not included, operating time up to 40 h, for models with weighing plate size C
- Permissible ambient temperature 10 °C/40 °C

**Accessories**

- **Protective working cover**, scope of delivery: 5 items, for models with weighing plate size
  - A KERN PCB-A02S05
  - B KERN PCB-A05S05
  - C KERN FKB-A02S05
- **Rechargeable battery pack external**, operating time up to 30 h without backlight, charging time approx. 10 h, for models with weighing plate size A, B, KERN KS-A01
- **Rechargeable battery pack internal**, operating time up to 30 h without backlight, charging time approx. 10 h, for models with weighing plate size A, B, KERN KB-A01N
- Further details, plenty of further accessories and suitable printers see *Accessories*

STANDARD



OPTION



Model	Weighing range [Max] kg	Readout [d] g	Smallest part weight [Normal] g/piece	Counting resolution Points	Net weight approx. kg	Weighing plate	Options	
							DAkkS Calibr. Certificate	DKD KERN
<b>CKE 360-3</b>	0,36	0,001	0,01	360.000	1	A	963-127	
<b>CKE 2000-2</b>	2	0,01	0,1	200.000	1,8	B	963-127	
<b>CKE 3600-2</b>	3,6	0,01	0,1	360.000	1,8	B	963-127	
<b>CKE 6K0.02</b>	6	0,02	0,2	300.000	7	C	963-128	
<b>CKE 8K0.05</b>	8	0,05	0,5	160.000	7	C	963-128	
<b>CKE 16K0.05</b>	16	0,05	0,5	320.000	7	C	963-128	
<b>CKE 16K0.1</b>	16	0,1	1	160.000	7	C	963-128	
<b>CKE 36K0.1</b>	36	0,1	1	360.000	7	C	963-128	
<b>CKE 65K0.2</b>	65	0,2	2	325.000	7	C	963-129	
<b>CKE 65K0.5</b>	65	0,5	5	130.000	7	C	963-129	

# KERN Pictograms

 <b>Internal adjusting:</b> Quick setting up of the balance's accuracy with internal adjusting weight (motordriven)	 <b>GLP/ISO log:</b> The balance displays serial number, user ID, weight, date and time, regardless of a printer connection	 <b>Suspended weighing:</b> Load support with hook on the underside of the balance
 <b>Adjusting program CAL:</b> For quick setting up of the balance's accuracy. External adjusting weight required	 <b>GLP/ISO log:</b> With weight, date and time. Only with KERN printers	 <b>Battery operation:</b> Ready for battery operation. The battery type is specified for each device
 <b>Memory:</b> Balance memory capacity, e.g. for article data, weighing data, tare weights, PLU etc.	 <b>Piece counting:</b> Reference quantities selectable. Display can be switched from piece to weight	 <b>Rechargeable battery pack:</b> Rechargeable set
 <b>Alibi memory:</b> Secure, electronic archiving of weighing results, complying with the 2014/31/EU standard.	 <b>Recipe level A:</b> The weights of the recipe ingredients can be added together and the total weight of the recipe can be printed out	 <b>Universal mains adapter:</b> with universal input and optional input socket adapters for A) EU, GB B) EU, GB, CH, USA C) EU, GB, CH, USA, AUS
 <b>Data interface RS-232:</b> To connect the balance to a printer, PC or network	 <b>Recipe level B:</b> Internal memory for complete recipes with name and target value of the recipe ingredients. User guidance through display	 <b>Mains adapter:</b> 230V/50Hz in standard version for EU. On request GB, USA or AUS version available
 <b>RS-485 data interface:</b> To connect the balance to a printer, PC or other peripherals. Suitable for data transfer over large distances. Network in bus topology is possible	 <b>Recipe level C:</b> Internal memory for complete recipes with name and target value of the recipe ingredients. User guidance through display, multiplier function, adjustment of recipe when dosages are exceeded or barcode recognition	 <b>Power supply:</b> Integrated in balance. 230V/50Hz standard EU. More standards e.g. GB, USA or AUS on request
 <b>USB data interface:</b> To connect the balance to a printer, PC or other peripherals	 <b>Totalising level A:</b> The weights of similar items can be added together and the total can be printed out	 <b>Weighing principle: Strain gauges</b> Electrical resistor on an elastic deforming body
 <b>Bluetooth* data interface:</b> To transfer data from the balance to a printer, PC or other peripherals	 <b>Percentage determination:</b> Determining the deviation in % from the target value (100 %)	 <b>Weighing principle: Tuning fork</b> A resonating body is electromagnetically excited, causing it to oscillate
 <b>WLAN data interface:</b> To transfer data from the balance to a printer, PC or other peripherals	 <b>Weighing units:</b> Can be switched to e.g. nonmetric units at the touch of a key. See balance model. Please refer to KERN's website for more details	 <b>Weighing principle: Electromagnetic force compensation</b> Coil inside a permanent magnet. For the most accurate weighings
 <b>Control outputs (optocoupler, digital I/O):</b> To connect relays, signal lamps, valves, etc.	 <b>Weighing with tolerance range:</b> (Check-weighing) Upper and lower limiting can be programmed individually, e.g. for sorting and dosing. The process is supported by an audible or visual signal, see the relevant model	 <b>Weighing principle: Single cell technology</b> Advanced version of the force compensation principle with the highest level of precision
 <b>Interface for second balance:</b> For direct connection of a second balance	 <b>Hold function:</b> (Animal weighing program) When the weighing conditions are unstable, a stable weight is calculated as an average value	 <b>Verification possible:</b> The time required for verification is specified in the pictogram +3 DAYS
 <b>Network interface:</b> For connecting the scale to an Ethernet network	 <b>Protection against dust and water splashes IPxx:</b> The type of protection is shown in the pictogram.	 <b>DAkkS calibration possible (DKD):</b> The time required for DAkkS calibration is shown in days in the pictogram +3 DAYS
 <b>Wireless data transfer:</b> between the weighing unit and the evaluation unit using an integrated radio module	 <b>Stainless steel:</b> The balance is protected against corrosion	 <b>Package shipment:</b> The time required for internal shipping preparations is shown in days in the pictogram 1 DAY
 <b>KERN Communication Protocol (KCP):</b> It is a standardized interface command set for KERN balances and other instruments, which allows retrieving and controlling all relevant parameters and functions of the device. KERN devices featuring KCP are thus easily integrated with computers, industrial controllers and other digital systems		 <b>Pallet shipment:</b> The time required for internal shipping preparations is shown in days in the pictogram 2 DAYS

## KERN – Precision is our business

To ensure the high precision of your balance KERN offers you the the appropriate test weight in the international OIML error limit classes E1-M3 from 1 mg - 2500 kg. In combination with a DAkkS calibration certificate the best pre-requisite for proper balance calibration.

The KERN DAkkS calibration laboratory today is one of the most modern and best-equipped DAkkS calibration laboratories for balances, test weights and force-measurement in Europe.

Thanks to the high level of automation, we can carry out DAkkS calibration of balances, test weights and force-measuring devices 24 hours a day, 7 days a week.

### Range of services:

- DAkkS calibration of balances with a maximum load of up to 50 t
- DAkkS calibration of weights in the range of 1 mg – 2500 kg
- Volume determination and measuring of magnetic susceptibility (magnetic characteristics) for test weights
- Database supported management of checking equipment and reminder service
- Calibration of force-measuring devices
- DAkkS calibration certificates in the following languages DE, GB, FR, IT, ES, NL, PL
- Conformity evaluation and reverification of balances and test weights

## Your KERN specialist dealer: