

# 16300/16700

Rectangular or square caps • distinct tactile feel • many legend options




## DISTINCTIVE FEATURES

Rectangular cap : 6 x 12.3 mm; h=16.9 mm

Square cap : 14.9 x 14.9 mm; h=14.6 mm



Many standard legends options

Many functions incl quiet with Unimec™ switches






SWITCH SPECIFICATIONS : see Unimec™ series.

### UNIMEC™+16300



### UNIMEC™+16700



# 16300/16700

Rectangular or square caps • distinct tactile feel • many legend options



## BUILD YOUR PART NUMBER

NON-ILLUMINATED

SERIES	FUNCTION	CAP	COLOR
15			
	400 momentary quiet silver	16300	00 blue
	401 momentary silver	16700	02 green
	402 momentary gold		03 grey
	420 momentary quiet gold		04 yellow
	451 latching silver		06 white
	452 latching gold		08 red
			09 black



## MOUNTING

- Panel cut-out :  
16300 : min. 12.7 x 6.4 mm  
16700 : min. 15.3 x 15.3 mm
- Switch spacing AxB :  
16300 : min. 13 x 13 mm  
16700 : min. 15.5 x 15.5 mm



## MATERIALS

- Cap : ABS UL94HB

# 16310-15

Square solutions • distinct tactile feel • height 16 mm • illumination option



## DISTINCTIVE FEATURES

Square solution 15.1 x 15.1 mm

h=16.0 mm

1-4 LED illumination option




Many standard legend options for 16300 cap

Many functions incl quiet with Unimec™ switches






SWITCH SPECIFICATIONS : see Unimec™ series.




### UNIMEC+16300 + 16310






### UNIMEC+16300 + 16311



### UNIMEC+16300 + 16312



### UNIMEC+16300 + 16315



The company reserves the right to change specifications without notice. All tolerance if not otherwise specified  $\pm 0.2$ mm.

# 16310-15

Square solutions • distinct tactile feel • height 16 mm • illumination option

## BUILD YOUR PART NUMBER

### ILLUMINATED

SERIES	FUNCTION	CAP	COLOR	BEZEL	COLOR	LED 1 - 4	COLOR
15		16300					
400	momentary quiet silver		00 blue	16311		16921	
401	momentary silver		02 green	16312		16920	
402	momentary gold		03 grey	16314			
420	momentary quiet gold		04 yellow	16315			
451	latching silver		06 white		03 grey		04 yellow
452	latching gold		08 red		08 red		08 red
			09 black		09 black		22 green


### NON-ILLUMINATED

SERIES	FUNCTION	CAP	COLOR	BEZEL	COLOR
15		16300		16310	
400	momentary quiet silver		00 blue		00 blue
401	momentary silver		02 green		02 green
402	momentary gold		03 grey		03 grey
420	momentary quiet gold		04 yellow		04 yellow
451	latching silver		06 white		06 white
452	latching gold		08 red		08 red
			09 black		09 black

**NOTICE** : please note that not all combinations of above numbers are available. Refer to [www.apem.com](http://www.apem.com) for further information.

## MOUNTING

- Panel cut-out : min. 14.1 x 14.1 mm
- Switch spacing AxB : min. 15.24 x 15.24 mm



## MATERIALS

- Cap & bezel : ABS UL94HB

# 16324-26

Square solutions • distinct tactile feel • height 20.5 mm • illumination option



## DISTINCTIVE FEATURES

Square solution 15.1 x 15.1 mm

h=20.5 mm

1-2 lens illumination option




Many standard legend options for 16300 cap

Many functions incl quiet with Unimec™ switches






SWITCH SPECIFICATIONS : see Unimec™ series.




### UNIMEC™+16300 + 16324



### UNIMEC™+16300 + 16325



### UNIMEC™+16300 + 16326



# 16324-26

Square solutions • distinct tactile feel • height 20.5 mm • illumination option

## BUILD YOUR PART NUMBER

### ILLUMINATED

SERIES	FUNCTION	CAP	COLOR	BEZEL	LENS 1 OR 2	LED 1 OR 2
15		16300			16927	16922
	400 momentary quiet silver		00 blue	16325 one lens		
	401 momentary silver		02 green	16326 two lenses		
	402 momentary gold		03 grey			
	420 momentary quiet gold		04 yellow			
	451 latching silver		06 white		03 grey	02 green
	452 latching gold		08 red		09 black	04 yellow
			09 black			08 red


### NON-ILLUMINATED

SERIES	FUNCTION	CAP	COLOR	BEZEL	COLOR
15		16300		16324	
	400 momentary quiet silver		00 blue		03 grey
	401 momentary silver		02 green		09 black
	402 momentary gold		03 grey		
	420 momentary quiet gold		04 yellow		
	451 latching silver		06 white		
	452 latching gold		08 red		
			09 black		

**NOTICE :** please note that not all combinations of above numbers are available. Contact APEM for further information.

## MOUNTING

- Panel cut-out : min. 14.1 x 14.1 mm
- Switch spacing AxB : min. 15.24 x 15.24 mm



## MATERIALS

- Cap & bezel : ABS UL94HB
- Lens : polycarbonate UL94V2

# Legends and solid colors

Available for Unimec caps



## STANDARD LEGENDS

STANDARD LEGENDS		
LEGEND	16300 18_	16700 18_
0	000	200
1	001	201
2	002	202
3	003	203
4	004	204
5	005	205
6	006	206
7	007	207
8	008	208
9	009	209
→	033	233
↑	034	234

All standard legends are white on black caps.

The size of the legends listed may not correspond to the actual size.

Custom legends and other color combinations are available, please ask APEM or your local distributor, if you do not find what you need on the list.




## SOLID COLORS

CAP	CODE	Colour / RAL Code							
		Blue / 5012	green / 6018	Grey / 7004	Yellow / 1023	White / 9010	Red / 3000	Black / 9004	
		00	02	03	04	06	08	09	
16300		•	•	•	•	•	•	•	
16700		•	•	•	•	•	•	•	
16310		•	•	•	•	•	•	•	
16311				•			•	•	
16312				•			•	•	
16314				•			•	•	
16315				•			•	•	
16324				•				•	
16325				•				•	
16326				•				•	

The RAL Codes mentioned are the codes nearest to the solid colors in the multimec™ range.

# Unimec™

8 contact functions •  
2 pole • distinct tactile feel



## DISTINCTIVE FEATURES

12.6 x 12.6 mm; h=15.7 mm

2 pole

Momentary, latching or quiet

8 contact functions

Up to 10,000,000 cycle lifetime



## ENVIRONMENTAL SPECIFICATIONS

- Sealing : IP54 according to IEC 60529
- Working temperature : -40°C/+160°C
- Storage temperature : -65°C/+160°C
- Soldering : IEC 68-2-3



## ELECTRICAL SPECIFICATIONS


- Recommended load :
  - Gold contacts : min. 0.5µmA - max. 250mA - 120V - 9W AC - 6W DC
  - Silver contacts : min. 0.5mA - max. 250mA - 120V - 9W AC - 6W DC
- Contact resistance : max. 100mΩ (initially)
- Insulation resistance : >10MΩ
- Contact bounce : max. 10ms
- Dielectric strength between adjacent contacts : 1000 V for 2 min
- Insulation resistance between adjacent contacts : 5 X 10<sup>13</sup>Ω
- Capacitance between adjacent contacts : 0.5 pF



## MECHANICAL SPECIFICATIONS

- Standard actuation force : 2.5N
- Max. actuation force : 100N for 10 sec
- Travel : 1.8 mm
- Lifetime :
  - momentary : >10,000,000 cycles
  - latching : 5,000,000 cycles

The company reserves the right to change specifications without notice.



## MATERIALS

- Housing : LCP UL94V0
- Actuator : LCP UL94V0
- Switch spring : Stainless steel
- Key spring : Stainless steel
- Latch pin : Stainless steel
- Fixed contacts :
  - Silver : SnCu + 2µNI + 3µAg
  - Gold : SnCu + 2µNI + 3µAu
- Moving contacts :
  - Silver : Stainless steel + 3µAg
  - Gold : Stainless steel + 3µAg + 1µAu
- Terminals : SnCu + 2µNI + 3µSn100




All tolerance if not otherwise specified ±0.2mm.



# Unimec™

8 contact functions •  
2 pole • distinct tactile feel

## UNIMEC





- TH
- momentary, latching or quiet
- 8 contact functions

All tolerances unless otherwise noted : ±0.2 mm




## PCB LAYOUT


### PCB MOUNTING HOLE DIMENSIONS



With 3mm LED  
16923 and 16924




With round LED  
16920 and 16921





With square LED  
16922

### FUNCTIONAL DIAGRAM




- up  
-- down

### CIRCUIT DIAGRAM



With round LED  
16920 and 16921




With rect LED  
16922




## WIRING


Select the contact function you require - and design your PC board accordingly




1 make contact



1 break contact



1 change  
over contact




2 make contact




2 break contact



2 change  
over contact




2 make  
& 2 break



reverse polarity



## BUILD YOUR PART NUMBER



\*quiet function has silver terminals, in case of gold terminals the part number is 15420



## ABOUT THIS SERIES



**Notice** : please note that not all combinations of above numbers are available. Refer to [www.apem.com](http://www.apem.com) for further information.



**Laser marking on the switch for identification** : 15400 A; 15420 H; 15401 E; 15402 F; 15451 I; 15452 J



**Accessories** : See pages 379 - 384 or cap and bezel options





## USAGE GUIDELINES

### HOW TO GET THE BEST RESULTS WITH MEC SWITCHES ?

These guidelines are offered to users of MEC Switches as an aid to ensure successful and reliable switch operation. Please see the technical specifications for details on operating and storage temperatures and soldering guidelines to make sure you select the best switch for your application. When wave soldering is taking place, MEC strongly recommend that the temperature profile is analyzed and compared with the temperature rating of the switch. It is also important to monitor the accumulated heat buildup from both the pre-heat zones and the solder zone.

All standard accessories for unimec™ switches are made from ABS plastic with a maximum operating temperature of 65°C. It is strongly recommended that accessories are mounted after soldering of the switch.

LEDs have their own temperature specifications. When fitted in a switch the LED will determine the max. operating temperature, i.e. 16923 has an upper temperature limit of 85°C!

### MOUNTING AND DISMOUNTING

If switches are to be mounted in rows it is essential that the recommendations regarding spacing are followed. PC board thickness should be 1.4±0.2 mm and terminal hole diameter should be 0.9 mm.

All unimec™ caps and bezels are easily snapped onto the switch modules and can be changed at a later time with the exception of the unimec 16.700 cap. Once this cap is installed it is not designed to be removed. To do so may cause damage to the switch and the PC board if not done very carefully.

If the 16.300 or 16.700 cap must be removed from a unimec™ latching switch, make sure that the switch actuator is in the released, upper position before attempting to remove the cap. This will prevent possible damage to the internal latching pin.

### SOLDERING AND CLEANING UNIMEC™ SERIES

Most assembly and field problems experienced by users of unsealed switches are caused by the contamination of the contacts during soldering and cleaning.

Contact contamination may be recognized by an increase in contact resistance and possible intermittent operation of the switch, especially in low power applications. Care must be taken not to submerge the switch in cleaning agents or

spray the switch during cleaning. The switch must be protected at all times to prevent contamination by flux or cleaning liquids.

For unimec™ latching versions we recommend to leave the actuator in the released upper position during soldering. This makes the switch more resistant to overheating.

### SOLDERING - THROUGH HOLE VERSIONS

**Hand soldering:** Max. 350°C for max. 3 sec., this applies for both low temperature and high temperature versions.

**Wave soldering:** Heat built up in the switch during pre-heating and soldering must not exceed the maximum operating temperature of the switch. If, for some reason, a high pre-heating temperature is required, MEC recommend the high temperature switches. In any case peak temperature must not exceed 260°C, and soldering time is max 10 sec. (IEC-68-2-20)

### ROHS COMPLIANCE

As of 1 July 2006 MEC has completed the conversion to RoHS compliance. For more info please see our homepage [www.apem.com](http://www.apem.com)

### TEMPERATURE LIMITS:

Switch	160 °C
LEDs	85/100 °C
Accessories	65 °C

### PACKAGING

Unimec™ switches are packed in rigid tubes of 50 pieces each.

A box contains 1.000 pcs.