

REV

ECO

NOTES: UNLESS OTHERWISE SPECIFIED

2. MATERIAL:

HOUSING: THERMOPLASTIC SEAL: SILICONE RUBBER

- 3. MODIFICATIONS: N/A
- 4. SPECIFICATIONS:
 - 4.1 CURRENT RATING: 7.5 AMPS
 - 4.2 OPERATING TEMPERATURE: -55°C TO +125°C


/1\SEE SHEET 2 FOR KEY ARRANGEMENTS AND COLORS.

REQUIRES CONTACT

RETENTION WEDGE AWM-12S

- 4.3 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
- 4.4 INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 25°C.
- 4.5 MOISTURE RESISTANCE: IP67 (MATED CONDITION)
- 4.6 MATING CYCLE DURABILITY: 100 CYCLES
- 4.7 RoHS COMPLIANT
- 5. MATING PART: ATM04-12PX* RECEPTACLE.

 (X = A,B,C,D KEYS; * = MODIFICATIONS AND COLORS)
- 6. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.



$ \wedge$						
<u>/7</u>	CONTACT	SIZE AND	REAR	SEAL	WIRE	RANGE:

CONTACT	MIN. INSUL	MAX. INSUL	TYPICAL
SIZE	O.D.	O.D.	WIRE RANGE
20	1.35 mm (.053 in)	3.05 mm (.120 in)	

	SEE S	SHEET2									
	PART N	IUMBER		DESCRIPTION IT				ITEM			
QUANTITY		MA	T	ERIA	ALS L	.IST					H
UNLESS OTHER		SIGNATURES		DATE	\Amphonol						
2) Tolerances are a		D.PAR	KS	18/JUN/13	Amphenol			i			
2 PL DEC ±0.15 3 PL DEC ±0.08	Angles ±1°	CHECKED:			Sine Systems - www.amphenol-sine.com					ĺ	
3) Note reference = X		ENGINEER:			44724 Morley Drive				ĺ		
MATERIAL SPECIFICATIONS:		APPROVAL:			Clinton Township, MI 48036						
MATERIAL SPECIFICATIONS:		CUSTOMER:		PLUG, KEYED, 12 SOCKET, ATM SERIE				RIES	;		
		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY, DESIGN FEATURES.					•	•			
PROCESS SPECIFICATIONS:				B C	DWG NO:	ATM06-12S	X-XXX	A REV	13 ×		
NEXT ASS'Y:		MANUFACTURING VAR			SCALE: NONE			SHEET 1	OF	2	

SSI-80ML V TOMBHUMV

REVISIONS

DATE

06/07/13

APPR

PLUG, KEYED, 12 SOCKET, ATM SERIES

ATM06-12SX-XXX

REV: A3


BY


DRP

DESCRIPTION

RELEASE NEW DWG FORMAT


P/N ATM06-12SA **KEY-A CONFIGURATION** STANDARD COLOR: GREY






KEY-A CONFIGURATION					
COLOR PART NUMBER					
* GREY	ATM06-12SA				
BLACK	ATM06-12SA-BLK				
GREEN	ATM06-12SA-GRN				
BROWN	ATM06-12SA-BRN				


P/N ATM06-12SB **KEY-B CONFIGURATION** STANDARD COLOR: BLACK






KEY-B CONFIGURATION					
COLOR	PART NUMBER				
GREY	ATM06-12SB-GRY				
*BLACK	ATM06-12SB				
GREEN	ATM06-12SB-GRN				
BROWN	ATM06-12SB-BRN				


P/N ATM06-12SC **KEY-C CONFIGURATION** STANDARD COLOR: GREEN






KEY-C CONFIGURATION					
COLOR	PART NUMBER				
GREY	ATM06-12SC-GRY				
BLACK	ATM06-12SC-BLK				
* GREEN	ATM06-12SC				
BROWN	ATM06-12SC-BRN				

P/N ATM06-12SD **KEY-D CONFIGURATION** STANDARD COLOR: BROWN






*BROWN	ATM06-12SD			
GREEN	ATM06-12SD-GRN			
BLACK	ATM06-12SD-BLK			
GREY	ATM06-12SD-GRY			
COLOR	PART NUMBER			
KEY-D CONFIGURATION				

NOTE:

AN ASTERISKS (*) PLACED BEFORE THE COLOR DENOTES THE STANDARD MOLDED COLOR OF THE CONNECTORS SHOWN ABOVE.

OTHER COLORS SHOWN ARE AVAILABLE VIA SPECIAL ORDER.



A3 SH:

ATM06-12SX-XXX

PLUG, KEYED, 12 SOCKET, ATM SERIES

A Series™ - Contact Size 20 Options (Works with: ATM, DuraMate and PanelMate Series)

Machined Contacts, Sockets & Pins						
Part Number	Description	Size	AWG	Туре		
AT60-010-2031	Male Contact - Pin, Gold-plated	20	16-18	Machined		
AT62-005-20141	Female Contact - Socket, Gold-plated	20	16-18	Machined		
AT60-010-20141	Male Contact - Pin, Nickel-plated	20	16-18	Machined		
AT62-005-2031	Female Contact - Socket, Nickel-plated	20	16-18	Machined		
AT60-202-2031	Male Contact - Pin, Gold-plated	20	20-22	Machined		
AT62-201-2031	Female Contact - Socket, Gold-plated	20	20-22	Machined		
AT60-202-20141	Male Contact - Pin, Nickel-plated	20	20-22	Machined		
AT62-201-20141	Female Contact - Socket, Nickel-plated	20	20-22	Machined		

Tooling - Machined Contacts						
Part Number	Part Number Description					
AUTK-20	Hand Crimp Tool, Size 20					
AUTK-100	Universal Heavy Duty Contact Crimping Tool Kit, Size 12/16/20					
CA-5D12	Universal Hand Crimp Tool, Size 12/16/20					
CA-5E12	Pneumatic Crimp Tool, Size 12/16/20					

Stamped & Formed Contacts, Sockets & Pins					
Part Number	Description	Size	AWG	Туре	
AT60-20-0144	Male Contact - Pin, Gold-plated	20	16-22	Stamped & Formed	
AT62-20-0144	Female Contact - Socket, Gold-plated	20	16-22	Stamped & Formed	
AT60-20-0244	Male Contact - Socket, Gold-plated	20	16-22	Stamped & Formed	
AT62-20-0244	Female Contact - Socket, Gold-plated	20	16-22	Stamped & Formed	
AT60-20-0122	Male Contact - Pin, Nickel-plated	20	16-22	Stamped & Formed	
AT62-20-0122	Female Contact - Socket, Nickel-plated	20	16-22	Stamped & Formed	
AT60-20-0222	Male Contact - Socket, Nickel-plated	20	16-22	Stamped & Formed	
AT62-20-0222	Female Contact - Socket, Nickel-plated	20	16-22	Stamped & Formed	
AT60-20-0277	Male Contact - Socket, Tin-plated	20	16-22	Stamped & Formed	
AT62-20-0277	Female Contact - Socket, Tin-plated	20	16-22	Stamped & Formed	
AT60-20-0422	Male Contact - Socket, Nickel-plated	20	20-22	Stamped & Formed	
AT62-20-0444	Female Contact - Socket, Gold-plated	20	20-22	Stamped & Formed	

Tooling - Stamped & Formed Contacts					
MFX-3974	Crimp Die - Size 20				
MFX-3976	Crimp Die - Size 20 (20-22AWG -04XX Series)				
MFX-3978	Crimp Die - Size 20 (20-22AWG -02XX Series)				
ATT-20-00	Hand Crimp Tool - Size 20 (20AWG)				

	Contact Removal Tools (For both Machined or Stamped & Formed Contacts)						
Part Number	Description						
ATRT-100	Contact and Wedgelock Extraction Tool						
AT11-240-2005	Contact Removal Tool, Plastic, Size 20						

Sealing Plugs (For both Machined or Stamped & Formed Contacts)	
Part Number	Description
AT13-204-2005	Sealing Plug, Size 20, White
AT13-204-2005-SR	Sealing Plug, Size 20, SR01 Series, Black
ATM13-217-2005	Locking Sealing Plug, Size 20, Grey
ATM13-217-2005-SR	Locking Sealing Plug, Size 20, SR01 Series, Blue